

GRL18S-F2336 GR18S

CYLINDRICAL PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
GRL18S-F2336	1059533

Other models and accessories → www.sick.com/GR18S

Illustration may differ



Detailed technical data

Features

Sensor/ detection principle	Photoelectric retro-reflective sensor, Dual lens
Dimensions (W x H x D)	18 mm x 18 mm x 38.1 mm
Housing design (light emission)	Cylindrical
Thread diameter (housing)	M18 x 1
Optical axis	Axial
Sensing range max.	0.03 m 7.2 m ¹⁾
Sensing range	0.06 m 6 m ¹⁾
Type of light	Visible red light
Light source	PinPoint LED ²⁾
Light spot size (distance)	Ø 175 mm (7 m)
Wave length	650 nm
Adjustment	None
Indication	
LED indicator green	Operating indicator Static: power on
LED indicator yellow	Status of received light beam Static: object not present Static off: object present

¹⁾ Reflector PL80A.

 $^{^{2)}}$ Average service life: 100,000 h at $\rm T_U$ = +25 $^{\circ}\rm C.$

Mechanics/electronics

Supply voltage	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	30 mA
Switching output	PNP
Switching mode	Dark switching
Signal voltage PNP HIGH/LOW	$V_S - (\le 3 \text{ V}) / \text{approx. } 0 \text{ V}$
Output current I _{max.}	\leq 100 mA $^{3)}$
Response time	< 500 µs ⁴⁾
Switching frequency	1,000 Hz ⁵⁾
Connection type	Connector M12, 3-pin
Circuit protection	A ⁶⁾ B ⁷⁾ D ⁸⁾
Protection class	III
Polarisation filter	✓
Housing material	Plastic, ABS
Optics material	Plastic, PMMA
Enclosure rating	IP67
Items supplied	Fastening nuts (2 x)
Electromagnetic compatibility (EMC)	EN 60947-5-2
Ambient operating temperature	-25 °C +55 °C ⁹⁾
Ambient temperature, storage	-40 °C +70 °C
UL File No.	NRKH.E348498 & NRKH7.E348498

 $^{^{1)}\,\}mbox{Limit}$ values. Operated in short-circuit protected network: max. 8 A.

Classifications

ECI@ss 5.0	27270902
ECI@ss 5.1.4	27270902
ECI@ss 6.0	27270902
ECI@ss 6.2	27270902
ECI@ss 7.0	27270902
ECI@ss 8.0	27270902
ECI@ss 8.1	27270902
ECI@ss 9.0	27270902
ECI@ss 10.0	27270902

 $^{^{2)}\,\}mathrm{May}$ not exceed or fall below U_{V} tolerances.

 $^{^{3)}}$ At Uv > 24 V or ambient temperature > 49 °C, IA max. = 50 mA.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

 $^{^{7)}}$ B = inputs and output reverse-polarity protected.

 $^{^{\}rm 8)}$ D = outputs overcurrent and short-circuit protected.

 $^{^{9)}}$ At $\rm U_{v}$ <=24V and $\rm I_{A}{<}50mA.$


GRL18S-F2336 | GR18S

CYLINDRICAL PHOTOELECTRIC SENSORS

ECI@ss 11.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

Connection diagram


Cd-045



Characteristic curve

GRL18S

Operating reserve




Distance in m (feet)

- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- ④ Reflector P250
- ⑤ Reflector PL22
- © Reflective tape REF-Plus 3436


Light spot size

GRL18S



Sensing range diagram


GRL18S



- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- ④ Reflector P250
- ⑤ Reflector PL22
- ® Reflective tape REF-Plus 3436

Dimensional drawing (Dimensions in mm (inch))

GR18S, plastic, connector, straight



- ① Connector M12, 3-pin
- ② Threaded mounting hole M18 x 1
- 3 LED indicator yellow
- 4 LED indicator green
- ⑤ Fastening nut; 22 mm hex, plastic
- 6 Mounting ring

Recommended accessories

Other models and accessories → www.sick.com/GR18S

	Brief description	Туре	Part no.
Mounting brad	ckets and plates		
40	Mounting bracket for M18 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M18	5308446
	Universal mounting bracket for reflectors, steel, zinc coated	BEF-WN-REFX	2064574
Plug connectors and cables			
	Head A: female connector, M12, 3-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m	YG2A13- 050UB1XLEAX	2095753
Reflectors			
	Rectangular, screw connection, 51 mm x 61 mm, PMMA/ABS, Screw-on, 2 hole mounting	P250	5304812

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

