

# PRO-ELEC



**Folding LED Work Light**  
**Models: PEL00946, PEL00947, PEL00948**  
**and PEL00949**

## IMPORTANT SAFETY INFORMATION

**Please read these instructions carefully before use and retain for future reference.**

- When using electrical appliances basic safety precautions should always be followed.
- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting to the mains power supply.
- Keep the work light out of the reach of children.
- LED lamps are extremely bright. To avoid possible damage to the eyes, do not stare into an LED beam.
- If the supply cord is damaged, it must be replaced by a qualified engineer in order to avoid a hazard.
- Ensure that the supply cord is kept away from heat or sharp edges that could cause damage.
- In use, avoid touching any external surface of the work light, due to the possibility of high temperatures.
- Do not leave the work light unattended during use.
- The work light has a sealed LED lamp and is maintenance free. The LED lamp cannot be replaced. When the LED lamp reaches the end of its life, the work light will have to be replaced.
- This appliance is designed for domestic use only and should not be used for industrial purposes.
- Do not use in areas where an explosive or chemical atmosphere may exist.
- Do not use in areas where ventilation is restricted.

## USAGE

- To stand the work light upright, hold the base tube frame down onto the ground and raise the upright part as far as it will go.
- The work light is suitable for both indoor and outdoor use.
- Please note however that the mains connector must only be plugged into an interior power socket or an IP65 rated outdoor enclosure.
- The work light must be positioned so that there is at least 1m between the front of the work light and the surface to be illuminated.
- Do not use on damp or conductive surfaces such as metal. It should be placed away from any flammable materials.
- The angle of the light can be adjusted by slackening off the two thumb wheels and rotating the LED unit to the desired position then re-tightening the thumb wheels to lock it into place.



## CLEANING & MAINTENANCE

- Always unplug and allow the work light to cool down before cleaning.
- Clean the work light using a soft, dry cloth.
- Do not use any chemicals, abrasives or solvents that may damage the work light.

## SPECIFICATION

Model	PEL00946	PEL00947	PEL00948	PEL00949
Rated Voltage	85-260V AC 50/60Hz			
Nominal Luminous Flux	750lm	1500lm	2250lm	3750lm
Wattage	10W	20W	30W	50W
Beam Angle	120°	120°	120°	120°
Number of switching cycles	10,000	10,000	10,000	10,000
Colour Temperature	6000K	6000K	6000K	6000K
Colour Rendering (CRI Ra)	≥80	≥80	≥80	≥80
Ingress Rating	IP65	IP65	IP65	IP65
Dimensions (mm)	240 x 205 x 150	250 x 235 x 165	265 x 265 x 175	310 x 315 x 180
Weight	0.899kg	1.291kg	1.603kg	1.720kg



## **INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.**

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China  
PO Box 13362 Dublin 2  
PR2 9PP

Man Rev 1.2