



Voluntary safety information based on the Safety Data Sheet in accordance with Annex II of Regulation (EC) No 1907/2006

Page 1 of 10

SDS No. : 552583
V002.0

BERGQUIST BOND PLY TBP 850 known as Bond-Ply 100

Revision: 25.08.2022
printing date: 26.08.2022

Replaces version from: 12.12.2019

SECTION 1: Identification of the article and of the company/undertaking

1.1. Product identifier

BERGQUIST BOND PLY TBP 850 known as Bond-Ply 100

1.2. Relevant identified uses of the article and uses advised against

Intended use:

Thermal Conductive Material

1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 211 797 0

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the article

Classification (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

2.2. Label elements

Label elements (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

Following substances are present in a concentration $\geq 0,1\%$ and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in concentration \geq the concentration limit that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Voluntary Information: Only Substances of Very High Concern and Skin Sensitising substances will be disclosed in this section.

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
2-ethylhexyl acrylate 103-11-7 203-080-7 01-2119453158-37	0,1- < 1 %	Skin Irrit. 2, H315 Skin Sens. 1, H317 STOT SE 3, H335 Aquatic Chronic 3, H412		

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the article

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.
In case of fire, keep containers cool with water spray.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective equipment.
Remove sources of ignition.
Ensure adequate ventilation.
Avoid contact with skin and eyes.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Keep in suitable and closed containers for disposal.
Sweep up spilled material. Avoid creating dust.
Scrape up as much material as possible.
Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid skin and eye contact.
See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.
Wash hands before work breaks and after finishing work.
Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.
Keep container tightly sealed.
Refer to Technical Data Sheet

7.3. Specific end use(s)

Thermal Conductive Material

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

None

Occupational Exposure Limits

Valid for
Ireland

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
2-Ethylhexyl acrylate 103-11-7	aqua (freshwater)		0,00272 mg/l				
2-Ethylhexyl acrylate 103-11-7	aqua (marine water)		0,00027 mg/l				
2-Ethylhexyl acrylate 103-11-7	aqua (intermittent releases)		0,011 mg/l				
2-Ethylhexyl acrylate 103-11-7	sewage treatment plant (STP)		2,3 mg/l				
2-Ethylhexyl acrylate 103-11-7	sediment (freshwater)				0,126 mg/kg		
2-Ethylhexyl acrylate 103-11-7	Soil				1 mg/kg		
2-Ethylhexyl acrylate 103-11-7	sediment (marine water)				0,0126 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
2-Ethylhexyl acrylate 103-11-7	Workers	Inhalation	Long term exposure - local effects		37,5 mg/m ³	
2-Ethylhexyl acrylate 103-11-7	Workers	dermal	Acute/short term exposure - local effects		0,242 mg/cm ²	
2-Ethylhexyl acrylate 103-11-7	General population	Inhalation	Long term exposure - local effects		4,5 mg/m ³	
2-Ethylhexyl acrylate 103-11-7	General population	dermal	Acute/short term exposure - local effects		0,242 mg/cm ²	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state	solid
Delivery form	Currently under determination
Colour	white
Odor	slightly
Melting point	Not available.
Solidification temperature	Not applicable, Product is a solid.
Initial boiling point	> 200 °C (> 392 °F)
Flammability	The product is not flammable.
Explosive limits	Currently under determination
Flash point	Not applicable, Product is a solid.
Auto-ignition temperature	Not applicable, Product is a solid.
Decomposition temperature	Not applicable, Substance/mixture is not self-reactive, no organic peroxide and does not decompose under foreseen conditions of use
pH	Currently under determination
Viscosity (kinematic)	Not applicable, Product is a solid.
Solubility (qualitative) (Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	Currently under determination
Vapour pressure	Not available.
Density	Currently under determination
Relative vapour density:	Not available.
Particle characteristics	Not applicable Product is not powder.

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity**10.1. Reactivity**

None.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information**1.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008****Acute oral toxicity:**

Hazardous substances CAS-No.	Value type	Value	Species	Method
2-ethylhexyl acrylate 103-11-7	LD50	4.435 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

Hazardous substances CAS-No.	Value type	Value	Species	Method
2-ethylhexyl acrylate 103-11-7	LD50	7.522 mg/kg	rabbit	not specified

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	irritating	20 h	rabbit	not specified

Serious eye damage/irritation:

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	not irritating	9 d	rabbit	not specified

Respiratory or skin sensitization:

Hazardous substances CAS-No.	Result	Test type	Species	Method
2-ethylhexyl acrylate 103-11-7	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		Ames Test
2-ethylhexyl acrylate 103-11-7	negative	oral: gavage		rat	OECD Guideline 486 (Unscheduled DNA Synthesis (UDS) Test with Mammalian Liver Cells in vivo)

Carcinogenicity

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
2-ethylhexyl acrylate 103-11-7	not carcinogenic	dermal	24 m The animals were treated th...	mouse	male	not specified

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure::

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
2-ethylhexyl acrylate 103-11-7		inhalation: vapour	90 d 6 h/day; 5 days/week	rat	OECD Guideline 413 (Subchronic Inhalation Toxicity: 90-Day)

Aspiration hazard:

Hazardous substances CAS-No.	Viscosity (kinematic) Value	Temperature	Method	Remarks
2-ethylhexyl acrylate 103-11-7	1,19 mm ² /s	40 °C	OECD Test Guideline 114	

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information

12.1. Toxicity

Toxicity (Fish):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	LC50	1,81 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	EC50	1,3 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	NOEC	0,19 mg/l	21 d	Daphnia magna	EPA OTS 797.1330 (Daphnid Chronic Toxicity Test)

Toxicity (Algae):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	NOEC	0,45 mg/l	72 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)
2-ethylhexyl acrylate 103-11-7	EC50	1,71 mg/l	72 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
2-ethylhexyl acrylate 103-11-7	EC10	> 1 mg/l	16 h		not specified

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
2-ethylhexyl acrylate 103-11-7	readily biodegradable	aerobic	70 - 80 %	15 d	EU Method C.4-D (Determination of the "Ready" Biodegradability Manometric Respirometry Test)

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
2-ethylhexyl acrylate 103-11-7	4,64	25 °C	OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
2-ethylhexyl acrylate 103-11-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Dispose of in accordance with local and national regulations.

SECTION 14: Transport information**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the article**

VOC content

< 1 %

(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H335 May cause respiratory irritation.

H412 Harmful to aquatic life with long lasting effects.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Voluntary safety information has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the article in the state in which it is delivered. It is intended to describe our articles from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this voluntary safety information are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.