

# Figure 8 Parallel Speaker Cable

RoHS  
Compliant



## Description

0.34mm<sup>2</sup> Stranded PACW, Figure 8 construction, PVC Insulation.

## Application

For the connecting wiring between the amplifier & speaker.

## Construction

### Conductor

Material : Plain Annealed Copper Wire  
Size : 0.34mm<sup>2</sup>  
Construction : Stranded (7/0.25mm)

### Insulation

Material : PVC  
Nominal O.D : 2.1mm × 4.2mm  
Colour : Black


## Physical Properties

Min. Bend Radius : 21mm  
Operating Temperature : -15°C to +60°C  
Flame Test : IEC60332-1-2

## Electrical Properties

Rated Voltage : 48V AC (not for power application)  
Max. Conductor DC Resistance @20°C : 55Ω/km

## Diagram



## Part Number Table

Description	Part Number
Multicore Cable, Figure 8 Twin, 2 Core, 0.34mm <sup>2</sup> , 100m, Black	2X463 BLK

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.