



## SPECIFICATIONS

Model Name	Radeon™ RX 6400 AERO ITX 4G
Graphics Processing Unit	Radeon™ RX 6400
Cores	768 Units
Memory	4GB GDDR6
Bus Standard	PCI Express® Gen 4 x 4
Memory Interface	64-bit
Core Clocks	Boost: Up to 2321 MHz Game: Up to 2039 MHz
Memory Speed	16 Gbps
Maximum Displays	2
Output	DisplayPort x 1 (v1.4a) / HDMI x 1 (Supports 4K@120Hz/8K@60Hz and VRR as specified in HDMI 2.1)
HDCP Support	Y
Power consumption (W)	53W
Virtual Reality Ready	Y
Digital Maximum Resolution	7680 x 4320
Recommended Power Supply (W)	350W
Power Connectors	N/A
DirectX Version Support	12 API
OpenGL Version Support	4.6
Card Dimension(mm)	172 x 112 x 39 mm
Weight	358g / 718g

## FEATURES



### Afterburner

Take full control with the most recognized and widely used graphics card overlocking software in the world.




### Custom PCB

The custom PCB has been engineered with hardened circuits and optimized trace routing for performance and reliability.



### Thermal Padding

An abundance of thermal pads use any chance for additional heat transfer directly from the components.



### MSI Center

The exclusive MSI Center software lets you monitor, tweak and optimize MSI products in real-time.

## CONNECTIONS



1. HDMI
2. DisplayPort