A and C Weighted Digital Sound Level Meter 30dB to 130dB





Specifications

30~130dB at A, 35~130dB at °C
30Hz~8kHz
A and C
30-130dBA 35-130dBC
A and C characteristics
FAST 125ms, SLOW 1sec
polarized capacitive microphone
4-digit,resolution:0.1dB,sampling rate:2 times/sec
Each analog bar represents 1dB,sampling rate is 20times/sec
30~80dB, 40~90dB, 50~100dB, 60~110dB, 70~120dB, 80~130dB, 6 gear levels in total
Microcomputer will automatically select the best gear level in the range from 30 to 130dB
\checkmark
\checkmark
\checkmark
\checkmark
4x1.5V AAA Batteries
196mm×60mm×30mm
Approx.190g

Part Number Table

Description	Part Number
A and C Weighted Digital Sound Level Meter, 30dB to 130dB	D03130

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

