

Product information

71 72 910

Bolt Cutter



Cuts hard components up to 48 HRC

- Cutting capacity up to 48 HRC hardness
- Robust cutting edges are additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Forged-in stopper with comfortable shock- absorber
- Good access due to very flat construction of head and joint area
- Ergonomically angled handles to minimise effort
- Sturdy non-slip two-colour multi-component handle sleeves
- Precise adjustment (12 positions) by eccentric bolt
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Bolted cutter head, replaceable
- Joint: special tool steel, forged
- Handles: steel tube, powder-coated
- Blade: chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	71 72 910
EAN	4003773066781
Head	grey atramentized
Handles	with multi-component grips
Weight	4,950 g
Dimensions	910 x 170 x 42 mm
Reach	no
RohS	no

Technical details	
HRC 19	Ø 13 mm
HRC 40	Ø 10 mm
HRC 48	Ø 9 mm
Cutting edge length mm	46 mm
Head thickness	42 mm

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

Spare Parts	
71 79 910	Spare cutter head for 71 72 910 complete with screws,

technical change and errors excepted



