

## Product information

# 72 62 200

## High Leverage Flush Cutter

For soft metal and plastic



**Hard cutter for soft material: Made to cut soft metal and plastics with a clean, flush cut**

- For easy and flush cutting of soft metal or thicker profiles and plastic components
- Energy-saving, flush cutting also of thick workpieces thanks to extremely effective lever action mechanism with very low friction
- Space for hands and flush cutting due to 20° angled head with joint bar on one side
- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- Precision cutting edges for soft material
- Durable due to induction-hardened cutting edges to 59 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	72 62 200
EAN	4003773081913
Pliers	black atramentized
Handles	with slim multi-component grips
Weight	375 g
Dimensions	200 x 62 x 24 mm
Reach	yes
RohS	no

### Technical details

Cutting capacities soft wire (diameter)	Ø 6.0 mm
---	----------

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

### Spare Parts

71 19 200 01	Spare spring holder for 71 X2 200 / 72 62 200,
--------------	--

technical change and errors excepted



Clean, flush cutting of copper conductor rails



Ideal for the flush cutting plastic sprues with large diameters

