

## Product information

# 86 06 250

## Pliers Wrench

Pliers and a wrench in a single tool

IEC 60900 DIN EN 60900



⚡ 1000V 




- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings - working directly on chrome!
- Practical adjustment scale: A laser-cut (metric and imperial) scale enables pre-setting to the width across flats
- Also excellent for gripping, holding, pressing and bending workpieces
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Fast adjustment by pushing a button directly on the workpiece
- No unintentional shift of the gripping jaws and no slipping of the joint
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened

### General

Article No.	86 06 250
EAN	4003773082408
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	525 g
Dimensions	250 x 75 x 28 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details

Jaw thickness (joint) (B2)	8.0 mm
Joint thickness (B3)	14.0 mm
Tips thickness (B1)	8.0 mm
Adjustment positions	19
Capacities for nuts	Ø 2 Inch
Capacities for nuts	52 mm



<b>Classification</b>	
eCl@ss 5.1.4	21043826
proficl@ss 6.0	AAA936c004
<b>Accessories</b>	
86 09 250 V01	Protective jaws for 86 XX 250, 3 pairs
<b>Spare Parts</b>	
87 09 01	Assortment of spare parts for adjustment for 86/87 XX 250/300 (without 87 2X XXX),

*technical change and errors excepted*

