



12500 TI Boulevard, MS 8640, Dallas, Texas 75243

**PCN#20220802000.1**

**Qualification of new Fab site (FFAB) using qualified Process Technology, Die Revision, and additional Assembly, Datasheet & BOM option for select devices**

**Change Notification / Sample Request**

**Date:** August 03, 2022  
**To:** PREMIER FARNELL PCN

Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments (TI). The details of this change are on the following pages, and are in alignment with our standard product change notification (PCN) [process](#).

TI requires acknowledgement of receipt of this notification within 30 days of the date of this notice. Lack of acknowledgement of this notice within 30 days constitutes acceptance of the change. If samples or additional data are required, requests must be received within 30 days of this notification, given that samples are not built ahead of the change.

The Proposed First Ship date in this PCN letter is the earliest possible date that customers could receive the changed material. It is our commitment that the changed device will not ship before that date. If samples are requested within the 30 day sample request window, customers will still have 30-days to complete their evaluation regardless of the proposed 1st ship date.

This particular PCN is related to TI's multiyear transition plan for our two remaining factories with 150-millimeter production (DFAB in Dallas, Texas, and SFAB in Sherman, Texas). DFAB will remain open, but will focus on 200-mm production, with a smaller set of technologies. SFAB will close no earlier than 2024 and no later than 2025. As referenced in the "reason for change" below, these changes are part of our multiyear plan to transition these products to newer, more efficient manufacturing processes and technologies, underscoring our commitment to product longevity and supply continuity.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the PCN Team ([PCN\\_admin\\_team@list.ti.com](mailto:PCN_admin_team@list.ti.com)). For sample requests or sample related questions, contact your local Field Sales Representative. As always, we thank you for your continued business.

PCN Team  
SC Business Services

**20220802000.1**  
**Attachment: 1**

**Products Affected:**

The devices listed on this page are a subset of the complete list of affected devices. According to our records, these are the devices that you have purchased within the past twenty-four (24) months. The corresponding customer part number is also listed, if available.

DEVICE	CUSTOMER PART NUMBER
INA128U	null

Technical details of this Product Change follow on the next page(s).

<b>PCN Number:</b>	20220802000.1		<b>PCN Date:</b>	August 03, 2022																			
<b>Title:</b>	Qualification of new Fab site (FFAB) using qualified Process Technology, Die Revision, and additional Assembly, Datasheet & BOM options for select devices																						
<b>Customer Contact:</b>	<a href="#">PCN Manager</a>		<b>Dept:</b>	Quality Services																			
<b>Proposed 1<sup>st</sup> Ship Date:</b>	Oct 31, 2022		<b>Sample Requests accepted until:</b>	Sept 3, 2022*																			
<b>*Sample requests received after Sept 3, 2022 will not be supported.</b>																							
<b>Change Type:</b>																							
<input type="checkbox"/>	Assembly Site	<input checked="" type="checkbox"/>	Assembly Process	<input checked="" type="checkbox"/>	Assembly Materials																		
<input checked="" type="checkbox"/>	Design	<input checked="" type="checkbox"/>	Electrical Specification	<input type="checkbox"/>	Mechanical Specification																		
<input type="checkbox"/>	Test Site	<input type="checkbox"/>	Packing/Shipping/Labeling	<input type="checkbox"/>	Test Process																		
<input type="checkbox"/>	Wafer Bump Site	<input type="checkbox"/>	Wafer Bump Material	<input type="checkbox"/>	Wafer Bump Process																		
<input checked="" type="checkbox"/>	Wafer Fab Site	<input checked="" type="checkbox"/>	Wafer Fab Materials	<input checked="" type="checkbox"/>	Wafer Fab Process																		
		<input type="checkbox"/>	Part number change																				
<b>PCN Details</b>																							
<b>Description of Change:</b>																							
Texas Instruments is pleased to announce the qualification of a new fab & process technology (FFAB, BICOM3XHV) die revision, and Assembly & BOM option for selected devices as listed below in the product affected section. Construction differences are noted below:																							
<table border="1"> <thead> <tr> <th colspan="3">Current Fab Site</th> <th colspan="3">Additional Fab Site</th> </tr> <tr> <th>Current Fab Site</th> <th>Process</th> <th>Wafer Diameter</th> <th>Additional Fab Site</th> <th>Process</th> <th>Wafer Diameter</th> </tr> </thead> <tbody> <tr> <td>SFAB</td> <td>J11</td> <td>150 mm</td> <td>FFAB</td> <td>BICOM3XHV</td> <td>200 mm</td> </tr> </tbody> </table>			Current Fab Site			Additional Fab Site			Current Fab Site	Process	Wafer Diameter	Additional Fab Site	Process	Wafer Diameter	SFAB	J11	150 mm	FFAB	BICOM3XHV	200 mm			
Current Fab Site			Additional Fab Site																				
Current Fab Site	Process	Wafer Diameter	Additional Fab Site	Process	Wafer Diameter																		
SFAB	J11	150 mm	FFAB	BICOM3XHV	200 mm																		
The die was also changed as a result of the process change.																							
Additionally, there will be a BOM/Assembly options introduced for these devices in Group 1 below:																							
		<b>MLA Current</b>	<b>MLA Alternate</b>																				
Bond wire composition, diameter		Au, 1.2 mils	Cu, 1.0 mil																				
Mold Compound		4209640	4226323																				
Mount Compound		4205846	4147858																				
The datasheets will be changing as a result of the above mentioned changes. The datasheet change details can be reviewed in the datasheet revision history. The link to the revised datasheet is available in the table below.																							

Changes from Revision E (April 2019) to Revision F (May 2022)	Page
• Updated the numbering format for tables, figures, and cross-references throughout the document.....	1
• Added bandwidth and noise specifications in <i>Features</i> .....	1
• Changed <i>Applications</i> to link to latest end-equipment solutions on ti.com.....	1
• Changed reference from INA819 to INA818 in <i>Device Comparison Table</i> .....	4
• Added single supply specification to <i>Absolute Maximum Ratings</i> .....	5
• Added note clarifying output short-circuit "to ground" in <i>Absolute Maximum Ratings</i> refers to short-circuit to $V_S / 2$ .....	5
• Added single supply specification to <i>Recommended Operating Conditions</i> .....	5
• Changed input common-mode voltage range specification from $V - 2$ to $(V-) + 2$ in <i>Recommended Operating Conditions</i> .....	5
• Deleted INA128-HT and INA129-HT operating temperature specifications from <i>Recommended Operating Conditions</i> .....	5
• Added specified temperature range to <i>Recommended Operating Conditions</i> .....	5
• Added $V_{REF} = 0\text{ V}$ , $V_{CM} = V_S / 2$ , and $G = 1$ to "unless otherwise noted" conditions in <i>Electrical Characteristics</i> and <i>Typical Characteristics</i> for clarity.....	6
• Changed test condition for offset voltage drift specification in <i>Electrical Characteristics</i> from " $T_A = T_{MIN}$ to $T_{MAX}$ " to " $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ " for clarity.....	6
• Changed typical long-term stability specification from $\pm 0.1 \pm 3/G\text{ }\mu\text{V/mo}$ to $\pm 0.2 \pm 3/G\text{ }\mu\text{V/mo}$ in <i>Electrical Characteristics</i> .....	6
• Changed common-mode voltage specification from $(V-) + 2\text{ V}$ minimum and $(V+) - 2\text{ V}$ minimum across two rows to $(V-) + 2\text{ V}$ minimum and $(V+) - 2\text{ V}$ maximum across one row in <i>Electrical Characteristics</i> .....	6
• Deleted typical common-mode voltage specifications in <i>Electrical Characteristics</i> .....	6
• Added test condition of " $R_S = 0\text{ }\Omega$ " to safe input voltage specification in <i>Electrical Characteristics</i> for clarity....	6
• Added test condition of " $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ " to input bias current drift specification in <i>Electrical Characteristics</i> for clarity.....	6
• Added test condition of " $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ " to input offset current drift specification in <i>Electrical Characteristics</i> for clarity.....	6
• Changed maximum gain error specification for INA128PA/UA and INA129PA/UA with $G = 1$ from $\pm 0.01\%$ to $\pm 0.1\%$ in <i>Electrical Characteristics</i> .....	6
• Added test condition of " $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ " for gain drift in <i>Electrical Characteristics</i> for clarity.....	6
• Changed parameter names from "Voltage - Positive" to "Positive output voltage swing" and from "Voltage - Negative" to "Negative output voltage swing" in <i>Electrical Characteristics</i> .....	6
• Deleted typical positive and negative output voltage swing specifications in <i>Electrical Characteristics</i> .....	6
• Added test condition of "Continuous to $V_S / 2$ " to short-circuit current specification in <i>Electrical Characteristics</i> for clarity.....	6
• Changed typical bandwidth specification for $G = 10$ from 700 kHz to 640 kHz in <i>Electrical Characteristics</i> .....	6
• Changed typical slew rate specification from 4 V/ $\mu\text{s}$ to 1.2 V/ $\mu\text{s}$ in <i>Electrical Characteristics</i> .....	6
• Changed typical settling time specification for $G = 1$ , $G = 10$ , and $G = 100$ from 7 $\mu\text{s}$ , 7 $\mu\text{s}$ , and 9 $\mu\text{s}$ respectively to 12 $\mu\text{s}$ , 12 $\mu\text{s}$ , and 12 $\mu\text{s}$ , in <i>Electrical Characteristics</i> .....	6
• Deleted redundant voltage range, operating temperature range, and specification temperature range specifications from <i>Electrical Characteristics</i> .....	6
• Changed Figures 7-1, 7-3, 7-4, 7-9, 7-10, 7-11, 7-16, 7-17, 7-20, 7-21.....	8
• Changed values discussed in <i>Input Common-Mode Range</i> from typical input common-mode voltage range values to maximum and minimum values.....	14
• Changed Figure 9-1 to fix missing text and include reference voltage.....	15
• Added more detailed guidance concerning REF pin in <i>Design Requirements</i> .....	15
• Changed Figures 9-6, 9-7.....	18
• Changed Figures 9-10 and 9-11 to fix missing text.....	19
• Added <i>Related Documentation</i> links to <i>Device and Documentation Support</i> .....	22

Products	Current Datasheet Number	New Datasheet Number	Link to full datasheet
INA128/9	SBOS051E	SBOS051F	<a href="https://www.ti.com/lit/ds/symlink/ina129.pdf?ts=1659050265615&amp;ref_url=https%253A%252F%252Fwww.ti.com%252Fproduct%252FINA129%253FkeyMatch%253DINA129%2526tsearch%253Dsearch-everything%2526usecase%253DGPN">https://www.ti.com/lit/ds/symlink/ina129.pdf?ts=1659050265615&amp;ref_url=https%253A%252F%252Fwww.ti.com%252Fproduct%252FINA129%253FkeyMatch%253DINA129%2526tsearch%253Dsearch-everything%2526usecase%253DGPN</a>

**Reason for Change:**

These changes are part of our multiyear plan to transition products from our 150-millimeter factories to newer, more efficient manufacturing processes and technologies, underscoring our commitment to product longevity and supply continuity.

**Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):**

None

**Impact on Environmental Ratings**

Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings.

RoHS	REACH	Green Status	IEC 62474
<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change	<input checked="" type="checkbox"/> No Change

**Changes to product identification resulting from this PCN:****Fab Site Information:**

Chip Site	Chip Site Origin Code (20L)	Chip Site Country Code (21L)	Chip Site City
SH-BIP-1	SHE	USA	Sherman
<b>FFAB</b>	<b>FRE</b>	<b>DEU</b>	<b>Freising</b>

**Die Rev:****Current****New**

Die Rev [2P]	Die Rev [2P]
E	A

Sample product shipping label (not actual product label)

 **TEXAS INSTRUMENTS**  
MADE IN: Malaysia  
2DC: 20:  
MSL 2 /260C/1 YEAR SEAL DT  
MSL 1 /235C/UNLIM 03/29/04  
OPT:  
ITEM: 39  
**LBL: 5A (L)T0:1750**



(1P) **SN74LS07NSR**  
(Q) **2000** (D) **0336**  
(31T) LOT: 3959047MLA  
(4W) TKY (1T) 7523483SI2  
(P)  
(2P) REV: (V) 0033317  
(20L) ~~SSO: SHE~~ (21L) ~~CCO: USA~~  
(22L) ASO: MLA (23L) ~~ACO: MYS~~

**Product Affected:****Group 1 Device list (Wafer fab, die revision, BOM and Datasheet changes)**

INA128U	INA128UAE4	INA129U/2K5	INA128U/2K5G4
INA129U	INA128UAG4	INA128UA/2K5	INA128UA/2K5E4
INA128UA	INA129UAE4	INA129UA/2K5	INA128UA/2K5G4
INA129UA	INA128U/2K5	INA128U-2/2K5	INA129UA/2K5G4
INA128UG4			

**Group 2 Device list (Datasheet changes only)**

INA128P	INA128PA	INA128PG4	INA129PG4
INA129P	INA129PA		

For alternate parts with similar or improved performance, please visit the product page on [TI.com](https://www.ti.com)



TI Information  
Selective Disclosure

**Qualification Report**

Approve Date 01-Apr-2022

**Qualification Results**

Data Displayed as: Number of lots / Total sample size / Total failed

Type	Test Name / Condition	Duration	Qual Device: INA128U	QBS Process Reference: INA828ID	QBS Package Reference: INA849D
HTOL	Life Test, 100C <sup>A</sup>	300 Hours	-	-	1/77/0
HTOL	Life Test, 150C	300 Hours	-	3/231/0	-
HBM	ESD - HBM	2000 V	1/3/0	1/3/0	1/3/0
CDM	ESD - CDM	1000 V	1/3/0	1/3/0	1/3/0
LU	Latch-up	JEDEC78	1/6/0	1/6/0	1/6/0
ED	Electrical Characterization	Per Datasheet Parameters	1/30/0	3/90/0	1/30/0
HAST	Biased HAST, 130C/85%RH	96 Hours	-	3/231/0	-
HBM	ESD - HBM	2000 V	1/3/0	1/3/0	1/3/0
HTSL	High Temp Storage Bake 170C	420 Hours	-	3/231/0	3/231/0
TC	Temperature Cycle, -65/150C	500 Cycles	-	3/231/0	3/231/0
THB	Biased Temperature and Humidity, 85C/85%RH	1000 Hours	-	-	3/231/0
UHAST	Unbiased HAST 130C/85%RH	96 Hours	-	3/231/0	3/231/0

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable  
- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours  
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours  
- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles  
Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

**Green/Pb-free Status:**

Qualified Pb-Free(SMT) and Green

<sup>A</sup> Tj of device at 150C

Change Number: C2011216

TI Qualification ID: 20201124-137263

- QBS: Qual By Similarity

- Qual Device INA128U is qualified at LEVEL2-260C

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours

- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours

- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

**Green/Pb-free Status:**

Qualified Pb-Free(SMT) and Green



TI Information  
Selective Disclosure

## Qualification Report

Approve Date 01-Apr-2022

### Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Type	Test Name / Condition	Duration	Qual Device: INA129U	QBS Product Reference: INA128U	QBS Process Reference: INA828ID	QBS Package Reference: INA849D
HTOL	Life Test, 100C <sup>A</sup>	300 Hours	-	-	-	1/77/0
HTOL	Life Test, 150C	300 Hours	-	-	3/231/0	-
HBM	ESD - HBM	2000 V	-	1/3/0	1/3/0	1/3/0
CDM	ESD - CDM	1000 V	-	1/3/0	1/3/0	1/3/0
LU	Latch-up	JEDEC78	-	1/6/0	1/6/0	1/6/0
ED	Electrical Characterization	Per Datasheet Parameters	-	1/30/0	3/90/0	1/30/0
HAST	Biased HAST, 130C/85%RH	96 Hours	-	-	3/231/0	-
HTSL	High Temp Storage Bake 170C	420 Hours	-	-	3/231/0	3/231/0
TC	Temperature Cycle, -65/150C	500 Cycles	-	-	3/231/0	3/231/0
THB	Biased Temperature and Humidity, 85C/85%RH	1000 Hours	-	-	-	3/231/0
UHA	Unbiased HAST 130C/85%RH	96 Hours	-	-	3/231/0	3/231/0
YLD	FTY and Bin Summary	-	1/Pass	-	-	-

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

- The following are equivalent HTOL options based on an activation energy of 0.7eV: 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours

- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours

- The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: <http://www.ti.com/>

**Green/Pb-free Status:**

Qualified Pb-Free(SMT) and Green

<sup>A</sup> Tj of device at 150C

TI Qualification ID: 20210624-140661



For questions regarding this notice, e-mails can be sent to the contacts shown below or your local Field Sales Representative.

Location	E-Mail
WW Change Management Team	<a href="mailto:PCN_ww_admin_team@list.ti.com">PCN_ww_admin_team@list.ti.com</a>

#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disdaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI’s products are provided subject to TI’s Terms of Sale ([www.ti.com/legal/termsofsale.html](http://www.ti.com/legal/termsofsale.html)) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI’s provision of these resources does not expand or otherwise alter TI’s applicable warranties or warranty disclaimers for TI products.