

BEAKER HEATERS

Ideal for Laboratory and Oil Bath Applications



SRBH Series



- ✓ Easy-to-Install and Remove
- ✓ Moisture and Chemical Resistant
- ✓ Evenly Heats Across Beaker Surface
- ✓ Fits Griffin and Standard Size Beakers
- ✓ Hook and Loop Closure Allow for Quick Installation and Removal
- ✓ Easily View Graduation During Set-Up and Operation

- ✓ Heating Element Laminated Between Two Layers of 15 ml Fiberglass Reinforced Silicone Rubber
- ✓ 120 or 240 Vac
- ✓ Requires a Temperature or Power Controller* (Not Included)
- ✓ 73/23/EC (Low Voltage Directive)

SPECIFICATIONS

Max Exposure Temperature: 232°C (450°F)
Power Density: 5.0 watts/in² (0.008 watts/mm²)
Dielectric Strength: Over 2000V
Power Leads: 61 cm (2')
Standard 2-Prong Plug: 120 Vac (NEMA 1 to 15)
Bare Wire Connection: 240 Vac

To Order

120 Vac Model No.	240 Vac Model No.	Total Watts	Height mm (in)	Length mm (in)	Size ml (oz)	Beaker Dia mm (in)
SRBH0250-1	SRBH0250-2	150	76 (3)	311 (12.25)	250 (8.45)	69 (2.7)
SRBH0400-1	SRBH0400-2	200	89 (3.5)	349 (13.75)	400 (13.5)	76 (3.0)
SRBH0600-1	SRBH0600-2	250	102 (4)	381 (15)	600 (20.3)	91 (3.6)
SRBH1000-1	SRBH1000-2	350	117 (4.6)	438 (17.28)	1000 (33.8)	109 (4.3)

Comes complete with operator's manual.

* For a complete selection of controllers, visit us online.

Ordering Example: SRBH0600-1 beaker heater, 250 watts, 600 ml (20.3 oz) beaker volume.