

Product information

90 42 340

Punch Lock Riveter

- To join metal section sheets used in dry walling for dividing walls and drop ceilings, without needing screws or rivets
- For U- and C-shaped sections with max 1.2 mm metal (2 x 0.6 mm)
- Minimum handforce required due to optimum lever transmission
- Pliers body: special tool steel, rolled, oil-hardened



General

Article No.	90 42 340
EAN	4003773071884
Pliers	burnished
Handles	with multi-component grips
Weight	901 g
Dimensions	340 x 96 x 19 mm
Reach	no
RohS	no

Technical details

Capacity in millimetres	max. 1.2 (2 x 0.6)
-------------------------	--------------------

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC011914
ETIM 6.0	EC011914
proficl@ss 6.0	EAC043c008
UNSPSC 13.1	27112115

Spare Parts

90 49 340	Spare punch for 90 42 340,
90 49 340 M	Spare die for 90 42 340,

technical change and errors excepted



The punching tool is squeezed through the metal section sheets



Setting the pliers for connection of two metal section sheets