

Smart Temperature Transmitters



TX13



- ✓ **K, J, N, E, T, R, S**
Thermocouples and mV Inputs
- ✓ **Pushbutton Configuration**
- ✓ **56 Preprogrammed Ranges Ready-to-Use**
- ✓ **User Trim—Null Out Sensor Error**
- ✓ **Programmable Burnout with Sensor Fail Indicator**
- ✓ **Galvanically Isolated**

The TX13 is a “smart” in head transmitter that accepts thermocouple temperature sensors and converts sensor output over a configured range to a standard industrial (4 to 20 mA) transmission signal.

A simple push button operation allows the user to select TC type, burnout direction, select fixed ranges and trim 4 and 20 mA points. The in head transmitter incorporates the latest digital technology to ensure accurate drift-free performance.

If required the desired range can be specified at the time of order, removing the need for user configuration. If the range is not specified then the transmitter will be shipped with the default range of 0 to 1000°C (32 to 1832°F) Type K.

Specifications

Isolation: Tested to 250 Vdc

Sensor Burnout: Either up or down scale output

Cold Junction:

Range: -40 to 85°C (-40 to 185°F)

Accuracy: ±0.5°C (33°F)

Tracking: ±0.05°C/°C (32°F/°F)

Stability:

Offset: 0.1°C/°C (32°F/°F)

Span: 0.05°C/°C (32°F/°F)

Output

Output Type: 2 wire, 4 to 20 mA current loop

Output Range: 4.0 to 20.0 mA

Output Connection: Screw terminal

Maximum Output: 21.5 mA
(in high burnout condition)

Minimum Output: 3.8 mA
(in low burnout condition)

Accuracy: (mA output /2000) or 5 uA
(whichever is the greater)

Loop Voltage Effect: 0.2 uA/V

Thermal Drift: 1 uA/°C

Maximum Output Load:

$[(V_{supply}-10)/20]K$

(Example: 700 @ 24V)

Update Time: 500 mS

Response Time: 1 second

Start Up Time: 4 seconds
(1 out < 4 mA during start up)

Warm-Up Time: 1 minute to full accuracy

Power Supply: 10 to 30 Vdc

Environmental

Ambient Operating Range:

-40 to 85°C (-40 to 185°F)

Ambient Storage Temperature:

-50 to 90°C (-58 to 194°F)

Ambient Humidity Range: 10 to 90%

RH non condensing

Physical

Dimensions: 43 mm Dia; 21 mm H

(1.7"; 0.8")

Weight: 31 g (0.07 lbs) (encapsulated)

Specifications @ 20°C—Input

Sensor	Range °C (°F)	Accuracy
K	-200 to 1370 (-328 to 2498)	± 0.5°C (33°F) or ± 0.01% which ever the greater
J	-100 to 1200 (-148 to 2192)	± 0.5°C (33°F) or ± 0.01% which ever the greater
E	-200 to 1000 (-328 to 1832)	± 0.5°C (33°F) or ± 0.01% which ever the greater
N	-180 to 1300 (-292 to 2372)	± 0.5°C (33°F) or ± 0.01% which ever the greater
T	-200 to 400 (-328 to 752)	± 0.5°C (33°F) or ± 0.01% which ever the greater
R	-10 to 1760 (14 to 3200)	± 0.5°C (33°F) or ± 0.01% which ever the greater over range 800 to 1600
S	-10 to 1760 (14 to 3200)	± 0.5°C (33°F) or ± 0.01% which ever the greater over range 800 to 1600
mV	-10 to 70 (14 to 158)	± 0.02% of full scale



TX13,
shown larger
than actual size.

Approvals

EMC - BS EN 61326 :1998: Electrical equipment for measurement control and laboratory use

ANNEX A: Immunity test requirements for equipment intended for use in industrial locations

ANNEX F: Test configurations, operational conditions and performance criteria for transducers with integrated or remote signal conditioning

IEC 61000-4-2: Electrostatic discharge

IEC 61000-4-3: EM field

IEC 61000-4-4: Transient burst (output)

IEC 61000-4-5: Surge (output)

Note: Sensor input wires to be less than 3 m (10') to comply.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Description
TX13	Thermocouple/ mV smart transmitter
TX2-100	2 core screened cable, 30 metre reel
PSR-24L-230-UK	Regulated power supply, 24 Vdc, 400 mA, stripped leads, 230 Vac input. 3-pin UK plug
PSR-24L-230	Regulated power supply, 24 Vdc, 400 mA, stripped leads, 230 Vac input. 2-pin Euro plug
TX-SCALED	Scaling charge for factory set up of range (specify temperature range)

Comes with operator's manual.

Ordering Example: TX13, thermocouple smart transmitter,

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters