
NEW™ EARTH TERMINAL BLOCKS

Starts at

Pack of 25

RoHS



XBUT4D12PE-25PK, for pack of 25



XBUT35PE-25PK, for pack of 25



XBUT4D22PE-25PK, for pack of 25



All models shown smaller than actual size.

- Maintenance-Free Connections
- Global Acceptance
- Multi-Conductor Connections
- Flexible Plug-In Bridge System
- Large Surface Area for Marking
- Standardised Testing System
- Metal Parts Made of Tin-Plated Copper Alloy

The earth terminal blocks have the same shape and pitch as the standard terminal block, in a green yellow housing. They easily snap onto the DIN rail to make a reliable mechanical and electrical contact which meets all requirements of IEC 60-947-7-2.

SPECIFICATIONS FOR XBUT4PE, XBUT4D12PE, XBUT4D22PE

Terminal Width: 6.2 mm
Wire Size: 10 AWG/4 mm²
IEC 60 947-7-1 in AWG: 26-10
EN 50 019 in AWG: 26-10
UL-cUL Ratings in AWG: 26-10
Width/Length/Cover Width in mm:
XBUT4PE: 6.2/46.9/2.2
XBUT4D12PE: 5.2/56.8/2.2
XBUT4D22PE: 6.2/64.1/2.2
Height for 35 x 7.5/35 x 15 in mm: 47.5/55.0

SPECIFICATIONS FOR XBUT25D12PE, XBUT25D22PE


Terminal Width: 5.2 mm
Wire Size: 12 AWG/2.5 mm²
IEC 60 947-7-1 in AWG: 26-12
EN 50 019 in AWG: 26-12
UL-cUL Ratings in AWG: 26-12
Width/Length/Cover Width in mm: 5.2/56.8/2.2
Height for 35 x 7.5/35 x 15 in mm: 47.5/55.0

OTHER SPECIFICATIONS FOR XBUT4PE XBUT4D12PE, XBUT4D22PE, XBUT25D12PE, XBUT25D22PE


TECHNICAL DATA IN ACCORDANCE WITH IEC
XBUT4PE
Rated Surge Voltage in kV/Contamination Class: 8/3
XBUT4D12PE, XBUT4D22PE, XBUT25D12PE, and XBUT25D22PE
Rated Surge Voltage in kV/Contamination Class: 6/3
Surge Voltage Category/Insulating Material Group: III/I

CONNECTION CAPACITY
XBUT4PE, XBUT4D12PE, and XBUT4D22PE
Stranded with Ferrule/with Ferrule and Plastic Sleeve in mm²: 0.25 to 4/0.25 to 4
XBUT25D12PE, XBUT25D22PE
Stranded with Ferrule/with Ferrule and Plastic Sleeve in mm²: 0.25 to 2.5/0.25 to 2.5

MULTI-CONDUCTOR CONNECTION (SAME CROSS-SECTION)
Solid/Stranded in mm²: 0.14 to 1.5/0.14 to 1.5
Stranded with Ferrules without Plastic Sleeve in mm²: 0.25 to 1.5
Stranded with Twin Ferrule with Plastic Sleeve in mm²: 0.5 to 2.5
XBUT4PE/XBUT4D12PE, XBUT4D22PE, XBUT25D12PE, and XBUT25D22PE
Stripping Length in mm: 9/8
Thread: M3
Torque, Nm: 5.3 to 7.1



XBUT25D22PE-25,
for pack of 25



XBUT4D12PE-25PK,
for pack of 25

To Order *(Specify Model Number)*

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	DESCRIPTION
XBUT4PE-25PK	6.2 mm wide, 2.6 mm dia. max, green/yellow earth blocks, pack of 25
XBUT4D12PE-25PK	6.2 mm wide, 2.6 mm dia. max, 3-wire multi-conductor earth blocks, pack of 25
XBUT4D22PE-25PK	6.2 mm wide, 2.6 mm dia. max, 4-wire multi-conductor earth blocks, pack of 25
XBUT25D12PE-25PK	5.2 mm wide, 2 mm dia. max, 3-wire multi-conductor earth blocks, pack of 25
XBUT25D22PE-25PK	5.2 mm wide, 2 mm dia. max, 4-wire multi-conductor earth blocks, pack of 25

Ordering Example: XBUT4PE-25PK, *earth terminal blocks,* ***XBACUT10-10PK,*** *end covers,* ***XBANS3575P,*** *DIN rail*

ACCESSORIES

MODEL NO.	DESCRIPTION
XBACUT10-10PK	Grey end cover, pack of 10 for XBUT4PE-25PK
XBACUT4D12-10PK	Grey end cover, pack of 10 for XBUT4D12PE-25PK, XBUT25D12PE-25PK
XBACUT4D22-10PK	Grey end cover, pack of 10 for XBUT4D22PE-25PK, XBUT25D22PE-25PK
XBATUT10-10PK	Grey partition plate, pack of 10 for XBUT4PE-25PK
XBAFBS25-10PK	Red 2-position plug-in bridge, pack of 10 for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS35-10PK	Red 3-position plug-in bridge, pack of 10 for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS55-10PK	Red 5-position plug-in bridge, pack of 10 for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS105-10PK	Red 10-position plug-in bridge, pack of 10 for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS505	Red 50-position plug-in bridge for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS36-10PK	Red 3-position plug-in bridge, pack of 10 for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS56-10PK	Red 5-position plug-in bridge, pack of 10 for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS106-10PK	Red 10-position plug-in bridge, pack of 10 for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBAFBS506	Red 50-position plug-in bridge for XBUT4PE-25PK, XBUT4D12PE-25PK, XBUT4D22PE-25PK
XBATSPAI4-10PK	Test adaptor, pack of 10
XBMZB6-10PK	White blank marker strip, pack of 10
XBANS3575P	DIN rail 35 x 7.5 mm x 2 m slotted
XBANS3575U	DIN rail 35 x 7.5 mm x 2 m solid
XBANS3515P	DIN rail 35 x 15 mm x 2 m slotted
XBANS3515U	DIN rail 35 x 15 mm x 2 m solid
XBAES35C-50PK	1-screw mounted end stop, pack of 50
XBAES35T-50PK	3-screw mounted end stop, pack of 50
XBAES35N-50PK	Snap-on end stop, pack of 50

SPECIFICATIONS FOR XBUT6PE


Terminal Width: 8.2 mm
Maximum Wire Size: 8 AWG/6 mm²
IEC 60 947-7-1 in AWG: 24-8
EN 50 019 in AWG: 24-8
UL-cUL Ratings in AWG: 24-8

TECHNICAL DATA DIMENSIONS
Width/Length/Cover Width in mm: 8.2/46.9/2.2
Height for 35 x 7.5/35 x 15 in mm: 47.5/55.0

TECHNICAL DATA IN ACCORDANCE WITH IEC
Rated Surge Voltage in kV/Contamination Class: 8/3
Surge Voltage Category/Insulating Material Group: III/I

CONNECTION CAPACITY
Stranded with Ferrule/with Ferrule and Plastic Sleeve in mm²: 0.25 to 6/0.25 to 6

MULTI-CONDUCTOR CONNECTION (SAME CROSS-SECTION)
Solid/Stranded in mm²: 0.2 to 2.5/0.2 to 2.5
Stranded with Ferrules without Plastic Sleeve in mm²: 0.25 to 1.5
Stranded with Twin Ferrule with Plastic Sleeve in mm²: 0.5 to 4
Stripping Length in mm: 10
Thread: M4
Torque, Nm: 1.5 to 1.8



XBUT6PE-25, for pack of 25

All models shown larger than actual size.



XBAES35C-50PK for pack of 50



XBACUT10-10PK for pack of 10



XBATUT10-10PK for pack of 10



XBANS3575P

To Order *(Specify Model Number)*

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	DESCRIPTION
XBUT6PE-25PK	Green/yellow earth terminal block, pack of 25

***Ordering Example: XBUT6PE-25PK,** earth terminal blocks, **XBANS3575P,** DIN rail*

ACCESSORIES FOR XBUT6PE

MODEL NO.	DESCRIPTION
XBACUT10-10PK	Grey end cover, pack of 10
XBATUT10-10PK	Grey partition plate, pack of 10
XBAFBS28-10PK	Red 2-position plug-in bridge, pack of 10
XBATSPAI4-10PK	Test adaptor, pack of 10
XBMZB8-10PK	White blank marker strip, pack of 10
XBANS3575P	DIN rail 35 x 7.5 mm x 2 m slotted
XBANS3575U	DIN rail 35 x 7.5 mm x 2 m solid
XBANS3515P	DIN rail 35 x 15 mm x 2 m slotted
XBANS3515U	DIN rail 35 x 15 mm x 2 m solid
XBAES35C-50PK	One-screw mounted end stop, pack of 50
XBAES35T-50PK	Three-screw mounted end stop, pack of 50
XBAES35N-50PK	Snap-on end stop, pack of 50

SPECIFICATIONS FOR XBUT10PE

Terminal Width: 10.2 mm
Maximum Wire Size: 6 AWG/10 mm²
IEC 60 947-7-1 in A/AWG: 76/20-6
EN 50 0191 in A/AWG: 54/69/20-6
UL-cUL Ratings in AWG: 20-6

TECHNICAL DATA DIMENSIONS
Width/Length/Cover Width in mm: 10.2/46.9/2.2
Height for 35 x 7.5 / 35 x 15 in mm: 47.5/55.0

TECHNICAL DATA IN ACCORDANCE WITH IEC
Maximum Load Current in A/Cross-Section in mm²: 76/16
Rated Surge Voltage in kV/Contamination Class: 8/3
Surge Voltage Category/Insulating Material Group: III/I

CONNECTION CAPACITY
Stranded with Ferrule/with Ferrule and Plastic Sleeve in mm²: 0.5 to 10/0.5 to 10
MULTI-CONDUCTOR CONNECTION (SAME CROSS-SECTION)
Solid/Stranded in mm²: 0.5 to 4/0.5 to 4
Stranded with Ferrules without Plastic Sleeve in mm²: 0.5 to 2.5
Stranded with Twin Ferrule with Plastic Sleeve in mm²: 0.5 to 6
Stripping Length in mm: 10
Thread: M4
Torque Nm: 1.5 to 1.8



XBUT10PE-25PK, for pack of 25, shown larger than actual size.



XBAES35C-50PK for pack of 50



XBATUT10-10PK for pack of 10



XBACUT10-10PK for pack of 10

All models shown smaller than actual size.

To Order *(Specify Model Number)*

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	DESCRIPTION
XBUT10PE-25PK	Green/yellow earth terminal block, pack of 25

***Ordering Example: XBUT10PE-25PK,** earth terminal blocks, **XBANS3575P,** DIN rail,*

ACCESSORIES FOR XBUT10PE

MODEL NO.	DESCRIPTION
XBACUT10-10PK	Grey end cover, pack of 10
XBATUT10-10PK	Grey partition plate, pack of 10
XBAFBS210-10PK	Red 2-position plug-in bridge, pack of 10
XBARBUT10-10PK	Red reducing bridge, pack of 10
XBMZB10-10PK	White blank marker strip, pack of 10
XBANS3575P	DIN rail 35 x 7.5 mm x 2 m slotted
XBANS3575U	DIN rail 35 x 7.5 mm x 2 m solid
XBANS3515P	DIN rail 35 x 15 mm x 2 m slotted
XBANS3515U	DIN rail 35 x 15 mm x 2 m solid
XBAES35C-50PK	1-screw mounted end stop, pack of 50
XBAES35T-50PK	3-screw mounted end stop, pack of 50
XBAES35N-50PK	Snap-on end stop, pack of 50

SPECIFICATIONS FOR XBUT16PE

Terminal Width: 12 mm
Maximum Wire Size:
4 AWG/16 mm
IEC 60 947-7-1 in A/AWG: 101/15-4
UL-cUL Ratings in AWG: 16-4

TECHNICAL DATA DIMENSIONS

Width/Length/Cover Width in mm:
12/52.8/2.2
Height for 35 x 7.5/35 x 15 in mm:
54.8/62.3

TECHNICAL DATA IN ACCORDANCE WITH IEC


Maximum Load Current in A/Cross-Section in mm²: 101/25
Rated Surge Voltage in kV/Contamination Class: 8/3
Surge Voltage Category/Insulating Material Group: III/I

CONNECTION CAPACITY

Stranded with Ferrule/with Ferrule and Plastic Sleeve in mm²: 1.0 to 16/1.0 to 16

MULTI-CONDUCTOR CONNECTION (SAME CROSS-SECTION)

Solid/Stranded in mm²: 1.0 to 6/1.0 to 4
Stranded with Ferrules without Plastic Sleeve in mm²: 1.0 to 4
Stranded with Twin Ferrule with Plastic Sleeve in mm²: 0.75 to 10
Stripping Length in mm: 10
Thread: M5
Torque Nm: 2.5 to 3.0



XBUT16PE-25PK, for pack of 25, shown larger than actual size.



XBATUT10-10PK for pack of 10



XBANS3575P,



XBAES35C-50PK for pack of 50

All models shown smaller than actual size.

To Order *(Specify Model Number)*

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	DESCRIPTION
XBUT16PE-25PK	Green/yellow earth terminal block pack of 25

***Ordering Example: XBUT16PE-25PK,** earth terminal blocks, **XBANS3575P,** DIN rail*

ACCESSORIES FOR XBUT16PE

MODEL NO.	DESCRIPTION
XBACUT16-10PK	Grey end cover, pack of 10
XBATUT10-10PK	Grey partition plate, pack of 10
XBAFBS212-10PK	Red 2 position plug-In bridge, pack of 10
XBATSPAI4-10PK	Test adaptor, pack of 10
XBMZB10-10PK	White blank marker strip, pack of 10
XBANS3575P	DIN rail 35 x 7.5 mm x 2 m slotted
XBANS3575U	DIN rail 35 x 7.5 mm x 2 m solid
XBANS3515P	DIN rail 35 x 15 mm x 2 m slotted
XBANS3515U	DIN rail 35 x 15 mm x 2 m solid
XBAES35C-50PK	1-screw mounted end stop, pack of 50
XBAES35T-50PK	3-screw mounted end stop, pack of 50
XBAES35N-50PK	Snap-on end stop, pack of 50



XBUT35PE-25PK,
for pack of 25, shown
larger than actual size.

SPECIFICATIONS FOR XBUT35PE

Terminal Width: 16 mm
Maximum Wire Size: 0 AWG/35 mm²
IEC 60 947-7-1 in A/AWG: 125/15-0
UL-cUL Ratings in AWG: 14-1/0

TECHNICAL DATA DIMENSIONS

Width/Length/Cover Width in mm: 16.0/60.2
Height for 35 x 7.5/35 x 15 in mm: 65.7/73.2

TECHNICAL DATA IN ACCORDANCE WITH IEC

Maximum Load Current in A/ Cross-Section in mm²: 125/50
Rated Surge Voltage in kV/ Contamination Class: 8/3
Surge Voltage Category/Insulating Material Group: III/I

CONNECTION CAPACITY

Stranded with Ferrule/with Ferrule and Plastic Sleeve in mm²: 1.5 to 35/1.5 to 35

MULTI-CONDUCTOR CONNECTION (SAME CROSS-SECTION)

Solid/Stranded in mm²: 1.5 to 16/1.5 to 10
Stranded with Ferrules without Plastic Sleeve in mm²: 1.5 to 10
Stranded with Twin Ferrule with Plastic Sleeve in mm²: 1.5 to 10
Stripping Length in mm: 16
Thread: M6
Torque, Nm: 3.2 to 3.7



XBATUT10-10PK
for pack of 10



XBANS3575P



XBAES35C-50PK
for pack of 50

All models shown smaller than actual size.

To Order *(Specify Model Number)*

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	DESCRIPTION
XBUT35PE-25PK	Green/yellow earth terminal block, pack of 25

** No end covers required.*
***Ordering Example: XBUT35PE-25PK,** earth terminal blocks, **XBANS3575P,** DIN rail*

ACCESSORIES FOR XBUT35PE

MODEL NO.	DESCRIPTION
XBAFBS212-10PK	Red 2-position plug-in bridge, pack of 10
XBATUT10-10PK	Grey partition plate, pack of 10
XBACAT10-10PK	Grey end cover, pack of 10
XBATSPAI4-10PK	Test adaptor, pack of 10
XBANS3575P	DIN rail 35 x 7.5 mm x 2 m slotted
XBANS3575U	DIN rail 35 x 7.5 mm x 2 m solid
XBANS3515P	DIN rail 35 x 15 mm x 2 m slotted
XBANS3515U	DIN rail 35 x 15 mm x 2 m solid
XBAES35C-50PK	1-screw mounted end stop, pack of 50
XBAES35T-50PK	3-screw mounted end stop, pack of 50
XBAES35N-50PK	Snap-on end stop, pack of 50

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk

UNITED STATES
www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA
www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY
www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM
www. omega.co.uk
Manchester, England
0800-488-488

FRANCE
www.omega.fr
088-466-342

CZECH REPUBLIC
www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX
www.omega.nl
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters