


Part No. 1001388 / 1001430 5 GHz Single Band Stamped Metal Embedded Antenna 5 GHz

Supports: Wi-Fi applications, Agriculture, Automotive, WLAN, Smart Home, Healthcare, Digital Signage, MIMO Applications



5 GHz Single Band Stamped Metal Embedded Antenna

4900-5900 MHz

KEY BENEFITS

Stay-in-Tune

KYOCERA AVX's antenna technology provides superior RF field containment, resulting in less interaction with surrounding components.

Quicker Time-to-Market

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met.

Reliability

Products are the latest RoHS version compliant

APPLICATIONS

- Embedded Telematics design
 - Tracking
- Cellular, Headsets, •
- Healthcare M2M,
- Tablets Gateway,
- Industrial devices **Smart Grid**
- Access Point Handheld
 - OBD-II

KYOCERA AVX's 1001388 & 1001430 are the World's SMALLEST 5 GHz High Performance Stamped Metal antennas. These antennas are designed for WLAN MIMO enabled devices including routers, media players, and other mobile communications devices.

Real-World Performance and Implementation

KYOCERA AVX Stamped metal antennas are designed to produce optimal performance and 3D radiation patterns, offering increased coverage range without compromising on footprint dimensions.

Greater Flexibility

KYOCERA AVX's first-in-class technology enables the advance concept designs that deliver superior performance in reception critical applications.

Electrical Specifications

Typical performance on 75 x 75 mm PCB

Frequency (MHz)	5150 - 5825	5150 - 5825	
Part Number #	1001388	1001430	
Peak Gain	3.5 dBi	4.5 dBi	
Average Efficiency	73%	72%	
Return Loss in dB	< -10 dB		
Feed Point Impedance	50 ohms unbalanced		
Polarization	Linear		
Power Handling	2.0 Watt CW		

Mechanical Specifications & Ordering Part Number

Ordering Part #	1001388	1001430	
Dimensions (mm)	8.75 x 4.05 x 2.01	8.75 x 4.05 x 2.01	
Mounting Type	SMT		
Weight (grams)	0.025		
Packaging	Tape & Reel, 2K pcs/Reel		
Demo Board	1003666-01		





Antenna Dimensions (1001388)

Typical antenna dimensions (mm)


Part Number	A (mm)	A (mm) B (mm)	
1001388	8.75 ± 0.3	4.05 ± 0.3	2.01 ± 0.3








Top View



Height

Pin#	Description
1	Feed
2	Ground







Antenna Dimensions (1001430)

Typical antenna dimensions (mm)


Part Number	A (mm)	B (mm)	C (mm)
1001430	8.75 ± 0.3	4.05 ± 0.3	2.01 ± 0.3








Top View




Pin#	Description
1	Feed
2	Ground






Return Loss and Efficiency Plots (1001388)

Typical performance on 75 x 75 mm PCB






Antenna Radiation Patterns (1001388)


Typical performance on 75 x 75 mm PCB Measured @ 5220, 5780 MHz








© SŸUÔÒ܌ƌXÝ









Return Loss and Efficiency Plots (1001430)

Typical performance on 75 x 75 mm PCB








Antenna Radiation Patterns (1001430)


Typical performance on 75 x 75 mm PCB Measured @ 5220, 5780 MHz














Antenna Layout (1001388) Typical layout dimensions (mm) Antenna. Outline SOLDER MASK BOTTOM METAL PADS TOP METAL 344 000 SOLDER MASK 0.00 0.00 0.20 2.40 3.00 Pin #1 Pin Descriptions 4.90 6.20 Pin #2 Pin# Description 6.**4**0 Feed 2 Ground 50Ω SUBSTRATE Transmission line TOP METAL Matching Pi Network (Demo Board) Component Value **Tolerance** P1 DNI DNI 3.70 3.10 2.35 0.75 0.00 0.50 S1 0Ω N/A P2 DNI DNI *Actual matching values depend on 0.00 customer design 0.20 2.40 3.00 4.10 Antenna · 6.20 Outline 6.40 50ohm

3.00

BOTTOM METAL







Antenna Demo Board

Typical layout dimensions (mm)

Part Number	A (mm)	B (mm)	C1 (mm)	C2 (mm)
1003666-01	75.0	75.0	10.5	10.5

