

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product form : Mixture
Product name : HUMBROL ENAMEL RANGE
UFI : 2PRV-W05G-S00N-TQ7P
Product code : HUMB

1.2. Relevant identified uses of the substance or mixture and uses advised against**1.2.1. Relevant identified uses**

No additional information available

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Rustins Ltd
Waterloo road
UK- London
T +44(0)2084504666
rustins@rustins.co.uk - rustins.ltd

1.4. Emergency telephone number

Emergency number : +44 (0)208 450 4666

Country	Organisation/Company	Address	Emergency number	Comment
Ireland	National Poisons Information Centre Beaumont Hospital	PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2566 (Healthcare professionals- 24/7) +353 1 809 2166 (public, 8am - 10pm, 7/7)	
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	Only for healthcare professionals

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No. 1272/2008 [CLP]**

Flammable liquids, Category 3 H226
Specific target organ toxicity — Single exposure, Category 3, Narcosis H336
Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

Flammable liquid and vapour. May cause drowsiness or dizziness.

2.2. Label elements**Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

Hazard pictograms (CLP) :



HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Signal word (CLP)	: Warning
Contains	: Hydrocarbons, C9 - C11, n alkanes, isoalkanes, cyclics, <2% aromatics
Hazard statements (CLP)	: H226 - Flammable liquid and vapour. H336 - May cause drowsiness or dizziness.
Precautionary statements (CLP)	: P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P233 - Keep container tightly closed. P240 - Ground and bond container and receiving equipment. P241 - Use explosion-proof electrical/ventilating/lighting equipment. P261 - Avoid breathing dust/fume/gas/mist/vapours/spray. P271 - Use only outdoors or in a well-ventilated area. P280 - Wear eye protection, face protection. P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower. P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing. P312 - Call a POISON CENTER, doctor if you feel unwell. P370+P378 - In case of fire: Use media other than water to extinguish. P403+P233 - Store in a well-ventilated place. Keep container tightly closed. P403+P235 - Store in a well-ventilated place. Keep cool. P405 - Store locked up. P501 - Dispose of contents to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.
EUH-statements	: EUH208 - Contains COBALT 6 %(13586-82-8). May produce an allergic reaction.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Hydrocarbons, C9 - C11, n alkanes, isoalkanes, cyclics, <2% aromatics	CAS-No.: 64742-48-9 EC-No.: 919-857-5 EC Index-No.: 649-327-00-6 REACH-no: 01-2119463258-33	≥ 50	Flam. Liq. 3, H226 STOT SE 3, H336 Asp. Tox. 1, H304
COBALT 6 %	CAS-No.: 13586-82-8	≥ 0.1 – < 1	Eye Irrit. 2, H319 Skin Sens. 1, H317 Repr. 2, H361f

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Call a poison center or a doctor if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Rinse skin with water/shower. Take off immediately all contaminated clothing.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a poison center or a doctor if you feel unwell.

HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects : May cause drowsiness or dizziness.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

5.2. Special hazards arising from the substance or mixture

Fire hazard : Flammable liquid and vapour.
Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. No open flames, no sparks, and no smoking. Avoid breathing dust/fume/gas/mist/vapours/spray.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material. Notify authorities if product enters sewers or public waters.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Ground/bond container and receiving equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Flammable vapours may accumulate in the container. Use explosion-proof equipment. Wear personal protective equipment. Use only outdoors or in a well-ventilated area. Avoid breathing dust/fume/gas/mist/vapours/spray.

Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

7.2. Conditions for safe storage, including any incompatibilities

Technical measures	: Ground/bond container and receiving equipment.
Storage conditions	: Store in a well-ventilated place. Keep cool. Keep container tightly closed. Store locked up.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

Safety glasses

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing

Hand protection:

Protective gloves

8.2.2.3. Respiratory protection

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colour Range.
Odour	: Aromatic hydrocarbon.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: < 38 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 0.93 – 1.25
Solubility	: Water: Insoluble Acetone: Soluble Organic solvent: Soluble
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: 400 – 1800 mm ² /s
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Flammable liquid and vapour.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral)	: Not classified
-----------------------	------------------

HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: May cause drowsiness or dizziness.

Hydrocarbons, C9 - C11, n alkanes, isoalkanes, cyclics, <2% aromatics (64742-48-9)

STOT-single exposure	May cause drowsiness or dizziness.
----------------------	------------------------------------

STOT-repeated exposure : Not classified

Aspiration hazard : Not classified

HUMBROL ENAMEL RANGE

Viscosity, kinematic	400 – 1800 mm ² /s
----------------------	-------------------------------

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified
Not rapidly degradable	

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods	: Dispose of contents/container in accordance with licensed collector's sorting instructions.
Additional information	: Flammable vapours may accumulate in the container.






SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

HUMBROL ENAMEL RANGE

Safety Data Sheet


according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
UN 1263	UN 1263	UN 1263	UN 1263	UN 1263
14.2. UN proper shipping name				
PAINT / PAINT RELATED MATERIAL	PAINT RELATED MATERIAL	Paint related material	PAINT RELATED MATERIAL	PAINT RELATED MATERIAL
Transport document description				
UN 1263 PAINT / PAINT RELATED MATERIAL, 3, III, (D/E)	UN 1263 PAINT RELATED MATERIAL, 3, III	UN 1263 Paint related material, 3, III	UN 1263 PAINT RELATED MATERIAL, 3, III	UN 1263 PAINT RELATED MATERIAL, 3, III
14.3. Transport hazard class(es)				
3	3	3	3	3
				
14.4. Packing group				
III	III	III	III	III
14.5. Environmental hazards				
Dangerous for the environment: No	Dangerous for the environment: No Marine pollutant: No	Dangerous for the environment: No	Dangerous for the environment: No	Dangerous for the environment: No
No supplementary information available				

14.6. Special precautions for user

Overland transport

Classification code (ADR) : F1
 Special provisions (ADR) : 163, 367, 650
 Limited quantities (ADR) : 5L
 Excepted quantities (ADR) : E1
 Packing instructions (ADR) : P001, IBC03, LP01, R001
 Special packing provisions (ADR) : PP1
 Mixed packing provisions (ADR) : MP19
 Portable tank and bulk container instructions (ADR) : T2
 Portable tank and bulk container special provisions (ADR) : TP1, TP29
 Tank code (ADR) : LGBF
 Vehicle for tank carriage : FL
 Transport category (ADR) : 3
 Special provisions for carriage - Packages (ADR) : V12
 Special provisions for carriage - Operation (ADR) : S2
 Hazard identification number (Kemler No.) : 30
 Orange plates :



Tunnel restriction code (ADR) : D/E
 EAC code : •3Y

Transport by sea

Special provisions (IMDG) : 163, 223, 367, 955
 Limited quantities (IMDG) : 5 L

HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Excepted quantities (IMDG)	: E1
Packing instructions (IMDG)	: P001, LP01
Special packing provisions (IMDG)	: PP1
IBC packing instructions (IMDG)	: IBC03
Tank instructions (IMDG)	: T2
Tank special provisions (IMDG)	: TP1, TP29
EmS-No. (Fire)	: F-E
EmS-No. (Spillage)	: S-E
Stowage category (IMDG)	: A
Properties and observations (IMDG)	: Miscibility with water depends upon the composition.

Air transport

PCA Excepted quantities (IATA)	: E1
PCA Limited quantities (IATA)	: Y344
PCA limited quantity max net quantity (IATA)	: 10L
PCA packing instructions (IATA)	: 355
PCA max net quantity (IATA)	: 60L
CAO packing instructions (IATA)	: 366
CAO max net quantity (IATA)	: 220L
Special provisions (IATA)	: A3, A72, A192
ERG code (IATA)	: 3L

Inland waterway transport

Classification code (ADN)	: F1
Special provisions (ADN)	: 163, 367, 650
Limited quantities (ADN)	: 5 L
Excepted quantities (ADN)	: E1
Equipment required (ADN)	: PP, EX, A
Ventilation (ADN)	: VE01
Number of blue cones/lights (ADN)	: 0

Rail transport

Classification code (RID)	: F1
Special provisions (RID)	: 163, 367, 650
Limited quantities (RID)	: 5L
Excepted quantities (RID)	: E1
Packing instructions (RID)	: P001, IBC03, LP01, R001
Special packing provisions (RID)	: PP1
Mixed packing provisions (RID)	: MP19
Portable tank and bulk container instructions (RID)	: T2
Portable tank and bulk container special provisions (RID)	: TP1, TP29
Tank codes for RID tanks (RID)	: LGBF
Transport category (RID)	: 3
Special provisions for carriage – Packages (RID)	: W12
Colis express (express parcels) (RID)	: CE4
Hazard identification number (RID)	: 30

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Contains no substance subject to Regulation (EU) 2019/1148 of the European Parliament and of the Council of 20 June 2019 on the marketing and use of explosives precursors.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit

HUMBROL ENAMEL RANGE

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Abbreviations and acronyms:

VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:

Asp. Tox. 1	Aspiration hazard, Category 1
EUH208	Contains COBALT 6 %(13586-82-8). May produce an allergic reaction.
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H361f	Suspected of damaging fertility.
Repr. 2	Reproductive toxicity, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.