


Magnetic Cable Connector **multicomp** PRO

RoHS
Compliant



Male Magnetic Connector 7 Pin to Type A USB Cable



Dimensions : Millimetres

Specifications

Current Rate	: 2A
Contact Resistance	: 30mΩ
Operating temperature range	: -40°C to +80°C
PIN Quantity	: 7 pin
Pogo Pin Working Stroke	: 0.9mm & 0.75mm
Durability	: 10,000 cycles
Spring force	: 25gf to 30gf
Material	
Plunger	: Brass C3604, 3u" gold plating
Barrel	: Brass C3604, 3u" gold plating
Spring	: SUS304
Magnetic	: NdFeB, N52, Ni Plating
Injection Housing	: PA66 + 30%GF,UL94V-0
Over-moulding	: PVC
Cable	: PVC, 28AWG + 24AWG, UL

Features


- LED light change from red to green while power is full
- LED on both side of the magnetic connector

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro


multicomp PRO

Magnetic Cable Connector **multicomp** PRO

Female Magnetic Connector



Pin Assignment		
Pin	Signal	Description
Pin1	GND	Ground
Pin2	D-	Data-
Pin3	D+	Data+
Pin4	VCC	DC +5V
Pin5	D+	Data+
Pin6	D-	Data-
Pin7	GND	Ground



Specifications

Current Rate	: 2A
Contact Resistance	: 50mΩ
Operating temperature range	: -40°C to +85°C
Pin	: Brass, C3604, 3u" gold plating
Magnet	: NdFeB, N52
Housing	: PA46+30%GF

Dimensions : Millimetres

Part Number Table

Description	Part Number
Male Magnetic Connector 7 Pin to Type A USB Cable, 100mm, White	MP009325
Female Magnetic Connector, 7 Pin , White	MP009326
Connector Kit, 7 Pin Male Cable and Female Magnetic Connector, White	MP009327
Male Magnetic Connector 7 Pin to Type A USB Cable, 100mm, Black	MP009337
Female Magnetic Connector, 7 Pin , Black	MP009338
Connector Kit, 7 Pin Male Cable and Female Magnetic Connector, Black	MP009339

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO