

## Safety Data Sheet

According to Annex II to REACH - Regulation 2020/878 and to Annex II to UK REACH

### SECTION 1. Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name **SGM494**

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Silicone grease.**

#### 1.3. Details of the supplier of the safety data sheet

Name **CHT UK BRIDGWATER LTD**  
Full address **Amber House Showground Road**  
District and Country **TA6 6AJ Bridgwater (Somerset)**  
**England**  
Tel. **+44(0)1278411400**  
Fax **+44(0)1278411444**

e-mail address of the competent person responsible for the Safety Data Sheet **info.uk@cht.com**Supplier: **CHT Germany GmbH**  
**Bismarckstraße 102**  
**72072 Tübingen**  
**Germany**

#### 1.4. Emergency telephone number

For urgent inquiries refer to **Australia: 0418529118**  
**All other enquiries +44(0)1278 411400**

### SECTION 2. Hazards identification

#### 2.1. Classification of the substance or mixture

The product is not classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP). However, since the product contains hazardous substances in concentrations such as to be declared in section no. 3, it requires a safety data sheet with appropriate information, compliant to (EU) Regulation 2020/878.

Hazard classification and indication: --

#### 2.2. Label elements

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms: --

Signal words: --

Hazard statements:  
**EUH210** Safety data sheet available on request.

Precautionary statements: --

#### 2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage  $\geq$  than 0,1%.The product does not contain substances with endocrine disrupting properties in concentration  $\geq$  0.1%.

## SECTION 3. Composition/information on ingredients

### 3.1. Substances

Information not relevant

### 3.2. Mixtures

Contains:

Identification	x = Conc. %	Classification (EC) 1272/2008 (CLP)
<b>TRIMETHYL BORATE</b>		
CAS	121-43-7	0.2 ≤ x < 0.3
EC	204-468-9	<b>Flam. Liq. 3 H226, Repr. 1B H360, Acute Tox. 3 H301, Acute Tox. 3 H311, Acute Tox. 3 H331, STOT SE 1 H370, Eye Irrit. 2 H319</b>
INDEX	005-005-00-1	<b>STA Oral: 100 mg/kg, STA Dermal: 300 mg/kg, STA Inhalation vapours: 3 mg/l, STA Inhalation mists/powders: 0.501 mg/l</b>
REACH Reg.	01-2119906953-33	

The full wording of hazard (H) phrases is given in section 16 of the sheet.

## SECTION 4. First aid measures

### 4.1. Description of first aid measures

**EYES:** Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice.

**SKIN:** Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated clothing before using it again.

**INHALATION:** Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately.

**INGESTION:** Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

### 4.3. Indication of any immediate medical attention and special treatment needed

Information not available

## SECTION 5. Firefighting measures

### 5.1. Extinguishing media

#### SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

#### UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

### 5.2. Special hazards arising from the substance or mixture

#### HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Do not breathe combustion products.

### 5.3. Advice for firefighters

#### GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

#### SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

## SECTION 6. Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

### 6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

### 6.3. Methods and material for containment and cleaning up

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

### 6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

## SECTION 7. Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat, sparks and naked flames; do not smoke or use matches or lighters. Without adequate ventilation, vapours may accumulate at ground level and, if ignited, catch fire even at a distance, with the danger of backfire. Avoid bunching of electrostatic charges. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat. Avoid leakage of the product into the environment.

### 7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container. Store in a cool and well ventilated place, keep far away from sources of heat, naked flames and sparks and other sources of ignition. Keep containers away from any incompatible materials, see section 10 for details.

### 7.3. Specific end use(s)

Information not available

## SECTION 8. Exposure controls/personal protection

### 8.1. Control parameters

Information not available

### 8.2. Exposure controls

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration.

When choosing personal protective equipment, ask your chemical substance supplier for advice.

Personal protective equipment must be CE marked, showing that it complies with applicable standards.

#### HAND PROTECTION

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

#### SKIN PROTECTION

Wear category I professional long-sleeved overalls and safety footwear (see Regulation 2016/425 and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

#### EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

#### RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded for the substance or one of the substances present in the product, use a mask with a type A filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387). In the presence of

## SECTION 8. Exposure controls/personal protection ... / >>

gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. The protection provided by masks is in any case limited.

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

### ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

## SECTION 9. Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Properties	Value	Information
Appearance	paste	
Colour	colourless	
Odour	characteristic	
Melting point / freezing point	Not available	
Initial boiling point	Not available	
Flammability	Not available	
Lower explosive limit	Not available	
Upper explosive limit	Not available	
Flash point	> 150 °C	
Auto-ignition temperature	> 400 °C	
pH	Not available	
Kinematic viscosity	paste	
Solubility	immiscible with water	
Partition coefficient: n-octanol/water	Not available	
Vapour pressure	Not available	
Density and/or relative density	1	
Relative vapour density	Not available	
Particle characteristics	Not applicable	

### 9.2. Other information

#### 9.2.1. Information with regard to physical hazard classes

Information not available

#### 9.2.2. Other safety characteristics

VOC (Directive 2010/75/EU)	0.28 % - 2.79	g/litre
VOC (volatile carbon)	0.10 % - 0.96	g/litre

## SECTION 10. Stability and reactivity

### 10.1. Reactivity

There are no particular risks of reaction with other substances in normal conditions of use.

### 10.2. Chemical stability

The product is stable in normal conditions of use and storage.

### 10.3. Possibility of hazardous reactions

No hazardous reactions are foreseeable in normal conditions of use and storage.

### 10.4. Conditions to avoid

None in particular. However the usual precautions used for chemical products should be respected.

### 10.5. Incompatible materials

Information not available

**SECTION 10. Stability and reactivity** ... / >>**10.6. Hazardous decomposition products**

Information not available

**SECTION 11. Toxicological information**

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.  
It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

**11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008**Metabolism, toxicokinetics, mechanism of action and other information

Information not available

Information on likely routes of exposure

Information not available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

Interactive effects

Information not available

ACUTE TOXICITY

ATE (Inhalation - mists / powders) of the mixture:	> 5 mg/l
ATE (Inhalation - vapours) of the mixture:	> 20 mg/l
ATE (Inhalation - gas) of the mixture:	0.0 mg/l
ATE (Oral) of the mixture:	>2000 mg/kg
ATE (Dermal) of the mixture:	>2000 mg/kg

TRIMETHYL BORATE

LD50 (Dermal):	1845 mg/kg (Rabbit)
STA (Dermal):	300 mg/kg estimate from table 3.1.2 of Annex I of the CLP (figure used for calculation of the acute toxicity estimate of the mixture)
LD50 (Oral):	6140 mg/kg (Rat)
STA (Oral):	100 mg/kg estimate from table 3.1.2 of Annex I of the CLP (figure used for calculation of the acute toxicity estimate of the mixture)

SKIN CORROSION / IRRITATION

Does not meet the classification criteria for this hazard class

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

Does not meet the classification criteria for this hazard class

Respiratory sensitization

Information not available

Skin sensitization

Information not available

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

**SECTION 11. Toxicological information ... / >>**CARCINOGENICITY

Does not meet the classification criteria for this hazard class

REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class

Adverse effects on sexual function and fertility

Information not available

Adverse effects on development of the offspring

Information not available

Effects on or via lactation

Information not available

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class

Target organs

Information not available

Route of exposure

Information not available

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

Target organs

Information not available

Route of exposure

Information not available

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

**11.2. Information on other hazards**

Based on the available data, the product does not contain substances listed in the main European lists of potential or suspected endocrine disruptors with human health effects under evaluation.

**SECTION 12. Ecological information**

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

**12.1. Toxicity**

Information not available

**12.2. Persistence and degradability**

Information not available

**12.3. Bioaccumulative potential**

**SECTION 12. Ecological information** ... / >>

Information not available

**12.4. Mobility in soil**

Information not available

**12.5. Results of PBT and vPvB assessment**

On the basis of available data, the product does not contain any PBT or vPvB in percentage  $\geq$  than 0,1%.

**12.6. Endocrine disrupting properties**

Based on the available data, the product does not contain substances listed in the main European lists of potential or suspected endocrine disruptors with environmental effects under evaluation.

**12.7. Other adverse effects**

Information not available

**SECTION 13. Disposal considerations****13.1. Waste treatment methods**

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.  
Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.  
CONTAMINATED PACKAGING  
Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

**SECTION 14. Transport information**

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

**14.1. UN number or ID number**

Not applicable

**14.2. UN proper shipping name**

Not applicable

**14.3. Transport hazard class(es)**

Not applicable

**14.4. Packing group**

Not applicable

**14.5. Environmental hazards**

Not applicable

**14.6. Special precautions for user**

Not applicable

**14.7. Maritime transport in bulk according to IMO instruments**

Information not relevant





**SECTION 16. Other information ... / >>****H319**  
**EUH210**Causes serious eye irritation.  
Safety data sheet available on request.

## LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- ATE: Acute Toxicity Estimate
- CAS: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE: Identifier in ESIS (European archive of existing substances)
- CLP: Regulation (EC) 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: Regulation (EC) 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA: Time-weighted average exposure limit
- TWA STEL: Short-term exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

## GENERAL BIBLIOGRAPHY

1. Regulation (EC) 1907/2006 (REACH) of the European Parliament
2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
3. Regulation (EU) 2020/878 (II Annex of REACH Regulation)
4. Regulation (EC) 790/2009 (I Atp. CLP) of the European Parliament
5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament
11. Regulation (EU) 2016/918 (VIII Atp. CLP) of the European Parliament
12. Regulation (EU) 2016/1179 (IX Atp. CLP)
13. Regulation (EU) 2017/776 (X Atp. CLP)
14. Regulation (EU) 2018/669 (XI Atp. CLP)
15. Regulation (EU) 2019/521 (XII Atp. CLP)
16. Delegated Regulation (UE) 2018/1480 (XIII Atp. CLP)
17. Regulation (EU) 2019/1148
18. Delegated Regulation (UE) 2020/217 (XIV Atp. CLP)
19. Delegated Regulation (UE) 2020/1182 (XV Atp. CLP)
20. Delegated Regulation (UE) 2021/643 (XVI Atp. CLP)
21. Delegated Regulation (UE) 2021/849 (XVII Atp. CLP)

- The Merck Index. - 10th Edition
- Handling Chemical Safety
- INRS - Fiche Toxicologique (toxicological sheet)
- Patty - Industrial Hygiene and Toxicology
- N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
- IFA GESTIS website
- ECHA website
- Database of SDS models for chemicals - Ministry of Health and ISS (Istituto Superiore di Sanità) - Italy

**SECTION 16. Other information ... / >>****Note for users:**

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

**CALCULATION METHODS FOR CLASSIFICATION**

Chemical and physical hazards: Product classification derives from criteria established by the CLP Regulation, Annex I, Part 2. The data for evaluation of chemical-physical properties are reported in section 9.

Health hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 3, unless determined otherwise in Section 11.

Environmental hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 4, unless determined otherwise in Section 12.

**Changes to previous review:**

The following sections were modified:

02 / 03 / 08 / 09 / 11 / 12 / 15 / 16.