

# CREALITY

## MPN - CR-10 SMART PRO

### Description - CR-10 Smart Pro 3D Printer



Multi-modes Smart Networking

Dual-mode Leveling

Full-metal Dual-gear Direct Extruder



Crealty  
Cloud App

Remote controls integrate  
intelligence and Pleasure



Smart+Manual  
Leveling

Dual-mode leveling ensures  
great-looking first layer



AI HD  
Camera

Real-time HD and handheld  
smart controls



LED  
Lighting

Eco-friendly fill light helps  
save on energy



Full-metal Dual-gear  
Direct Extruder

Strong extrusion and high  
filament compatibility



Dual Z Axes+Dual  
Diagonal Drawbars

Stable operations and  
enhanced accuracy

## **Product Parameter**

**Modeling Technology:** FDM (Fused Deposition Modeling)

**Working Mode:** SD Card/Wi-Fi/Network

**Printing Size (mm):** 300\*300\*400

**Product Weight (kg):** 13.6

**Filament:** PLA/TPU/PETG/ABS/Wood/PA/carbon fiber

**Print Precision:**  $\pm 0.1\text{mm}$

**Layer Thickness:** 0.1mm-0.4mm

**Hotbed Temperature:**  $\leq 100^{\circ}\text{C}$

**Nozzle Temperature:**  $\leq 300^{\circ}\text{C}$

**Printing Speed:** 80-100mm/s

**Display:** 4.3-inch HD Full viewing angle screen

**Power Supply:** AC100-240V 24V

**Leveling method:** Smart + Manual Leveling

**File Format:** STL/OBJ/AMF