Make ideas real



## R&S®FPH/ZPH-K105 EMF MEASUREMENT APPLICATION

## For frequency selective measurements



The perfect choice for

Spectrum/health regulators

Communications operators

Field maintenance contractors

University/research organizations


Measurement functions	
Isotropic measurements	Yes, with R&S®TS-EMF antenna
Antenna factors	Preloaded and configurable using R&S®InstrumentView software
Exposure time setting	Yes
Exposure limit display	Percent (%), ratio (E <sup>2</sup> /L <sup>2</sup> ), permille (‰), parts per million (ppm)
Number of exposure limits	2

## Professional EMF measurements with a simple setup

- ► Easy configuration via R&S®InstrumentView (free software)
- Automatic measurement of one or more frequencies/channels
- ► ICNIRP limit lines are predefined and user-definable limit lines can also be used
- ► Easy analysis with chart display
- ► Easy report generation for documentation

Your benefit	Features			
Save time in the field	<ul> <li>▶ Use R&amp;S®InstrumentView to preconfigure measurements before heading to the field</li> <li>− Multiple frequencies</li> <li>− Multiple channels</li> <li>− Set exposure time in line with requirements</li> </ul>			
Easy and flexible analysis and documentation	<ul> <li>▶ Add ICNIRP, ITU or local limits before or after measurements</li> <li>▶ View results using the analyzer</li> <li>▶ View results using the R&amp;S®InstrumentView software</li> <li>▶ Generate customizable reports</li> </ul>			
One-stop shop for isotropic or directional antennas	<ul> <li>▶ Isotropic antenna: R&amp;S®TS-EMF</li> <li>▶ Directional antenna: R&amp;S®HE400 series, R&amp;S®HE800-PA</li> </ul>			

Customizable report generation						
	Overview	Setup	Export			
	Report Content					
	Average Results Max Results					
	RMS Results Min Results			Min Results		
	General Information Measurement Settings					
	<b>✓</b>	Data Table	s	<b>✓</b> Graphics		



Popular accessories	
Description	Item
Portable EMF measurement system, hardcase	R&S®TS-EMF
Isotropic antenna, 30 MHz to 3 GHz for R&S®TS-EMF	R&S®TSEMF-B1
Isotropic antenna, 700 MHz to 6 GHz for R&S®TS-EMF	R&S®TSEMF-B2
Isotropic antenna, 9 kHz to 200 MHz for R&S®TS-EMF	R&S®TSEMF-B3

## **Feature highlights**

- ▶ Perform automatic measurements with the EMF wizard
- ► Set exposure time, e.g. 6 minutes per frequency point
- ► Preview results from the analyzer
- ► View consolidated and individual measurement results
- ► View results as a bar chart
- ► Add exposure limits before or after measurements
- ► Generate customized reports

Rohde & Schwarz customer support (www.rohde-schwarz.com/support) Rohde & Schwarz training (www.training.rohde-schwarz.com)

R&S® is a registered trademark of Rohde & Schwarz GmbH & Co. KG | PD 3683.7319.32 | Version 01.00 | May 2022 (np)

Trade names are trademarks of the owners | R&S®FPH/ZPH-K105 EMF measurement application | Data without tolerance limits is not binding Subject to change | © 2022 Rohde & Schwarz GmbH & Co. KG | 81671 Munich, Germany