

#### 12500 TI Boulevard, MS 8640, Dallas, Texas 75243

# PCN#20220503001.1 Qualification of alternate Assembly sites for select Devices Change Notification / Sample Request

**Date:** May 04, 2022 **To:** Newark/Farnell PCN

#### Dear Customer:

This is an announcement of a change to a device that is currently offered by Texas Instruments. The details of this change are on the following pages.

Texas Instruments requires acknowledgement of receipt of this notification within **30** days of the date of this notice. Lack of acknowledgement of this notice within 30 days constitutes acceptance of the change. If additional data is required, requests must be received within **30** days of this notification.

The changes discussed within this PCN will not take effect any earlier than the proposed first ship date on Page 3 of this notification, unless customer agreement has been reached on an earlier implementation of the change.

This notice does not change the end-of-life status of any product. Should product affected be on a previously issued product withdrawal/discontinuance notice, this notification does not extend the life of that product or change the life time buy offering/discontinuance plan.

For questions regarding this notice or to provide acknowledgement of this PCN, you may contact your local Field Sales Representative or the PCN Team (<a href="mailto:PCN\_www\_admin\_team@list.ti.com">PCN\_www\_admin\_team@list.ti.com</a>). For sample requests or sample related questions, contact your local Field Sales Representative.

Sincerely,

PCN Team SC Business Services

#### 20220503001.1 Attachment: 1

#### **Products Affected:**

The devices listed on this page are a subset of the complete list of affected devices. According to our records, these are the devices that you have purchased within the past twenty four (24) months. The corresponding customer part number is also listed, if available.

**DEVICE** TPS62080DSGR TPS62092RGTT **CUSTOMER PART NUMBER** 

null null

Technical details of this Product Change follow on the next page(s).

<b>PCN Number:</b> 20220503001.1		3001.1				PCN D	ate:	May 04, 2022			
Title:	Title: Qualification alternate Assembly sites for select devices										
Customer Contact: PCN Manager Dept: Quality Services											
Proposed 1 <sup>st</sup> Ship Date: Aug 4		, 20			provided at le request						
Chang	Change Type:										
	sembly Sit	e				Design		Wafer Bump Site			
	sembly Pro	cess				Data Sheet		Wafer Bump Material			
$\boxtimes$ As	sembly Ma	terial	ls			Part number change		Wafe	r Bum	p Process	
Me	chanical S	pecif	ication	1		Test Site		Wafer Fab Site			
Packing/Shipping/Labeling				Test Process		Wafer Fab Materials					
								•	Wafe	r Fab I	Process
PCN Details											

### **Description of Change:**

Texas Instruments Incorporated is announcing the qualification of additional assembly sites for the devices in the product affected section below. Construction options are as follows:

QFN (VQFN/WQFN/WSON/VSON) Build sites							
Assembly Sites TIEMA, Clark-AT, CDAT, CARZ, UTL1, UTL3, TIM, AS							
	422198						
Mold Compound	SID#1801512111						
	4208625						
	4207123						
	SID#1400410104						
	SID#1400020112						
Mount Compound	SID#PZ0031						
Mount Compound	SID#435143						
	SID#443156						
	SID#1400410104						
	SID#PZ0035						
MSL	LEVEL1-260CG, LEVEL2-260CG, LEVEL3-260CG						
LeadFrame Finish	NiPdAu, NiPdAuAg, Sn						
Bond Wire	Cu, Au						

## **Reason for Change:**

Supply continuity

Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):

None

#### **Impact on Environmental Ratings**

Checked boxes indicate the status of environmental ratings following implementation of this change. If below boxes are checked, there are no changes to the associated environmental ratings.

RoHS	REACH	Green Status	IEC 62474
		🛛 No Change	No Change

#### Changes to product identification resulting from this PCN:

Assembly Site	Assembly Site Origin (22L)	Assembly Country Code (23L)	Assembly City
UTL1	NSE	THA	Bangkok
UTL3	UT3	THA	Bangpakong
CARZ	CSZ	CHN	Jiangsu
Clark	QAB	PHL	Angeles City, Pampanga
TIEM	CU6	MYS	Melaka
ASEN	ASN	CHN	Suzhou
TIM	MLA	THA	Kuala Lumpur
CDAT	CDA	CHN	Chengdu

Sample product shipping label (not actual product label)



MADE IN: Malaysia 2DC: 2Q: MSL 2 /260C/1 YEAR SEAL DT MSL 1 /235C/UNLIM 03/29/04

LBL: 5A (L)TO:3750



(1P) SN74LS07NSR (Q) 2000 (D) 0336 (31T)LOT: 3959047MLA (4W) TKY(1T) 7523483SI2

(2P) REV: (V) 0033317 (20L) CSO: SHE (21L) CCO:USA (22L) ASO: MLA (23L) ACO: MYS

#### **Product Affected:**

BQ24300DSGR	BQ24738HRGRR	LP5912-1.8DRVT	TPS54060DRCT
BQ24300DSGT	BQ24738HRGRT	LP5912-2.8DRVR	TPS54140ADRCR
BQ24313DSGR	BQ24738RGRR	LP5912-2.8DRVT	TPS54140ADRCT
BQ24313DSGT	BQ24738RGRT	LP5912-3.0DRVR	TPS54160ADRCR
BQ24314DSGR	BQ24770RUYR	LP5912-3.0DRVT	TPS54160ADRCT
BQ24314DSGT	BQ24770RUYT	SN1307054RGRR	TPS54240DRCR
BQ24315DSGR	BQ24773RUYR	SN1307054RGRT	TPS54240DRCT
BQ24315DSGT	BQ24773RUYT	SN2830RUYR	TPS54260DRCR
BQ24316DSGR	BQ24777ARUYR	SN2830RUYT	TPS54260DRCT
BQ24316DSGT	BQ24777ARUYT	SN2833RGRR	TPS62080DSGR
BQ24316DSGTG4	BQ24777RUYR	SN2833RGRT	TPS62080DSGT
BQ24715RGRR	BQ24777RUYT	TLV62080DSGR	TPS62090RGTR
BQ24715RGRT	BQ24781RUYR	TLV62080DSGT	TPS62090RGTT
BQ24717RGRR	BQ24781RUYT	TLV62084DSGR	TPS62091RGTR
BQ24717RGRT	BQ24786RUYR	TLV62084DSGT	TPS62091RGTT
BQ24725ARGRR	BQ24786RUYT	TLV62090RGTR	TPS62092RGTR
BQ24725ARGRT	HPA02196RGRR	TLV62090RGTT	TPS62092RGTT
BQ24728HRGRR	HPA02277RGRR	TLV62095RGTR	TPS62093RGTR
BQ24728HRGRT	LP5912-0.9DRVR	TLV62095RGTT	TPS62093RGTT

BQ24728RGRR	LP5912-0.9DRVT	TPS54040ADRCR	TPS62095RGTR
BQ24728RGRT	LP5912-1.1DRVR	TPS54040ADRCT	TPS62095RGTT
BQ24735FRGRR	LP5912-1.1DRVT	TPS54060ADRCR	TPS62130RGTR
BQ24735FRGRT	LP5912-1.5DRVR	TPS54060ADRCT	TPS62130RGTRF0
BQ24735RGRR	LP5912-1.5DRVT	TPS54060DRCR	TPS62130RGTT
BQ24735RGRT	LP5912-1.8DRVR		
	•		



TI Information
Selective Disclosure

## **QFN Qualification Report**

### Data Displayed as: Number of lots / Total sample size / Total failed

	Stress Test	Duration	CDAT TLV75733PDRV	CDAT TPS65992DADRJK	CDAT TLC6983RRF
TC	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	3/231/0	3/231/0
HAST	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0	3/231/0	3/231/0
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	3/231/0	3/231/0	3/231/0
UHAST /AC	Unbiased HAST, 130C/85%RH Or Autoclave 121C	96 hours	3/231/0	3/231/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	3/66/0	2/44/0	3/66/0 (ADS5296RGC)
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	3/228/0	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

	Stress Test	Duration	Clark-AT LP5912Q1.2DRVRQ1	Clark-AT ONET4291VARGP	Clark-AT SH6966ACC0RGC
TC	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	3/231/0	3/231/0
HAST	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0	3/231/0	3/231/0
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	3/231/0	3/231/0	3/231/0
UHAST /AC	Unbiased HAST, 130C/85%RH Or Autoclave 121C	96 hours	3/231/0	3/231/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	1/22/0	3/66/0	3/66/0
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	3/228/0	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

	Stress Test	Duration	ASEN CSD87502Q2	ASEN TPS65988CFRSH	ASEN TPS65126RSH
тс	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	3/231/0	1/77/0
HAST/ THB	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0	3/231/0	3/231/0
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	3/231/0 (TIOL1XXDMW)	3/231/0	2/122/0
UHAST /AC	Unbiased HAST, 130C/85%RH Or Autoclave 121C	96 hours	3/231/0	3/231/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	3/66/0 (CSD58911Q2)	3/66/0	1/22/0 (TPS65987DDJRSH)
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	3/228/0	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

	Stress Test	Duration	CARZ TLV75733PDRV	CARZ TPD5S330RJK	CARZ UCD9211RHA
TC	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	3/231/0	3/231/0
HAST	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0	3/231/0	3/231/0 (ADS8548SRGC)
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	3/231/0	3/231/0	3/231/0
UHAST /AC	Unbiased HAST, 130C/85%RH Or Autoclave 121C	96 hours	3/231/0	3/231/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	3/66/0 (DS90LV028AQDQF)	3/66/0	3/66/0
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	3/228/0	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

	Stress Test	Duration	UTL1 TPS717XXQDRVQ1	UTL1 LM73606QRNPQ1	UTL1 SH6966ADU0RGC
TC	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	2/154/0	3/231/0
HAST	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0	3/231/0	3/231/0
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	3/231/0	2/154/0	3/231/0
UHAST /AC	Unbiased HAST,130C/85%RH Or Autoclave 121C	96 hours	3/231/0	2/154/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	2/44/0	1/22/0	1/22/0
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	3/228/0	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

	Stress Test	Duration	UTL3 TCAN1042DRBQ1 TCAN1042HVDRBQ1 TCAN1051VDRBQ1	UTL3 TPS22990DML	UTL3 CC2541F256RHA
тс	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	3/231/0	3/231/0
HAST	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0	3/231/0	3/230/0
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	3/231/0	3/231/0	3/231/0
UHAST /AC	Unbiased HAST, 130C/85%RH Or Autoclave 121C	96 hours	3/231/0	3/231/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	1/22/0	3/66/0	3/66/0
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	Pass	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

	Stress Test	Duration	TIEM AT LDC1612QDNTRQ1	TIEM AT LDC1614QRGHRQ1	TIEM AT DS125BR401Q4DK
TC	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	3/231/0	3/231/0
HAST	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0	3/231/0	3/231/0 (DP83848LFQSQE)
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	1/77/0	1/45/0	3/231/0
UHAST /AC	Unbiased HAST, 130C/85%RH Or Autoclave 121C	96 hours	3/231/0	3/231/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	3/66/0	3/66/0 (LMK00334RTVTQ1)	1/22/0
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	3/228/0	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

	Stress Test	Duration	TIM PCOBTF100RLQ	TIM CDCM1804RGE	TIM MSP430FR5739IRHA
TC	Temperature Cycling -65/150C Or Temperature Cycling -55/125C	500 Cycles Or 700 Cycles	3/231/0	3/231/0	3/231/0
HAST	Biased HAST 130C/85%RH Or Biased HAST 110C/85%RH Or Temperature Humidity Bias, 85C/85%RH	96 hours Or 264 hours Or 1000 hours	3/231/0 (TPS62170DSG)	3/231/0	3/231/0
HTSL	High Temp. Storage Bake 150C Or High Temp. Storage Bake 170C	1000 hours Or 420 hours	3/135/0	3/231/0	3/231/0
UHAST /AC	Unbiased HAST, 130C/85%RH Or Autoclave 121C	96 hours	3/231/0	3/231/0	3/231/0
SD	Solderability	8 Hour Steam age or 155C Dry Bake	3/66/0 (TPS62170DSG)	3/66/0 (TSC2200RHB)	3/66/0 (SN75DP128ARTQ)
WBP	Wire Bond Pull	Wires	3/228/0	3/228/0	3/228/0
WBS	Wire Bond Shear	Wires	3/228/0	3/228/0	3/228/0
MQ	Manufacturability	-	Pass	Pass	Pass

TLV75733PDRV, LDC1614QRGHRQ1, LDC1612QDNTRQ1, CSD87502Q2, PCOBTF100RLQ, TCAN1042DRBQ1, TCAN1042HVDRBQ1, TCAN1051VDRBQ1, TPS717XXQDRVQ1, LP5912Q1.2DRVRQ1 are qualified at L1-260C MSL rating.

TPS22990DML, TPD5S330RJK, ONET4291VARGP, CDCM1804RGE, TPS65992DADRJK, DS125BR401Q4DK, TPS62170DSG, LM73606QRNPQ1, TIOL1XXDMW are qualified at L2-260C MSL rating.

ADS8548SRGC, SH6966ACCORGC, SH6966ADUORGC, MSP430FR5739IRHA, UCD9211RHA, TPS65126RSH, TPS65988CFRSH, CC2541F256RHA, TLC6983RRF, DP83848LFQSQE are qualified at L3-260C MSL rating

- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, and HTSL, as applicable
- The following are equivalent HTSL options based on activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

Green/Pb-free Status: Qualified Pb-Free (SMT) and Green

For questions regarding this notice, e-mails can be sent to the contacts shown below or your local Field Sales Representative.

Location	E-Mail		
WW Change Management Team	PCN www admin_team@list.ti.com		

#### **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI

intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<a href="www.ti.com/legal/termsofsale.html">www.ti.com/legal/termsofsale.html</a>) or other applicable terms available either on <a href="ti.com">ti.com</a> or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.