

## QSN 600 FH

### Torque screwdriver Type S

0,08-9 N·m

Code	ETIM
1400169	ECO02132 Drehmomentschlüssel
EAN	UNSPSC
4002805921098	27-11-27-20 Drehmomentwerkzeuge
Country of Origin	eCl@ss
Great Britain	21-04-02-22 Drehmomentschlüssel
Customs tariff no.	
82054000	



### Article description

- Use:
  - Controlled screw tightening in the range of 1,2 - 6 N·m
  - High-speed, controlled tightening enables serial production
  - Electrical and electronic hardware industry, instrument-making industry and industrial manufacturing or in quality control
- Features:
  - Adjustable torque screwdriver - with scale
  - With 1/4" female hexagon drive for use with 1/4" hexagon bits as per DIN 3126 - C 6.3
  - With adaptor also suitable for 1/4" square drive sockets as per DIN 3124
  - Working accuracy: +/- 6 % tolerance of set torque
  - Acc. to DIN EN ISO 6789, traceable to national standards
  - Precision radial ball clutch and cam design for controlled bi-directional tightening
  - Precision mechanism slips very noticeably when the pre-set value is achieved
  - Automatic resetting to the starting position
  - "Positive-Lock" system automatically fixes the set value preventing it from wrong setting
  - 4 models in the range 0,08 N·m to 9 N·m
  - Micrometre scale graduation: 1 cN·m resp. 0,1 N·m
  - EPA-conformant (Electrostatic Protected Area), for use in sensitive electrostatic applications
- Scope of delivery:
  - Torque wrench type QSN
  - 1/4" square/hexagon drive adaptor (No. 757-20)
  - Model No. QSN 600 FH / QSN 900 FH with additional T-handle for easier work
  - Test certificate acc. to DIN EN ISO 6789
  - Delivery in sturdy cardboard packaging

### Article information

Contents (Qty of pieces)	1 tlg.	Torque range (min./max.) [N·m]	1-6 N.m
Total length [mm]	196 mm	Epa-/Esd-Model	1
Torque (min.) [N·m]	1 N·m	Torque range (min./max.) [cN·m]	-
Torque (max.) [N·m]	6 N·m	Trigger mechanism	Friction clutch
Total height [mm]	38 mm	Precision +/-	+/- 6 %
Net weight [kg]	0,335 kg	Direction of tightening	Left and right
Drive connector square (male)	1/4"	Fixed setting	0
Drive connector square (male)	6,3 mm	Test certificate	DIN EN ISO 6789-2:2017
REACH registration available	0	T-handle available	0