



SAFETY DATA SHEET ENDURANCE 2 STROKE ENGINE OIL

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name ENDURANCE 2 STROKE ENGINE OIL

Product number MTS011

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Engine oil.

1.3. Details of the supplier of the safety data sheet

Supplier TETROSYL EUROPE
79 rue du chemin vert
59.273 Fretin
TEL: 03 20 28 06 30
qualite@tetrosyl-france.com

Manufacturer TETROSYL LIMITED
Bury
Lancashire
England
BL9 7NY
0161 764 5981
0161 797 5899
info@tetrosyl.com

1.4. Emergency telephone number

Emergency telephone +44 (0)161 764 5981

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (SI 2019 No. 720)

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Not Classified

2.2. Label elements

Hazard statements NC Not Classified

Precautionary statements P101 If medical advice is needed, have product container or label at hand.
P102 Keep out of reach of children.

Supplemental label information EUH066 Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

Not applicable.

ENDURANCE 2 STROKE ENGINE OIL

SECTION 3: Composition/information on ingredients

3.2. Mixtures

DISTILLATES, HYDROTREATED HEAVY PARAFFINIC <3% DMSO EXTRACT (IP 346)		30-<60%
CAS number: 64742-54-7	EC number: 265-157-1	UK REACH registration number: UK-01-1759217276-5-0000

Classification

Asp. Tox. 1 - H304

DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSENE - UNSPECIFIED		10-<30%
CAS number: —	EC number: 926-141-6	
Repeated exposure may cause skin dryness or cracking.		

Classification

Asp. Tox. 1 - H304

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Get medical attention if any discomfort continues. Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
Inhalation	If spray/mist has been inhaled, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
Ingestion	Contact physician if larger quantity has been consumed. Rinse mouth thoroughly with water.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention if irritation persists after washing.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Do not rub eye.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure. Effects may be delayed. Keep affected person under observation.
Inhalation	May cause an asthma-like shortness of breath. Vapours may cause headache, fatigue, dizziness and nausea.
Ingestion	May cause discomfort if swallowed. May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.
Skin contact	Prolonged or repeated contact with skin may cause irritation, redness and dermatitis. Allergic rash.
Eye contact	May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations. If in doubt, get medical attention promptly.
-----------------------------	---

ENDURANCE 2 STROKE ENGINE OIL

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with the following media: Foam, carbon dioxide or dry powder. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards Fire creates: Carbon monoxide (CO). Carbon dioxide (CO₂). No unusual fire or explosion hazards noted.

Hazardous combustion products Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours. Oxides of carbon.

5.3. Advice for firefighters

Special protective equipment for firefighters Leave danger zone immediately.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Follow precautions for safe handling described in this safety data sheet. Avoid inhalation of vapours. Avoid contact with eyes and prolonged skin contact. Provide adequate ventilation. In case of spills, beware of slippery floors and surfaces.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground. Collect and dispose of spillage as indicated in Section 13.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Stop leak if possible without risk. Eliminate all sources of ignition. No smoking, sparks, flames or other sources of ignition near spillage. Provide adequate ventilation. Provide adequate ventilation. Contain spillage with sand, earth or other suitable non-combustible material. Avoid the spillage or runoff entering drains, sewers or watercourses. Absorb spillage with non-combustible, absorbent material. Collect and place in suitable waste disposal containers and seal securely.

6.4. Reference to other sections

Reference to other sections Wear protective clothing as described in Section 8 of this safety data sheet. Collect and dispose of spillage as indicated in Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Do not eat, drink or smoke when using the product. Avoid the formation of mists. Provide adequate ventilation. Avoid contact with skin and eyes. Always remove oil with soap and water or skin cleaning agent, never use organic solvents. Do not use oil-contaminated clothing or shoes, and do not put rags moistened with oil into pockets.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Keep containers upright. Store in tightly-closed, original container.

7.3. Specific end use(s)

ENDURANCE 2 STROKE ENGINE OIL

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

No exposure limits known for ingredient(s).

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Avoid inhalation of vapours. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. It is recommended that gloves are made of the following material: Nitrile rubber. It should be noted that liquid may penetrate the gloves. Frequent changes are recommended.

Other skin and body protection

Wear suitable protective clothing as protection against splashing or contamination.

Hygiene measures

Wash contaminated clothing before reuse. Wash promptly with soap and water if skin becomes contaminated.

Respiratory protection

No specific recommendations.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Clear liquid.
Colour	Dark. Blue.
Odour	Oil-like.
Odour threshold	Not determined.
pH	Not determined.
Melting point	Not determined.
Initial boiling point and range	192°C @ 1013 hPa
Flash point	77°C
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.
Vapour pressure	Not determined.
Vapour density	Scientifically unjustified.
Relative density	0.870 g/cm ³ @ 20°C

ENDURANCE 2 STROKE ENGINE OIL

Solubility(ies)	Insoluble in water.
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	45 mm ² /s @ 40°C 8.00 mm ² /s @ 100°C
Oxidising properties	Not determined.

9.2. Other information

Other information	None.
--------------------------	-------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
-------------------	---

10.2. Chemical stability

Stability	No particular stability concerns.
------------------	-----------------------------------

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not applicable.
---	-----------------

10.4. Conditions to avoid

Conditions to avoid	Avoid heat, flames and other sources of ignition.
----------------------------	---

10.5. Incompatible materials

Materials to avoid	Strong oxidising agents.
---------------------------	--------------------------

10.6. Hazardous decomposition products

Hazardous decomposition products	Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.
---	--

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation	No specific health hazards known.
Ingestion	May cause discomfort if swallowed.
Skin contact	Prolonged and frequent contact may cause redness and irritation.
Eye contact	May cause temporary eye irritation.

SECTION 12: Ecological information

Ecotoxicity	Not regarded as dangerous for the environment.
--------------------	--

12.1. Toxicity

Acute aquatic toxicity

Acute toxicity - fish

LC₅₀, 96 hours: 2200 (DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSENE – UNSPECIFIED) mg/l, Fish

ENDURANCE 2 STROKE ENGINE OIL

Acute toxicity - aquatic invertebrates Not determined.

Acute toxicity - aquatic plants Not determined.

12.2. Persistence and degradability

Persistence and degradability No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not determined.

12.4. Mobility in soil

Mobility The product is insoluble in water.

Adsorption/desorption coefficient Not available.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current UK criteria.

12.6. Other adverse effects

Other adverse effects Not available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Waste is classified as hazardous waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Disposal methods Confirm disposal procedures with environmental engineer and local regulations.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant
No.

14.6. Special precautions for user

Not applicable.

ENDURANCE 2 STROKE ENGINE OIL

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments	NOTE: Lines within the margin indicate significant changes from the previous revision.
Issued by	Regulatory Department
Revision date	25/01/2022
Revision	15
Supersedes date	04/02/2021
SDS status	Approved.
Hazard statements in full	H304 May be fatal if swallowed and enters airways.