

VQJ69595B

"Trigger" 4-Port Under-Dash Antenna Cellular/Wi-Fi/GNSS

The innovative *Trigger* family of multiport/multiband antennas provide an excellent solution for transportation, aftermarket fleet, public safety and IoT applications. The incorporation of both vertically and horizontally polarized cellular radiating elements has shown to provide improved signal received power and signal received quality. These parameters are critical for high density urban environments as well as long distance remote rural conditions. This translates to more consistent connectivity and data throughput for your mobile data applications.

The VQJ series Trigger antenna is configured for two-port operation over the 3G/4G/5G/ISM/CBRS bands and one-port operation over the low//high frequency Wi-Fi bands. An additional fourth port provides an active antenna for enabling GNSS global navigation services.

FEATURES AND BENEFITS

- Unique V-Pol / H-Pol cellular elements ensure highest signal retention and data throughput
- Ideal for vehicle under-dash locations mounted to
- ventilation ducting
- Dual axis bonding via VHB tape provides a rugged mount to jarring vehicle movements

APPLICATIONS

- Trucking
- FirstNet/Public safety
- Transportation/transit

- Aftermarket fleet
- Rugged LTE gateways

ELECTRICAL SPECIFICATIONS				
Antenna Model	VQJ69595B-92VC1 / VQJ69595B-92FAK			
Number of Ports	4			
Port Configuration	LTE (Cell) 2x		Wi-Fi 1x	
Operating Frequency (MHz)	698-960/1710-2620	2620-2700	2400-2500	4900-5900
Peak Gain - (dBi)	5.0		5.0	
Efficiency - Typical (%)	50		40	
VSWR - Max	<3.1:1		<3.1:1	
Nominal Impedance (Ohms)	50			
Max Power - Ambient 25°C (W)	5			

MECHANICAL SPECIFICATIONS			
Dimensions - L x W x H - mm (inches)	132.3 x 59.3 x 14.6 (5.21 x 2.33 x 0.57)		
Weight -g (lbs.)	206 (0.45)		
Cable Type	LMR100 (or equivalent) - Wi-Fi and LTE; RG174 - GNSS		
Mounting Tape (separate pack)	Mounting tape - 2x double-sided foam tape (75 x 40 x 1.6 mm thick)		
3M VHB 5962P or equivalent	PC, UL94 - VO Rating, UV Stable		
Radome Material	PC		
Radome Color	Black		
Radome Texture	MT11010		

ENVIRONMENTAL SPECIFICATIONS			
Operating Environment	Vehicular under dash; outdoor rated		
Operating Temperature - °C (°F)	-40 to +85°C (-40 to +185°F)		
Storage Temperature - °C (°F)	-40 to +85°C (-40 to +185°F)		
Ingress Protection Rating	IP67		
Material Substance Compliance	RoHS		

GNSS ANTENNA SPECIFICATIONS					
Frequency of Operation (MHz, reference)	1559 - 1606				
Band	BEIDOU GPS GLONASS				
Frequency Band (MHz)	1561.098 ±2.046	1575.42 ±1.023	1602 ±5		
GNSS Passive Gain (dBic)	5				
GNSS Active Gain (dBic)	32				
LNA Gain, Typ. (dB)	28 ±3				
DC Voltage, (V)	2.5 - 7				
Noise Figure; Max (dB)	≤ 2.5				
Polarization	RHCP				
Nominal Impedance (Ohms)	50				
Current Consumption, Max @ room temp mA	8.5 ±3 (at 3.0 V)				
Out-of-band Signal Rejection Min (dB)	698-960 MHz > 80	1428-1511 MHz > 80	1710-2700 MHz > 80	4900-5800 MHz > 70	
Input Max Power (dBm)	-10				

CONFIGURATION


DADT NUMBER	CABLE LENGTH	CONNECTORS			COLOR
PART NUMBER	PIGTAIL	LTE/CELL	WI-FI	GNSS	COLOR
VQJ69595B-92VC1	914 mm (3 ft.)	SMA-male (2x)	RP SMA-male	SMA-male	Black
VQJ69595B-92FAK	914 mm (3 ft.)	Fakra Type D Jack (Purple) (2x)	Fakra Type I Jack (Beige)	Fakra Type C Jack (Blue)	Black


PACKAGING INFORMATION


PACKAGE DIMENSIONS	MASTER CARTON	AIR PALLET	OCEAN PALLET
Number of Antennas	40	720	880
Height - cm (in.)	15.6 (6.1)	154.8 (60.9)	186.0 (73.2)
Length - cm (in.)	80 (31.5)	120 (47.2)	120 (47.2)
Width - cm (in.)	60 (23.6)	80 (31.5)	80 (31.5)
Shipping Weight - kg (lb.)	12.5 (27.6)	245 (540.1)	295 (650.4)

MECHANICAL DRAWING

VQJ69595B-92VC1










DIMENSION SHOWN NOT INCLUDE MOUNTING TAPE

VQJ69595B-92FAK









DIMENSION SHOWN NOT INCLUDE MOUNTING TAPE

MECHANICAL DRAWING

VQJ69595B-92VC1


VQJ69595B-92FAK






VSWR

LTE 2 (Horizontal)




VSWR

LTE 1 (Vertical




Wi-Fi




ISOLATION


LTE 2 - LTE 1




LTE 2 - Wi-Fi




EFFICIENCY






MEASUREMENT COORDINATION SYSTEM (GAIN PLOT ORIENTATION)





RADIATION PATTERNS - LTE ANTENNAS


698 MHz




746 MHz










806 MHz









860 MHz










____ LTE2 ____ LTE1

RADIATION PATTERNS - LTE ANTENNAS


960 MHz










1710 MHz









1880 MHz










____ LTE2 ____ LTE1

RADIATION PATTERNS - LTE ANTENNAS


2305 MHz










2412 MHz









2600 MHz










____ LTE 2 ____ LTE 1

RADIATION PATTERNS - WI-FI ANTENNAS


2450 MHz










4900 MHz









5550 MHz










- Wi-Fi

5875 MHz









--- Wi-Fi


RADIATION PATTERNS - GNSS ANTENNAS


1561.098 MHz






1575.42 MHz






Wi-Fi

1602 MHz





- Wi-Fi

TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 +44 (0) 800-267666 UK: +33 (0) 1-3420-8686 France: Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase..

©2021 TE Connectivity. All Rights Reserved.

11/21 Original

