



#### www.lemo.com

## **SUMMARY**

#### # Wires

Low voltage 4



Image is for illustrative purpose only

Series 0B

**Termination type** Female solder

IP rating 50

AWG wire size 30.00 - 22.00

Cable Ø 0.00 - 0.00 mm

**Status** active

Matching parts FGG.0B.304.CLAD56

## **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

## **Mechanics**

Shell Style/Model EE\*: Fixed receptacle, nut fixing (back panel mounting)

**Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Weight 5.04 g

#### **Performance**

Configuration 0B.304 : 4 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 7 Amps

## **Specifications**

Contact Type: Solder

Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.8 mm (0.031in)

Max. Solid Conductor: 0.34 mm<sup>2</sup> (AWG 22) Max. Stranded Conductor: 0.34 mm<sup>2</sup> (AWG 22)

R (max): 6.1 mOhm

Vtest (contact-contact): 850 V (AC), 1200 V (DC) Vtest (contact-shell): 700 V (AC), 1000 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## **Others**


Endurance (Shell): 5000


Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

# **DRAWINGS**







## **Dimensions**

	А	В	E	L	М	N	Р	<b>S</b> 1	S2	е
mm.	12	12.5	2.4	20.7	2.5	19.1	6.3	8.2	9	M9x0.6
in.	0,47	0,49	0,09	0,81	0,10	0,75	0,25	0,32	0,35	

# **RECOMMENDED BY LEMO**

## Tools

Spanner wrench: Socket for torque wrench DCM.0S.M09.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cables

CMN.04.T22.047QGC	TPR	Grey	
CMN.04.T22.048QGZE	TPR (medical)	Grey	>
CMN.04.T28.031PGCE	PVC	GREY	<b>&gt;</b>
CMN.04.T28.031PGZE		Grey	>€
CMN.04.T28.031PNCE	PVC	Black	<b>→</b>
CMN.04.T28.031PNZE			>€
CMN.04.T28.031QGC	TPR	Grey	
140240	PVC	Black	
140250	PVC	Grey	<b>&gt;</b>
40080	PVC	Black	
40086	PVC	Blue	
40140	PVC	Black	-5- <u>-</u>
40240	PTFE	White	<b>≥</b>
40260	PVC	Black	
4041	PVC	Grey	€
4050	PVC	Black	<b>→</b>
4080	PVC	Grey	
417920	PVC	Grey	
4220	PVC	Black	-
4221	PVC	Black	-
4260	PTFE	White	>=====================================
4280	PVC	Black	
80080	PVC	Grey	
80082	PVC	Red	
80084	PVC	Black	
CTR.75.030.121870G	PVC	Grey	<b>&gt;</b>

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.