Inline Coupler Cat6





Description

A female to female Cat6 coupler for a RJ45 lead. The Cat.6 performance is in compliance with the ANSI/TIN/EIA 568 C standard.

Specifications

In Line Connector A : RJ45
In Line Connector B : RJ45
Convert From Gender : Receptacle
Convert From Positions : 1 Ways
Convert To Gender : Receptacle
Convert To Positions : 1 Ways
Plastic Housing : ABS

RJ45 Contact Material and Finished : Phosphor Bronze with Nickel plated

Contact Area: Gold plated

Insertion Force : 900 gms for 8 contacts

Retention Strength : 7.7kgs between Jack and Plug


Operation Temperature : -20°C to +68°C


Durability

Jack : 750 cycles Plug-Jack mating and unmating test

Diagram







Part Number Table

| Description | Part Number |
|--|-------------|
| In-Line Adapter, RJ45, RJ45, RJ45, Receptacle, 1 Way | PSG91587 |

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

