


# LABFACILITY

## TEMPERATURE & PROCESS TECHNOLOGY

### Thermocouple Cable PFA Insulated Twin Twisted Pair



- ◆ PFA Teflon® twin twisted pair for extending or making simple thermocouples
- ◆ Single pair of PFA insulated conductors twisted together
- ◆ Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam & pressure etc.
- ◆ Thermocouple types K & T
- ◆ 50 & 100 metre reel lengths
- ◆ Tolerance Class 1 for optimum accuracy
- ◆ Insulation rating -75°C to 260°C
- ◆ Colour coded to IEC-584-3

T/C Type	Conductors	Cores	Reel Length	Manufacturers Part No.	Farnell Order Code
K	1/0.2mm	+Green/-White	5 metres	WK-203-D-5m	XF-1788-FAR
K	1/0.2mm	+Green/-White	10 metres	WK-203-D-10M	XF-1769-FAR
K	1/0.2mm	+Green/-White	25 metres	WK-203-D-25M	XF-1772-FAR
K	1/0.2mm	+Green/-White	50 metres	WK-203-D-50M	208-1277
K	1/0.2mm	+Green/-White	100 metres	WK-203-D-100M	208-1278
T	1/0.2mm	+Brown/-White	10 metres	WT-304-D-10M	XF-1789-FAR
T	1/0.2mm	+Brown/-White	25 metres	WT-304-D-25M	XF-1974-FAR
T	1/0.2mm	+Brown/-White	50 metres	WT-304-D-50M	208-1273
T	1/0.2mm	+Brown/-White	100 metres	WT-304-D-100M	208-1274
K	1/0.315mm	+Green/-White	50 metres	WK-204-D-50M	208-1279
T	1/0.315mm	+Brown/-White	50 metres	WT-306-D-50M	208-1275
K	7/0.2mm	+Green/-White	50 metres	XS-752-D-10M	XF-1787-FAR
K	7/0.2mm	+Green/-White	25 metres	XS-752-D-25M	XF-1773-FAR
K	7/0.2mm	+Green/-White	50 metres	XS-752-D-50M	208-1280
T	7/0.2mm	+Brown/-White	50 metres	XF-566-FAR	208-1276

#### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

#### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

#### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com