

# Features

## Power Module

- Wide input range (4.7 - 18VDC)
- Low profile 2mm
- Small footprint 3x2.8mm
- Adjustable output 0.8 to 5.4VDC
- Over 100°C ambient temperature at full load
- Integrated solution

### Description

The RPL-3.0A is a buck converter with an integrated inductor in a tiny 3mm x 2.8mm x 2mm thermally-enhanced QFN package. The input range is from 4.7 to 18VDC, allowing 5V and 12V supply rails to be used. The output voltage can be set with two resistors in the range from 0.8V up to 5.4VDC. The output current is up to 3A and is fully protected against continuous short-circuits, output overcurrent, or over-temperature faults. Its high current and small size as well as its high ambient temperature rating make the RPL-3.0A ideal for imaging systems, distributed power architectures, and portable equipment in telecom as well as in industrial applications where both thermal performance and board space are critical.

### Selection Guide

Part Number	Input Voltage Range [VDC]	Output Voltage Range [VDC]	Output Current max. [mA]	Efficiency <sup>(1)</sup> typ. [%]
RPL-3.0A	4.7 - 18	0.8 - 5.4	3000	88

#### Notes:

Note1: Efficiency tested at  $V_{IN} = 4.7\text{VDC}$ , full load, and  $V_{OUT} = 3.3\text{VDC}$

## RPL-3.0A

### 3 Amp 8-Pin QFN Package



### Model Numbering

RPL-3.0A-

Output Current \_\_\_\_\_ Packaging <sup>(2)</sup>

#### Notes:

Note2: add suffix "-R" for tape and reel packaging  
add suffix "-CT" for cut tape packaging (refer to "**PACKAGING INFORMATION**")

### Specifications

ABSOLUTE MAX RATINGS (exceeding these ratings may damage the device)				
Parameter	Symbol	Min.	Typ.	Max.
Absolute Maximum Voltage	$V_{IN}$ to GND	-0.3VDC		19VDC
	CTRL, SS, PG <sup>(3)</sup>	-0.3VDC		19.3VDC
	FB, $V_{OUT}$	-0.3VDC		6VDC
Maximum continuous power losses <sup>(4)</sup>	$T_{AMB} = 25^{\circ}\text{C}$			3.33W
Junction Temperature	$T_J$	-40°C		+125°C
Lead Temperature		10 seconds max		+260°C

**Notes:**

Note3: For CTRL absolute max ratings, please refer to "**CTRL Operating CONDITIONS**"


Note4: Exceeding maximum allowable power dissipation causes device to enter thermal shutdown which protects device from permanent damage. Refer to "**CHARACTERISTIC CURVES**"

## Specifications

OPERATING CONDITIONS ( $V_{IN} = 12VDC$ , $V_{OUT} = 3.3VDC$ , $I_{OUT} = 3A$ , unless otherwise noted, typical values are at $T_{AMB} = +25^{\circ}C$ )					
Parameter	Symbol	Condition	Min.	Typ.	Max.
Input Voltage Range	$V_{IN}$	refer to "SAFE OPERATING AREA"	4.7VDC		18VDC
Under Voltage Lockout UVLO		DC-DC ON	4.3VDC	4.5VDC	4.7VDC
		DC-DC OFF	3.9VDC	4.1VDC	4.3VDC
		hysteresis		400mV	
Output Voltage Range	$V_{OUT}$	refer to "OUTPUT VOLTAGE SETTING"	0.8VDC		5.4VDC
Output Current Range	$I_{OUT}$		0A		3A
Standby current	$I_{IN}$	$V_{CTRL} = \text{low}$ (DC-DC OFF)		2 $\mu$ A	5 $\mu$ A
Quiescent current	$I_Q$	$V_{CTRL} = \text{high}$ (DC-DC ON)	18mA	22mA	27mA
Switching frequency	$f_{SW}$		1.7MHz	2MHz	2.3MHz
Feedback voltage	$V_{FB}$		785mV	800mV	815mV
Output load regulation			refer to "Characteristic Curves"		
Maximum Duty Cycle			85%		
Minimum On Time				50ns	
Soft Start			External programmable soft start time limits the inrush current		
Rise time		$V_{OUT}$ from 10% to 90%; $C_{SS} = \text{open}$		370 $\mu$ s	500 $\mu$ s

### Typical Application

$V_{IN} = 12VDC$ ,  $V_{OUT} = 3.3VDC$ ,  $I_{OUT} = 3A$ , soft start time = 9.64ms




### Notes:

Note5: The RPL-3.0A requires a 10 $\mu$ F MLCC input capacitor as close as possible to  $V_{IN}$  and GND pin and 2x 22 $\mu$ F output capacitors to handle noise problems.

Note6: Transient load reaction time can be improved by adding a feedforward capacitor,  $C_{FF}$  in parallel with  $R_1$  but it is not required for normal operation.

### SAFE OPERATING AREA



## Specifications

### INPUT AND OUTPUT CAPACITOR

#### Input Capacitor

The RPL-3.0A requires a 10 $\mu$ F MLCC input capacitor for normal operation. To reduce back ripple current increase capacitance to 20 $\mu$ F MLCC.

#### Output Capacitor


The RPL-3.0A requires MLCC output capacitors for normal operation (see table). Transient load reaction time can be improved by adding a feed-forward capacitor,  $C_{FF}$  across  $R_1$ , but it is not required for normal operation.

Output capacitance		
$V_{OUTset}$ [VDC]	$C_{OUT}$ min. [ $\mu$ F]	$C_{OUT}$ max. [ $\mu$ F]
0.8	<0.9	300
0.9		400
1.8		600
3.3		1100

### OUTPUT VOLTAGE SETTING

A resistor divider connected to the FB pin (pin 6) sets the output voltage of the RPL-3.0A. The output voltage adjustment range is from 0.8VDC to 5.4VDC. The schematic below shows the feedback resistor connections for setting the output voltage. The recommended value of  $R_1$  is 49k9 $\Omega$ . Use the equation to calculate the value for  $R_2$ . The table below lists the  $R_2$  resistor values according to standard E96 values; therefore, the specified voltage may slightly vary.

#### Feedback Network



Practical example with  $V_{OUTset} = 1.8$ VDC

$$R_2 = \frac{0.8V}{(1.8V - 0.8V)} \times 49.9k\Omega = 39.92k\Omega$$


Table below lists recommended resistor values for common  $V_{OUT}$ :

$V_{OUTset}$ [VDC]	$R_1$ [ $\Omega$ ]	$R_2$ [ $\Omega$ ]	$C_{FF}$ [pF]*	$C_{OUT}$ [ $\mu$ F]
1.2	49k9	100k	optional *	2x 22
1.5		57k6		2x 22
1.8		40k2		2x 22
2.5		23k2		2x 22
3.3		15k8		2x 22
5		19k1		2x 22

\*to stabilize the system and optimize the load transient response, place a feed-forward capacitor ( $C_{FF}$ ) in parallel with  $R_1$ .

### SOFT START SETTING

The soft-start time can be programmed via the SS pin by connecting one capacitor between the SS pin and the GND pin. If this pin is floating, soft-start time is start time is approximately 370 $\mu$ s. The typical value of the SS charging current  $I_{SS}$  is 1.7 $\mu$ A. To guarantee the programmable soft-start time is not too short when using smaller SS capacitor. Refer to below recommended  $C_{SS}$  table:



$C_{SS}$ capacitor [ $n$ F]	Soft start time from 10% to 90% $V_{OUTset}$ [ms]
open	0.37
3.3	1.36
22	9.64
47	19.5
100	43.1
470	196
1000	482

## Specifications

CTRL OPERATING CONDITIONS ( $V_{IN} = 12VDC$ , $V_{OUT} = 3.3VDC$ , $I_{OUT} = 3A$ , unless otherwise noted, typical values are at $T_{AMB} = +25^\circ C$ )					
Parameter	Symbol	Condition	Min.	Typ.	Max.
CTRL rising threshold	$V_{CTRL\_RISING}$		0.9VDC		
CTRL falling threshold	$V_{CTRL\_FALLING}$				0.3VDC
CTRL pull down resistance		$V_{CTRL} = 0.2V$	300kΩ	400kΩ	500kΩ

POWER GOOD OPERATING CONDITIONS ( $V_{IN} = 12VDC$ , $V_{OUT} = 3.3VDC$ , $I_{OUT} = 3A$ , unless otherwise noted, typical values are at $T_{AMB} = +25^\circ C$ )					
Parameter		Condition	Min.	Typ.	Max.
PG thresholds		$V_{FB} = \text{rising, PG from low to high}$	91%	95%	99%

REGULATIONS					
Parameter		Condition	Min.	Typ.	Max.
Load Regulation		0-100% load			±1%
Line Regulation		low line to high line, 50% load			±1%
Temperature Regulation		$T_{AMB} = -40^\circ C$ to $+85^\circ C$ , 50% load			±2%

PROTECTION					
Parameter		Condition	Value		
Short Circuit Protection SCP			hiccup mode		
Over Current Protection OCP			3A typ.; 4.5A max.; auto recovery		
Thermal Shutdown		junction temperature hysteresis	150°C typ., auto recovery 15°C typ.		

THERMAL OPERATING CONDITIONS ( $V_{IN} = 12VDC$ , $V_{OUT} = 3.3VDC$ , $I_{OUT} = 3A$ , unless otherwise noted, typical values are at $T_{AMB} = +25^\circ C$ )					
Parameter	Symbol	Condition	Min.	Typ.	Max.
Operating Ambient Temperature	$T_{AMB}$	junction to ambient		refer to "Thermal Derating"	
Operating Case Temperature	$T_{CASE}$				115°C
Operating Junction Temperature	$T_J$		-40°C		+125°C
Thermal Resistance <sup>(7)</sup>	$R_{thJA}$	junction to ambient		30K/W	
	$R_{thJC}$	junction to case		0.5K/W	





**Notes:**

Note7: Tested with 80x80mm, double layer PCB (75μm copper) RECOM EVM board.



ENVIRONMENTAL					
Parameter		Condition	Value		
ESD		human-body model (HBM), ANSI/ESDA/JEDEC JS-001		$\pm 2.5kV$	
		charged-device model (CDM), JEDEC JESD22-C101		$\pm 1kV$	
MTTF		$T_J = 55^\circ C$ ; VCC max; CL = 60%		$19680 \times 10^3$ hours	

Specifications

TYPICAL PERFORMANCE CHARACTERISTICS ( $V_{OUT} = 2.5VDC$ ,  $T_J = +25^\circ C$ ; tested with RECOM evaluation module: RPL-3.0A-EVM-1)





TYPICAL PERFORMANCE CHARACTERISTICS ( $V_{OUT} = 3.3VDC$ ,  $T_J = +25^\circ C$ ; tested with RECOM evaluation module: RPL-3.0A-EVM-1)







continued on next page

Specifications

TYPICAL PERFORMANCE CHARACTERISTICS ( $V_{OUT} = 3.3VDC$ ,  $T_J = +25^\circ C$ ; tested with RECOM evaluation module: RPL-3.0A-EVM-1)



TYPICAL PERFORMANCE CHARACTERISTICS ( $V_{OUT} = 5.0VDC$ ,  $T_J = +25^\circ C$ ; tested with RECOM evaluation module: RPL-3.0A-EVM-1)



Specifications


**SAFETY AND CERTIFICATIONS**

Certificate Type (Safety)	Standard
RoHS2	RoHS 2011/65/EU + AM2015/863

**DIMENSION AND PHYSICAL CHARACTERISTICS**

Parameter	Type	Value
Dimension (LxWxH)		3.0 x 2.8 x 2.0mm
Weight		0.1g typ.

Dimension Drawing (mm)




**Pad Information**

Pad #	Function	Description
1	CTRL	Pull high to turn on. Integrated 400kΩ pull down resistor. This resistor is only active when V <sub>IN</sub> is available.
2	V <sub>IN</sub>	Input voltage pin. Decouple to GND with at least a 10µF MLCC
3	GND	GND pin
4, 5	V <sub>OUT</sub>	Output voltage pin. Decouple this pin to GND pin with 2x 22µF ceramic capacitor
6	FB	Feedback voltage pin. Connect to the center point of output resistor divider to set the output voltage. (refer to "OUTPUT VOLTAGE SETTING")
7	PG	Power good pin. Open drain output at PG OK status. Recommended pull-up resistor= 10-100kΩ
8	SS	Soft-start programming pin. Refer to "SOFT START SETTING"
thermal pad		This pad must be connected to GND

All dimensions exclude mold flash and metal burr.

Tolerances:  
x.x = ±0.1mm  
x.xx = ±0.05mm

**Recommended Footprint Details (\*)**  
(Top View)



\* A large ground plane greatly reduces noise and increases thermal performance.


## Specifications

### SOLDERING

Profile Feature	PB-Free Assembly
<b>Preheat</b>	
minimum Temperature (TS_min)	150°C
maximum Temperature (TS_max)	200°C
Time (tS)	60s-120s
<b>Liquids</b>	
Temperature (TL)	217°C
Time (tL)	60-150s
Peak Temperature (TP)	255°C
max Ramp Down Rate (from Ts_max to TP)	6°C/s
max Ramp Up Rate	3°C/s
max time from 25°C to Peak Temperature (TP)	8min

- 1 Pb-Free assembly is recommended according ro JEDEC J-STD020.
- 2 Ensure that the peak re-flow temperature does not exceed 240°C ±5°C as per JEDEC J-STD020
- 3 The re-flow time period during peak temperature of 240°C ±5°C should not exceed 30 seconds.
- 4 Re-flow time above liquids (217°C) should not exceed 150 seconds.
- 5 For solder paste use a standard SAC Alloy such as SAC 305, type 3 or higher.
- 6 Other soldering methods (e.g. vapor-phase) are not verified and have to be validated at his own risk.

### Solder Pofil



### PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	reel 13" (diameter + width)	Ø330.2 + 12.4mm
	tape and reel (carton)	355.0 x 340.0 x 39.0mm
	moisture barrier bag (" -CT")	100.0 x 100.0 x 30.0mm
Packaging Quantity	tape and reel	3000pcs
	moisture barrier bag (" -CT")	50pcs
Tape Width		12mm
Storage Temperature Range		-55°C to +150°C
Moisture Sensitive Level	MSL peak temp. <sup>(9)</sup>	Level 3, 260°C, 168hrs
<b>Notes:</b>	Note9: The Moisture Sensitivity Level rating is according to the JEDEC industry standard classifications and peak solder temperature	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.