


SPECIFICATIONS

Model Name	GeForce® GTX 1660 SUPER™ GAMING X
Graphics Processing Unit	NVIDIA® GeForce® GTX 1660 SUPER™
Cores	1408 Units
Memory	6GB GDDR6
Bus Standard	PCI Express x16 3.0
Memory Interface	192-bit
Core Clocks	Boost: 1830 MHz
Memory Speed	14 Gpbs
Maximum Displays	3
Output	DisplayPort x 3 (v1.4) / HDMI 2.0b x 1
Power consumption (W)	125 W
HDCP Support	2.2
Virtual Reality Ready	Y
Digital Maximum Resolution	7680x4320
Recommended Power Supply (W)	450 W
Power Connectors	8-pin x 1
DirectX Version Support	12 API
OpenGL Version Support	4.5
Card Dimension(mm)	247 x 127 x 46 mm
Weight	862g / 1460 g

CONNECTIONS



1. DisplayPort
2. HDMI

FEATURES



TORX FAN 3.0

Award-winning fan design combining two different fin designs for cool & quiet gaming.



ZERO FROZR

Eliminates fan noise by stopping the fans in low-load situations so you can focus on your game.



MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.



SOLID BACKPLATE

Increases toughness of the card to prevent bending while complementing the design.



CUSTOM PCB

An optimized PCB design with enhanced power delivery provides a solid base for high performance gaming.



OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



Mastery of Aerodynamics

Using groundbreaking aerodynamic techniques, the heatsink is optimized for efficient heat dissipation.



DRAGON CENTER

A consolidated platform that offers all software including MYSTIC LIGHT functionality for your MSI Gaming product.