

GluePRO 400 LCD

Case set
EAN 4007841 052690
Article number 052690



<2 min.

Quickstart

40-230 °C

Degree-accurate temperature
setting

1,5 kg/h

High adhesive performance

ø 11 mm

Glue sticks



CE



EMC

Function description

Professional gluing to the accuracy of a degree. Virtually any hot-melt adhesive can be used. Including acrylates demanding a high temperature or low-temperature Low Melt adhesives. The GluePRO 400 LCD is the ergonomic hot-melt glue applicator for professional use in industry and the trades, producing optimum results with the capability of setting the temperature to an accuracy of one degree. With a display for monitoring temperature to the accuracy of one degree (40-230°C). Heats up in under two minutes.

Technical specifications

Output	400 W	Temperature accuracy +/-	2 °C
Temperature	40 – 230 °C	Heating element	PTC heating element
Warm-up time	2 min	Voltage range (min)	220 V
Delivery rate	30 gr/min	Restart protection	Yes
Max. stick diameter	11.7 mm	Cord length	max.
Temperature display	LCD display	Dimensions (L x W x H)	230 x 70 x 290 mm
Function, hanger	Yes	Version	Case set
Soft grip	Yes	PU1, net weight	1,6 kg
Idle mode	Yes	Manufacturer's Warranty	1 year
Nozzle can be changed	Yes	PU1, EAN	4007841052690
Stroke adjustment	Yes	Netzstecker	Typ F
Temperature, adjustable	Yes		

Accessories

EAN 4007841 052737	Long nozzle
EAN 4007841 052744	Long nozzle, angled, ø 3.0 mm

GluePRO 400 LCD

Case set
EAN 4007841 052690
Article number 052690



Accessories

EAN 4007841 052928	Long nozzle, Ø 1.5 mm
EAN 4007841 052935	Long nozzle
EAN 4007841 052416	Acrylate glue sticks Ø 11 mm
EAN 4007841 052430	Fast glue sticks Ø 11 mm
EAN 4007841 052423	Flex glue sticks Ø 11 mm
EAN 4007841 052409	Low Melt glue sticks Ø 11 mm
EAN 4007841 050092	General-purpose glue sticks Ø 11 mm