


RoHS  
Compliant



## Description

These self-adhesive Optical Fibre Flag Labels are designed to be used on individual optical fibres. Supplied in A4 sheets, print through an ordinary office laser printer. The special shoulder design helps the user to align the label when fitting. These polyester labels incorporate a strong acylyic adhesive to ensure long term bonding

## Technical Data

Printing method : Standard Laser  
Material : Self-adhesive  
Polyester : Polyester  
Thickness : 36 micron  
Sheet Size : A4

## Storage Instructions

Storage Instructions : Store between 50°F (10°C) and 77°F (25°C)  
Conditions : Keep in dark conditions  
Humidity Resistance : 35% to 65% RH

## Testing:

Test	Method
Low Temperature	MIL-STD-810F Method 502.4 - 72 hours @ -40°C
Elevated Temperature	MIL-STD-202G Method 108A - 1000 hours @ 85°C
Hydrogen Sulphide	H2S Sour Gas Exposure (2% H2S)
UV Weathering*	ISO 4982 Part 3 Method A Cycle 1 - 500 hours
Salt Mist Spray	IEC60068-2-52 Test Kb Salt Mist (Cyclic)

\* Followed by a manipulation test. Manipulation of the labels were performed at -40°C at completion of the low temperature test.

## Additional Information

- Print using a standard office laser printer
- Pre-cut for rapid removal from sheet
- Super strength adhesive to ensure long-term bonding
- To print these labels download our free Multicomp Pro Labelling Software from the following links:

[farnell.com/multicomp-pro-label-software](http://farnell.com/multicomp-pro-label-software)  
[newark.com/multicomp-pro-label-software](http://newark.com/multicomp-pro-label-software)  
[element14.com/multicomp-pro-label-software](http://element14.com/multicomp-pro-label-software)

Fibre Flag Labels Images	Part Number
	MP005839
	MP005840

## Part Number Table

Description	Label Dimensions (mm)	Printable Area (mm)	Labels Per Sheet	Labels Per Pack	Cable Diameter	Part Number
Fibre Flag Label, White	10 × 20	10 × 20	75	750	OD Ø 1-2mm	MP005839
	30 × 20	30 × 20	30	300		MP005840

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.