

Vishay Dale

AUTOMOTIVE

RoHS


COMPLIANT

HALOGEN

FREE GREEN

<u>(5-2008)</u>

IHLE® High Current Inductors With E-Field Shield



APPLICATIONS

- High current storage inductor for synchronous buck converter (switch-node interference cancellation)
- High frequency SMPS inductor as storage and EMI filter to reduce the conducted emissions with grounding of E-Shield cover
- DC/DC converters for entertainment/navigation systems
- Noise suppression for motors: windshield wipers, power seats, power mirrors, heating and ventilation blower, connectivity, audio, and navigation power supply
- LED drivers

FEATURES

- High temperature, continuous operation up to 155 °C
- Improved radiated E-Field reduction over standard IHLE
- Polarity marked for more consistent performance in uni-polar applications
- Patented shielded construction
- Excellent DC/DC energy storage up to 2 MHz.
 Filter inductor applications up the SRF (see standard electrical specifications table)
- Integrated E-Field shield eliminates need for separate shielding
- Up to 20 dB radiated E-Field reduction at 1 cm
 Measured vertically from top center of device
- B-Field is contained by powdered iron encapsulataion
- AEC-Q200 qualified
- Low DCR/µH
- Handles high transient current spikes without saturation
- IHLE design; PATENT(S): www.vishav.com/patents
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

STANDARD ELECTRICAL SPECIFICATIONS									
			DCR MAX.	HEAT RATING CURRENT DC TYP.	SATURATION CURRENT DC TYP.		SRF TYP.		
PART NUMBER	(μH)	$(m\Omega)$	$(m\Omega)$	(A) ⁽¹⁾	(A) ⁽²⁾	(A) ⁽³⁾	(MHz)		
IHLE4040DDEWR47M5A	0.47	1.55	1.66	32	28	40.1	32.0		
IHLE4040DDEW1R0M5A	1.0	2.87	3.07	23	23	33.3	23.0		
IHLE4040DDEW1R5M5A	1.5	4.2	4.5	20	18	26.3	20.0		
IHLE4040DDEW2R2M5A	2.2	8.15	8.76	13.7	8.5	12.3	13.7		
IHLE4040DDEW3R3M5A	3.3	11	11.81	13.4	9.2	13.3	13.4		
IHLE4040DDEW4R7M5A	4.7	14.3	15.32	10	8.1	11.7	10.0		
IHLE4040DDEW6R8M5A	6.8	20.9	22.36	8.4	8	11.6	8.4		
IHLE4040DDEW100M5A	10	30.9	33.06	7	7.3	10.6	7.3		
IHLE4040DDEW150M5A	15	47	50.29	5.6	6.1	8.9	6.1		
IHLE4040DDEW220M5A	22	70.5	75.44	5.1	5.4	7.8	5.4		
IHLE4040DDEW330M5A	33	110	117.7	4	4.5	6.5	4.5		
IHLE4040DDEW470M5A	47	167	178	3.2	4	5.6	4.0		
IHLE4040DDEW680M5A	68	240	252	2.6	3.5	4.9	3.5		

Notes

- All test data is referenced to 25 °C ambient
- Operating temperature range -55 °C to +155 °C
- The part temperature (ambient + temp. rise) should not exceed 155 °C under worst case operating conditions. Circuit design, component
 placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be
 verified in the end application
- Rated operating voltage, across inductor (V1) = 75 V
- Rated isolation voltage, inductor lead to shield (V2) = 100 V
- (1) DC current (A) that will cause an approximate ΔT of 40 °C
- DC current (A) that will cause L₀ to drop approximately 20 %
- $^{(3)}$ DC current (A) that will cause L_0 to drop approximately 30 %


PATENT(S): www.vishay.com/patents

Revision: 14-Oct-2022

This Vishay product is protected by one or more United States and international patents.



Vishay Dale




DESCRIPTION						
IHLE-4040DD-5A	4.7 μH	± 20 %	EW	e3		
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD		

GLOBAL PART NUMBER							
I H L E	4 0 4 0 D	D E W 4 R 7 M 5 A					
PRODUCT FAMILY	SIZE	PACKAGE INDUCTANCE TOL. SERIES CODE VALUE					




Vishay Dale



Note


• Coplanarity of 4 terminals: 0.004" [0.10]

Vishay Dale



MAGNETIC FIELD AND POLARITY MARKING


CONFIGURATION OF THE "B" (FLUX) FIELD FOR THE IHLE




When a positive (+) voltage is placed on the terminal marked with the polarity dot and the opposite terminal is negative (-), the resulting current flow will create a magnetic south pole on the top side of the IHLP. Observing the polarity orientation when mounting the IHLP will insure the most consistent EMI reduction performance.

Drawing is for illustrative purposes only. The flux leakage from the inductor is minimal.






Vishay Dale










Vishay Dale





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.