

DIY Adhesives

**Araldite® Crystal**

Two component clear epoxy adhesive

**Other commercial names**

- Araldite® Cristal
- Araldite® Rapid Ceramic & Glass
- Araldite® Rapid (Scandinavia)

**Key properties**

- Fast curing at room temperature
- Transparent / colour free
- 1:1 mixing ratio
- Solvent free

**Description**

Araldite® Crystal is a transparent two part liquid epoxy adhesive suitable for bonding a wide range of substrates including metals, composites, ceramics and many plastics.

**Product data**

Property	Araldite® Crystal Resin	Araldite® Crystal Hardener	Araldite® Crystal mixed
Colour (visual)	colourless transparent	almost colourless	transparent
Specific gravity	1.15	1.16	1.16
Viscosity at 25°C (Pas)	18 - 45	15 - 35	ca 30
Pot Life (100 g at 25°C)	-	-	ca. 5 mins

**Processing**

**Pretreatment**


The strength and durability of a bonded joint are dependant on proper treatment of the surfaces to be bonded.

At the very least, joint surfaces should be cleaned with a good degreasing agent such as acetone, iso-propanol (for plastics) or proprietary degreasing agent in order to remove all traces of oil, grease and dirt.

Low grade alcohol, gasoline (petrol) or paint thinners should never be used.

The strongest and most durable joints are obtained by either mechanically abrading or chemically etching ("pickling") the degreased surfaces. Abrading should be followed by a second degreasing treatment

Mix ratio	Parts by weight	Parts by volume
Araldite® Crystal Resin	100	100
Araldite® Crystal Hardener	100	100



### Application of adhesive

The resin/hardener mix is applied directly or with a spatula to the pretreated and dry joint surfaces.

A layer of adhesive 0.05 to 0.10 mm thick will normally impart the greatest lap shear strength to the joint. Huntsman stresses that proper adhesive joint design is also critical for a durable bond. The joint components should be assembled and secured in a fix position as soon as the adhesive has been applied.

### Equipment maintenance

All tools should be cleaned with hot water and soap before adhesives residues have had time to cure. The removal of cured residues is a difficult and time-consuming operation.

If solvents such as acetone are used for cleaning, operatives should take the appropriate precautions and, in addition, avoid skin and eye contact.

### Times to minimum shear strength

Temperature	°C	23
Cure time to reach	hours	
LSS > 1MPa	minutes	20
Cure time to reach	hours	2
LSS > 10MPa	minutes	

LSS = Lap shear strength.


## Typical cured properties


### Average lap shear strengths of typical joints (ISO 4587)

Cured for 16 hours at 40°C for the metals and 7 days at 23°C for the plastics

Tested at 23°C.


Pre-treatment: plastics abraded and degreased, metals sandblasted and degreased.





## Lap shear strength versus temperature (ISO 4587) (typical average values)

Carried out on sandblasted and degreased aluminium, cure 16 hours at 40°C



### Storage

Araldite® Crystal may be stored for up to 5 years at room temperature provided the components are stored in sealed containers.

### Handling precautions

#### Caution

Our products are generally quite harmless to handle provided that certain precautions normally taken when handling chemicals are observed. The uncured materials must not, for instance, be allowed to come into contact with foodstuffs or food utensils, and measures should be taken to prevent the uncured materials from coming in contact with the skin, since people with particularly sensitive skin may be affected. The wearing of impervious rubber or plastic gloves will normally be necessary; likewise the use of eye protection. The skin should be thoroughly cleaned at the end of each working period by washing with soap and warm water. The use of solvents is to be avoided. Disposable paper - not cloth towels - should be used to dry the skin. Adequate ventilation of the working area is recommended. These precautions are described in greater detail in the Material Safety Data sheets for the individual products and should be referred to for fuller information.



**Huntsman Advanced Materials (Switzerland) GmbH**  
Klybeckstrasse 200  
CH - 4057 Basel  
Switzerland

Tel: +41 (0)61 299 11 11  
Fax: +41 (0)61 299 11 12

[www.aralditeadhesives.com](http://www.aralditeadhesives.com)

Huntsman Advanced Materials warrants only that its products meet the specifications agreed with the user. Specified data are analysed on a regular basis. Data which is described in this document as 'typical' or 'guideline' is not analysed on a regular basis and is given for information purposes only. Data values are not guaranteed or warranted unless if specifically mentioned.

The manufacture of materials is the subject of granted patents and patent applications; freedom to operate patented processes is not implied by this publication.

While all the information and recommendations in this publication are, to the best of Huntsman Advanced Material's knowledge, information and belief, accurate at the date of publication, **nothing herein is to be construed as a warranty, whether express or implied, including but without limitation, as to merchantability or fitness for a particular purpose. In all cases, it is the responsibility of the user to determine the applicability of such information and recommendations and the suitability of any product for its own particular purpose.**

The behaviour of the products referred to in this publication in manufacturing processes and their suitability in any given end-use environment are dependent upon various conditions such as chemical compatibility, temperature, and other variables, which are not known to Huntsman Advanced Materials. It is the responsibility of the user to evaluate the manufacturing circumstances and the final product under actual end-use requirements and to adequately advise and warn purchasers and users thereof.

Products may be toxic and require special precautions in handling. The user should obtain Safety Data Sheets from Huntsman Advanced Materials containing detailed information on toxicity, together with proper shipping, handling and storage procedures, and should comply with all applicable safety and environmental standards.

Hazards, toxicity and behaviour of the products may differ when used with other materials and are dependent on manufacturing circumstances or other processes. Such hazards, toxicity and behaviour should be determined by the user and made known to handlers, processors and end users.

Except where explicitly agreed otherwise, the sale of products referred to in this publication is subject to the general terms and conditions of sale of Huntsman Advanced Materials LLC or of its affiliated companies including without limitation, Huntsman Advanced Materials (Europe) BVBA, Huntsman Advanced Materials Americas Inc., Huntsman Advanced Materials (UAE) FZE, Huntsman Advanced Materials (Guangdong) Company Limited, and Huntsman Advanced Materials (Hong Kong) Ltd.

Huntsman Advanced Materials is an international business unit of Huntsman Corporation. Huntsman Advanced Materials trades through Huntsman affiliated companies in different countries including but not limited to Huntsman Advanced Materials LLC in the USA and Huntsman Advanced Materials (Europe) BVBA in Europe.

All trademarks mentioned are either property of or licensed to Huntsman Corporation or an affiliate thereof in one or more, but not all, countries.

Copyright © 2019 Huntsman Corporation or an affiliate thereof. All rights reserved