
SHC68-C68-D4 Specifications

2022-06-30



Contents

Specifications..... 3

Specifications

This document lists the specifications for the SHC68-C68-D4. Specifications in this document are nominal unless otherwise noted. Specifications are subject to change without notice. Refer to ni.com/manuals the most recent specifications.



Caution Do not exceed the operating specifications for the device connected to the SHC68-C68-D4. Refer to the documentation for your high-speed digital device for the warranted, maximum operating temperature, additional environmental requirements, and pinouts.

The SHC68-C68-D4 is available with the following options and lengths:

- 0.55 m (781013-01)
- 1 m (196275-01)
- 1 m low leakage^[1] (152870-01)
- 2 m (781293-01)

Visit ni.com/info and enter the Info Code D4COMPATIBILITY for a list of devices and accessories that are compatible with the SHC68-C68-D4.

Electrical Specifications

Maximum voltage	±30 VDC		
Specification	0.55 m	1 m and 1 m Low-Leakage ^[1]	2 m
Characteristic impedance	50 Ω ±10%	50 Ω ±10%	50 Ω ±10%
Resistance	0.3 Ω	0.5 Ω	1 Ω
Capacitance	60 pF	100 pF	200 pF
Propagation delay	2.7 ns	4.9 ns	9.6 ns
Channel-to-channel skew	50 ps	50 ps	75 ps

Physical Characteristics

Weight	
0.55 m	175 g (6.2 oz)
1 m and 1 m low leakage	255 g (9.0 oz)
2 m	435 g (15.3 oz)
Wire gauge	
Size	0.032 mm ² (32 AWG)
Stranding	7/0.08 mm (7/40)
I/O connectors	68-pin male VHDCI connector (x2)
I/O channels	40 single-ended channels

Safety

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1

Worldwide Support and Services

Visit ni.com/support to find support resources including documentation, downloads, and troubleshooting and application development self-help such as tutorials and examples.

Visit ni.com/services to learn about NI service offerings such as calibration options, repair, and replacement.

Visit ni.com/register to register your NI product. Product registration facilitates technical support and ensures that you receive important information updates from NI.

NI corporate headquarters is located at 11500 N Mopac Expwy, Austin, TX, 78759-3504, USA.

¹ The PCB surfaces of low-leakage cables are cleaned of contaminants during manufacturing, reducing induced current leakage.