



TECHNICAL INFORMATION

Watts:	15
Lumens:	1700
Shape:	Square
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	110°
Color Temperature:	3000K
Dimension:	200x200x47.5mm
lumens per watt:	110

PRO TRIMLESS DOME LIGHTS | LED LIGHTING


V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 2113909 - 15 White

[View more details](#)

SMD LED'S



FEATURES

- Uses High Quality Power Driver and LED Chip
- Excellent heat dissipation
- Robust PC body for utility applications
- IP44 ingress protection
- Excellent heat dissipation
- Applications - Living Room, Bedroom, Utilities, Passage etc

PACKAGING

Gross Weight (Kgs):	0.63
Unit CBM:	0.00289
Dimension:	200x200x47.5mm

MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	205
Width (Box) mm:	55
Height (Box) mm:	215

LISTING DETAILS

Commodity Code:	9405114090
Ean Code:	3800157681148