

Tab M10 FHD Plus (2nd Gen) ZA6H0017GB

Lenovo

PSREF
Product Specifications
Reference

PERFORMANCE

Processor

MediaTek Helio P22T (8C, 4x A53 @2.3GHz + 4x A53 @1.8GHz)

Graphics

Integrated IMG PowerVR GE8320 GPU

Chipset

MediaTek SoC Platform

Memory

2GB Soldered LPDDR4x

Storage

32GB eMMC (eMCP4x)

Expandable Memory

microSD Card (Up to 256GB, FAT32; 1TB, exFAT)

Card Reader

microSD Card Slot

Storage Support

- 32GB eMCP4x on systemboard
- microSD card, supports FAT32 up to 256GB, exFAT up to 1TB

Camera

Front 5.0MP / Rear 8.0MP

Microphone

2x, Array

Speakers

2 side speakers, optimized with Dolby® Atmos®

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Hall sensor
- Proximity (P) sensor

Vibration Motor

Eccentric Rotating Mass (ERM)

Battery

Integrated 5000mAh (Min.) / 5100mAh (Typ.)

Max Battery Life

Standby time: 6 wks

Online video playback time: 8.5 hr

Browsing time: 9 hr

Charging Time

Over 3.5 hr to fully charged

Power Adapter

5V / 2A

DESIGN

Display

10.3" FHD (1920x1200) IPS 330nits Glossy, Touch

Touchscreen

10-point Multi-touch

Case Material

Metal

Pen

No Support

Dimensions (WxDxH)

244.2 x 153.3 x 8.15 mm (9.61 x 6.03 x 0.32 inches)

Weight

Around 460 g (1.01 lbs)

Case Color

Iron Grey

SOFTWARE

Operating System

Android™ 9 (Pie) or later

CONNECTIVITY

WLAN + Bluetooth®

11ac 1x1 + BT5.0

WWAN

None

VoiceCall

No

Standard Ports

- 1x USB-C® 2.0 (support data transfer, OTG and Power Delivery)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Pogo pin connector (2-point)

Optional Ports (configured)

1x microSD card slot (WLAN models)

SERVICE

Base Warranty

1-year, Courier with 1-year Battery

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- RoHS compliant

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

Product : Lenovo® TB-X606F

TopSeller : Yes

Announce Date : 2020-08-11

EAN / UPC / JAN : 195042079876



- Lenovo reserves the right to change specifications or other product information without notice.
- Product image on this page is a sample, it may not match the real color of this model
- Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Tab M10FHD 2nd Folio BT Keyboard(US)

ZG38C03371

Folio bluetooth keyboard could protect your tablet and keep your tablet stand while typing. It connects the tablet through bluetooth.



Lenovo Active Pen 3 (2023)

ZG38C04479

With 4,096 levels of pressure and tilt detection, the Lenovo Active Pen 3 (2023) affords users the highest level of precision and control as they sketch or just take notes.

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference