



Voluntary safety information based on the Safety Data Sheet in accordance with Annex II of Regulation (EC) No 1907/2006

Page 1 of 9

SDS No. : 640955
V003.0

BERGQUIST SIL PAD TSP 1800 known as Sil-Pad 1200

Revision: 03.06.2022
printing date: 08.07.2022

Replaces version from: 27.05.2021

SECTION 1: Identification of the article and of the company/undertaking

1.1. Product identifier

BERGQUIST SIL PAD TSP 1800 known as Sil-Pad 1200

1.2. Relevant identified uses of the article and uses advised against

Intended use:

Thermal Interface Material

1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 211 797 0

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the article

Classification (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

2.2. Label elements

Label elements (CLP):

Substances and preparations marketed in a specific form or within specific containers need not to be classified according to the REACH Regulation Article 3 (3).

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

Following substances are present in a concentration $\geq 0,1\%$ and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in concentration \geq the concentration limit that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Manufactured item - article

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Voluntary Information: Only Substances of Very High Concern and Skin Sensitising substances will be disclosed in this section.

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
dimethyl maleate 624-48-6 210-848-5	0,01- < 0,1 %	Acute Tox. 4, Oral, H302 Eye Irrit. 2, H319 STOT SE 3, H335 Skin Sens. 1A, H317		

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:
not relevant.

Skin contact:
Rinse with running water and soap.
Obtain medical attention if irritation persists.

Eye contact:
Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:
Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the article

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Dispose of contaminated material as waste according to Section 13.

Scrape up as much material as possible.

Sweep up spilled material. Avoid creating dust.

Store in a partly filled, closed container until disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.

Keep container tightly sealed.

Refer to Technical Data Sheet

7.3. Specific end use(s)

Thermal Interface Material

SECTION 8: Exposure controls/personal protection**8.1. Control parameters**

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
dimethyl maleate 624-48-6	Workers	inhalation	Long term exposure - systemic effects		19,4 mg/m ³	
dimethyl maleate 624-48-6	Workers	dermal	Long term exposure - systemic effects		0,83 mg/kg	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:
Ensure adequate ventilation.
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area
Dust mask, P2 particle filter.

Hand protection:
Chemical-resistant protective gloves (EN 374).
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):
nitrile rubber (NBR; >= 0.4 mm thickness)
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):
nitrile rubber (NBR; >= 0.4 mm thickness)
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:
Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.
Protective eye equipment should conform to EN166.

Skin protection:
Wear suitable protective clothing.
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:
The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.
Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state	solid
Delivery form	solid
Colour	grey
Odor	None
Melting point	Currently under determination
Initial boiling point	Currently under determination
Flammability	Not applicable
Explosive limits	Not applicable, Product is a solid.
Flash point	Product is a solid.

Auto-ignition temperature	Currently under determination
Decomposition temperature	Currently under determination
pH	Currently under determination
Viscosity (kinematic)	Not applicable, Product is a solid.
Solubility (qualitative)	Currently under determination
Partition coefficient: n-octanol/water	Currently under determination
Vapour pressure	Currently under determination
Density	Currently under determination
Relative vapour density:	Not applicable, Product is a solid.
Particle characteristics	Currently under determination

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used properly.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

None if used for intended purpose.

SECTION 11: Toxicological information

General toxicological information:

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

1.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

Hazardous substances CAS-No.	Value type	Value	Species	Method
dimethyl maleate 624-48-6	LD50	1.410 mg/kg	rat	not specified

Acute dermal toxicity:

Hazardous substances CAS-No.	Value type	Value	Species	Method
dimethyl maleate 624-48-6	LD50	> 2.000 mg/kg	rat	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
dimethyl maleate 624-48-6	not irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
dimethyl maleate 624-48-6	irritating	24 h	rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous substances CAS-No.	Result	Test type	Species	Method
dimethyl maleate 624-48-6	sensitising	Guinea pig maximisation test	guinea pig	equivalent or similar to OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
dimethyl maleate 624-48-6	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
dimethyl maleate 624-48-6	negative	oral: gavage		mouse	OECD Guideline 474 (Mammalian Erythrocyte Micronucleus Test)

Carcinogenicity

No data available.

Reproductive toxicity:

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
dimethyl maleate 624-48-6	NOAEL P 200 mg/kg NOAEL F1 200 mg/kg	screening	oral: gavage	rat	OECD Guideline 421 (Reproduction / Developmental Toxicity Screening Test)

STOT-single exposure:

No data available.

STOT-repeated exposure::

No data available.

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains / surface water / ground water.

12.1. Toxicity**Toxicity (Fish):**

No data available.

Toxicity (Daphnia):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
dimethyl maleate 624-48-6	EC50	6,51 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

No data available.

Toxicity (Algae):

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
dimethyl maleate 624-48-6	EC50	13,34 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
dimethyl maleate 624-48-6	EC10	3,98 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

No data available.

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
dimethyl maleate 624-48-6	readily biodegradable	aerobic	96,7 %	28 d	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
dimethyl maleate 624-48-6	0,52	35 °C	OECD Guideline 117 (Partition Coefficient (n-octanol / water), HPLC Method)

12.5. Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

SECTION 14: Transport information

14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the article

VOC content < 1 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H302 Harmful if swallowed.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Voluntary safety information has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the article in the state in which it is delivered. It is intended to describe our articles from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this voluntary safety information are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.