

DATA SHEET

GAS DISCHARGE TUBES TELEPHONE INTERFACE

2R-6-T6 series

RoHS compliant & free



Product specification— April 27, 2021 V.1



Gas Discharge Tube (GDT) Data Sheet

Features


- Provide ultra-fast response to surge voltage from slow-rising surge of 100V/s to rapid-rising surge of 1KV/μs.
- Stable breakdown voltage.
- High insulation resistance.
- Low capacitance (≤1.0pF)
- High holdover voltage
- Large absorbing transient current capability.
- Micro-Gap Design
- Size: 6.0mm*6.0mm
- Storage and operating temperature: -40°C ~ +85°C
- Meets MSL level 1, per J-STD-020
- Safety certification: UL



Applications

- Repeaters, Modems.
- Telephone Interface, Line cards.
- Data communication equipment.
- Line test equipment


Part Number Code



Marking

- B** : BrightKing Logo
- 2RP090-6 : Device Marking Code
- XXXX : Internal Control Code

Dimensions



Electrical Characteristics

Part Number	DC Spark-over Voltage	Maximum Impulse Spark-over Voltage	Nominal Impulse Discharge Current	Alternating Discharge Current	Impulse Life	Minimum Insulation Resistance		Maximum Capacitance	Device Marking Code
	100V/s	1000V/μs	8/20μs 10times	50Hz, 1sec	10/1000μs 100A	Test Voltage	(GΩ)	1MHz	
	(V)	(V)	(KA)	(A)	(times)	DC(V)		(pF)	
2RP075M-6-T6	75±20%	650	20	10	300	50	1.0	1.0	2RP075-6
2RP090M-6-T6	90±20%	600	20	10	300	50	1.0	1.0	2RP090-6
2RM150M-6-T6	150±20%	750	10	5	300	100	1.0	1.0	2RM150-6
2RM230M-6-T6	230±20%	750	10	5	300	100	1.0	1.0	2RM230-6
2RM250M-6-T6	250±20%	800	10	5	300	100	1.0	1.0	2RM250-6
2RM300M-6-T6	300±20%	800	10	5	300	100	1.0	1.0	2RM300-6
2RM350M-6-T6	350±20%	850	10	5	300	100	1.0	1.0	2RM350-6
2RM400M-6-T6	400±20%	850	10	5	300	100	1.0	1.0	2RM400-6
2RM470M-6-T6	470±20%	850	10	5	300	100	1.0	1.0	2RM470-6
2RM600M-6-T6	600±20%	900	10	5	300	100	1.0	1.0	2RM600-6

Note: ① Specific code by request.


Electrical Ratings

Items	Test Condition/Description	Requirement
DC Spark-over Voltage	The voltage is measured with voltage ramp $dv/dt=100V/s$.	To meet the specified value
Maximum Impulse Spark-over Voltage	The maximum impulse spark-over voltage is measured with voltage ramp $dv/dt=1000V/\mu s$.	
Impulse Discharge Current	<p>Maximum 8/20μs surge current that can be applied between two electrodes, 5 positive and 5 negative surges, with 3 minutes interval time.</p>	

Alternating Discharge Current	Rated RMS value of AC current at 50Hz, 1 sec. for 10 times with interval time 3 min.
Insulation Resistance	The resistance of gas tube shall be measured between two electrodes.
Capacitance	The capacitance of gas tube shall be measured between two electrodes. Test frequency: 1MHz

Recommended Soldering Conditions

Reflow Soldering




Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T_L to T_P)	3°C/second max.
Preheat -Temperature Min ($T_{S\ min}$) -Temperature Max ($T_{S\ max}$) -Time (min to max) (t_s)	150°C 200°C 60-180 seconds
$T_{S\ max}$ to T_L -Ramp-up Rate	3°C/second max.
Time maintained above: -Temperature (T_L) -Time (t_L)	217°C 60-150 seconds
Peak Temperature (T_P)	260°C
Time within 5°C of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.


Packaging

Tape



Symbol	Dimension (mm)	
	Spec.	Tolerance
W	16.00	±0.20
P0	4.00	±0.10
P1	12.00	±0.10
P2	2.00	±0.10
D0	1.50	±0.1
E	1.75	±0.10
F	7.50	±0.10
A0	6.30	±0.10
B0	6.30	±0.10
K0	6.30	±0.10
t0	0.40	±0.10

Reel



D	330.00	±1.00
d	13.00	±0.50
L	20.00	±0.50
t	2.00	±0.20

Quantity: 800pcs