

LT2-LED LT-LED MV DUAL R/G and LT-LED 110/230V DUAL R/G



CE – certified to EMC directive 2004/108/EC.
 Complies with low voltage directive 2006/95/EC.
 High voltage transient and polarity reversal protected.
 Operating temperature: -20°C to + 55°C.



Mains 110/230V	red > 10cd green > 3cd	65 flashes/min 6 bursts/flash (red only)	85–265 Vac	IP67	158gms
Multivoltage MV			10–100Vdc		

Features:

A compact dual function LED beacon - green continuous and red flashing light.

- Multivoltage 10–100Vdc, and mains 110Vac and 230Vac versions
- Ideal for indicating process/system status – green continuous light for normal operation, red flashing to indicate status change
- A unique low cost alternative to conventional tower beacons
- Clear lens with coloured LEDs
- Low power consumption
- 3 year guarantee
- Weatherproof to IP67

Materials:

Polycarbonate lens and base. ROHS compliant.

Accessories:

FX2
mounting
base



FX40
mounting
bracket



FX39
mounting
pole



Product	<i>i</i> red flashing	<i>i</i> green constant	Red / Green
Mains 110/230V	15mA @ 110Vac 10mA @ 230Vac		448021
Multivoltage MV	110mA @ 12Vdc 55mA @ 24Vdc 35mA @ 50Vac 25mA @ 100Vac	80mA @ 12Vdc 40mA @ 24Vdc 25mA @ 50Vac 20mA @ 100Vac	446021

76 mm

95 mm

3 x 5.5mm holes

22.5 mm

45 mm