



TECHNICAL INFORMATION

Watts:	40
Lumens:	3270
Input Power:	AC:200-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Beam Angle:	120°
Color Temperature:	6400K
Dimension:	1194x35x67mm
Wire Length:	1.5m



FEATURES

- Suspended linear lights designed with Samsung LED Chips delivering a staggering Long lifespan of 30,000 hours
- Robust Aluminium body
- 1.5 meter suspended wire included
- Includes metal plates to join two fittings to form a linear assembly
- Excellent heat dissipation
- Suitable for commercial and residential applications

SLIM LINEAR LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21600 - 40 Black

[View more details](#)



PACKAGING

Gross Weight (Kgs):	1.85
Unit CBM:	0.00512
Dimension:	1194x35x67mm

MASTER BOX PACKAGING

Box Qty:	12
Length (Box) mm:	80
Width (Box) mm:	40
Height (Box) mm:	1280

LISTING DETAILS

Commodity Code:	94051190
Ean Code:	3800157676663