

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### remark

\*

Art. 31 and 2020/878/EU

### 1.1 Product identifier

**Trade name/designation** WSW SC L0 / WSW SC M1 - Solder Wire lead free Sn0.7Cu Flux L0/M1 3.5%

### Other means of identification

SDS-41 UK

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

#### Relevant identified uses

##### remark

Solder wire

##### Sector of uses [SU]

SU16 Manufacture of computer, electronic and optical products, electrical equipment

### 1.3 Details of the supplier of the safety data sheet

#### Supplier

Weller Tools GmbH

Carl-Benz-Strasse 2

Germany-74354 Besigheim

Telephone: +49 7143 580-0

Telefax: +49 7143 580-108

E-mail: info@weller-tools.com

Department responsible for information: environmental department

Information telephone: +49 7143 580-101

Information telefax: +49 7143 580-108

### 1.4 Emergency telephone number

GIZ Mainz +49 6131 - 19240 (German, English, French)

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

**Classification according to Regulation (EC) No 1272/2008 [CLP]**

#### health hazards

Skin Sens. 1

#### hazard statements for health hazards

H317 May cause an allergic skin reaction.

### 2.2 Label elements

**Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

#### Hazard components for labelling

rosin / colophony

#### Hazard pictograms



GHS07

#### Signal word

Warning

#### Hazard statements

##### hazard statements for health hazards

H317 May cause an allergic skin reaction.

#### Precautionary statements

##### General:

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

##### Prevention

P280 Wear protective gloves/protective clothing and eye/face protection.

##### Disposal:

P501 Dispose of contents/container to an appropriate recycling or disposal facility.

## Special rules for supplemental label elements for certain mixtures

EUH208 Contains . May produce an allergic reaction.

rosin / colophony

\*

## Special rules on packaging

The product is classified according to CLP regulation. A label is not required (CLP Att. I, 1.3.4.1). Information acc. 1.3.4.2 in Chapter 2.2

\*

## 2.3 Other hazards

### Other adverse effects

People who suffer from skin sensitization problems, asthma, allergies, chronic or recurring respiratory illnesses should not be deployed in any process using this mixture. Processing vapours can irritate the respiratory tracts, skin and eyes.

## SECTION 3: Composition / information on ingredients

### 3.1/3.2 Substances/Mixtures

#### Description

tin-alloy

#### Hazardous ingredients

colophony

>=2,3 - <=3,7 %

CAS 8050-09-7

EC 232-475-7

INDEX 650-015-00-7

REACHNo 01-2119480418-31-\*

Skin Sens. 1, H317

Copper

>=0,4 - <=0,7 %

CAS 7440-50-8

EC 231-159-6

REACHNo 01-2119480154-42

Aquatic Chronic 2, H411

tin

>=96 - <=99 %

CAS 7440-31-5

EC 231-141-8

REACHNo 01-2119486474-28

#### Additional information

\*

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General information

In case of allergic symptoms, especially in the breathing area, seek medical advice immediately.

#### Following inhalation

Provide fresh air. In case of respiratory tract irritation, consult a physician.

#### Following skin contact

Do not peel solidified product off the skin. After contact with molten product, cool skin area rapidly with cold water. In case of skin irritation, consult a physician.

#### After eye contact

In case of contact with eyes, rinse immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart. Subsequently consult an ophthalmologist.

#### Following ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention.

### 4.2 Most important symptoms and effects, both acute and delayed

No data available

### 4.3 Indication of any immediate medical attention and special treatment needed

No data available

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

Carbon dioxide (CO2)

Extinguishing powder

Foam

Dry extinguishing powder  
Sand

## Unsuitable extinguishing media

Full water jet

## 5.2 Special hazards arising from the substance or mixture

### Hazardous combustion products

Carbon monoxide  
Carbon dioxide (CO<sub>2</sub>)

## 5.3 Advice for firefighters

### Special protective equipment for firefighters

In case of fire: Wear self-contained breathing apparatus.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

#### For non-emergency personnel

##### Personal precautions

Use personal protection equipment.

#### For emergency responders

##### Personal protection equipment

Wear breathing apparatus if exposed to vapours/dusts/aerosols.

### 6.2 Environmental precautions

Do not empty into drains or the aquatic environment. Do not allow to enter into soil/subsoil.

### 6.3 Methods and material for containment and cleaning up

No data available

### 6.4 Reference to other sections

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

#### Advices on general occupational hygiene

When using do not eat, drink, smoke, sniff. Wash hands and face before breaks and after work and take a shower if necessary.

#### Protective measures

##### Advices on safe handling

Use only in well-ventilated areas. Do not breathe gas/fumes/vapour/spray.

Avoid:

Skin contact

Eye contact

##### Measures to prevent aerosol and dust generation

Vapours / aerosols should be extracted by suction directly at point of origin.

### 7.2 Conditions for safe storage, including any incompatibilities

#### Hints on joint storage

#### Materials to avoid

Do not store together with:

Food and feedingstuffs

#### Storage class

13

### 7.3 Specific end use(s)

No data available

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

#### Occupational exposure limit values

CAS No.	Substance name	LTV	STV	remark
7440-31-5	Tin compounds, inorganic, except SnH <sub>4</sub>	2 mg/m <sup>3</sup>	4 mg/m <sup>3</sup>	
7440-50-8	Copper, fume, respirable dust	0,2 mg/m <sup>3</sup>		Great Britain (UK)
				Great Britain (UK)

LTV = long-term occupational exposure limit value

STV = short-term occupational exposure limit value

source: GESTIS International Limit Values (<http://limitvalue.ifa.dguv.de/>)

Monitoring and observation processes: GESTIS Analytical Methods (<http://amcaw.ifa.dguv.de/>)

## remark

\*

## 8.2 Exposure controls

### Appropriate engineering controls

#### Technical measures to prevent exposure

Reduce exposure to fume by keeping operating temperatures as low as possible taking into account occupational exposure limits and safe handling temperatures (see Section 7). Where practicable handle within an enclosed process. Alternatively local exhaust ventilation should be considered.

### Personal protection equipment

#### Eye/face protection

##### Suitable eye protection:

Eye glasses with side protection

#### Skin protection

##### Suitable material:

NBR (Nitrile rubber)

**Thickness of the glove material**  $\geq 0,2$  mm

#### Body protection:

##### Suitable protective clothing:

Apron

#### Respiratory protection

##### Additional measures for respiratory protection

Half-face mask or quarter facepiece: maximum use concentration for substances with exposure limits: P1 filter: up to a max. of 4 times the exposure limit. P2 filter: up to a max. of 10 times the exposure limit. P3 filter: up to a max. of 30 times the expo.

## remark

If technical exhaust or ventilation measures are not possible or insufficient, respiratory protection must be worn.

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

#### Appearance

##### Physical state

solid

##### Colour

silver

##### Odour

odourless

	parameter	Method - source - remark
Melting point/freezing point	228 °C	
Boiling point or initial boiling point and boiling range		not determined
flammability		not determined
Upper explosion limit		not determined
lower explosion limit		not determined
Flash point (°C)		not determined
Auto-ignition temperature		not determined
Decomposition temperature		not determined
pH		not determined
Kinematic viscosity		not determined
Water solubility		insoluble
Soluble (g/L) in		not determined
Fat solubility		not determined

	parameter	Method - source - remark
Partition coefficient: n-octanol/water		not determined
Vapour pressure	<0,1 mbar	Temperature 20 °C
Density and/or relative density	7,3 g/cm³	Temperature 20 °C
Relative vapour density	6	20 °C
particle characteristics		not determined

## 9.2 Other information

### Solvent content

**Value** 0 %

#### remark

VOC (EU) 0,00 %

### Solid content

**Value** 100 %

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

No information available.

### 10.2 Chemical stability

The product is stable under storage at normal ambient temperatures.

### 10.3 Possibility of hazardous reactions

No hazardous reaction when handled and stored according to provisions.

### 10.4 Conditions to avoid

No information available.

### 10.5 Incompatible materials

No information available.

### 10.6 Hazardous decomposition products

Thermal decomposition can lead to the escape of irritating gases and vapours.

## SECTION 11: Toxicological information

### 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

#### Acute toxicity

#### Assessment/classification

Based on available data, the classification criteria are not met.

#### skin corrosion/irritation

**ingredient** colophony

#### Assessment/classification

Irritant.

#### Respiratory or skin sensitisation

#### Skin sensitisation

#### Assessment/classification

May cause sensitization by inhalation and skin contact.

### CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

#### Germ cell mutagenicity

#### Assessment/classification

Based on available data, the classification criteria are not met.

#### Reproductive toxicity

#### Assessment/classification

Based on available data, the classification criteria are not met.

### STOT-single exposure

#### STOT SE 3

#### Irritation to respiratory tract

#### Assessment/classification

May cause respiratory irritation.

## 11.2 Information on other hazards

### Endocrine disrupting properties

#### remark

This product does not contain a substance that has endocrine disrupting properties with respect to humans as no components meets the criteria.

## SECTION 12: Ecological information

### 12.1 Toxicity

#### Assessment/classification

No data available

### 12.2 Persistence and degradability

#### Assessment/classification

not readily biodegradable (according to OECD criteria)

### 12.3 Bioaccumulative potential

No information available.

### 12.4 Mobility in soil

No information available.

### 12.5 Results of PBT and vPvB assessment

No information available.

### 12.6 Endocrine disrupting properties

#### remark

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

### 12.7 Other adverse effects

No information available.

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

#### remark

The allocation of waste identity numbers/waste descriptions must be carried out according to the EEC, specific to the industry and process. Recycle according to official regulations.

### Directive 2008/98/EC (Waste Framework Directive)

#### Before intended use

**Waste code product** 170407

**hazardous waste** No

**Waste name**

mixed metals

#### Recovery operations

R4 Recycling/reclamation of metals and metal compounds

#### After intended use

**Waste code packaging** 150102

**hazardous waste** No

**Waste name**

plastic packaging

**Waste code packaging** 150101

**hazardous waste** No

**Waste name**

paper and cardboard packaging

## SECTION 14: Transport information

	Land transport (ADR/RID)	Sea transport (IMDG)	Air transport (ICAO-TI / IATA-DGR)
14.1 UN number or ID number	not applicable	not applicable	not applicable
14.2 Proper Shipping Name	not applicable	not applicable	not applicable
14.3 Class(es)	not applicable	not applicable	not applicable
14.4 Packing group	not applicable	not applicable	not applicable
14.5 Environmental hazards	not applicable	not applicable	not applicable
14.6 Special precautions for user	not applicable	not applicable	not applicable

	Land transport (ADR/RID)	Sea transport (IMDG)	Air transport (ICAO-TI / IATA-DGR)
14.7 Maritime transport in bulk according to IMO instruments	not applicable	not applicable	not applicable

## Additional information

### All transport carriers

No dangerous good in sense of these transport regulations.

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### EU legislation

#### Authorisations and/or restrictions on use

#### Restrictions of occupation

Observe restrictions to employment for juvenils according to the 'juvenile work protection guideline' (94/33/EC).

#### Other regulations (EU)

#### Directive 2012/18/EU on the control of major-accident hazards involving dangerous substances [Seveso-III-Directive]

##### Named dangerous substances

none

### 15.2 Chemical Safety Assessment

For this substance a chemical safety assessment has not been carried out.

## SECTION 16: Other information

### Abbreviations and acronyms

See overview table at [www.euphrac.eu](http://www.euphrac.eu)

### Classification for mixtures and used evaluation method according to regulation (EC) No 1272/2008 [CLP]

See SECTION 2.1 (classification).

### Indication of changes

\* Data changed compared with the previous version

### Relevant R-, H- and EUH-phrases (Number and full text)

H317 May cause an allergic skin reaction.

H411 Toxic to aquatic life with long lasting effects.

### Key literature references and sources for data

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.