

PRODUCT DATASHEET

HB P 87W 840 110DEG IP65

HIGH BAY GEN 4 | High-bay luminaires up to 150 lm/W and attractive UGR



Areas of application

- Replacement for high bay luminaires with mercury vapor or metal halide lamps
- Warehouses
- Logistics halls
- Industry
- High ceiling (e.g. in shopping malls, airports, commercial buildings, lobbies)

Product benefits

- Improved UGR compared to previous generations, down to $UGR \leq 22$ in combination with reflector
- High luminous efficacy
- Energy savings of up to 64 % compared to conventional high bay luminaires
- 5 years guarantee
- Optimized weight and size due to compact design

Product features


- Different luminous flux and beam angle for mounting heights of ~ 6 m to 14 m in 4000 K or 6500 K

TECHNICAL DATA**Electrical data**


Nominal wattage	87.00 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	400 mA
Inrush current	42 A
Inrush current time T_{h50}	378 μ s
Max. no. of lum. on circuit break. B16 A	5
Max. no. of lum. on circuit break. C10 A	5
Max. no. of lum. on circuit break. C16 A	9
Power factor λ	≥ 0.95
Total harmonic distortion	< 20 %
Protection class	I
Operating mode	Mains voltage

Photometrical data

Luminous flux	13000 lm
Luminous efficacy	150 lm/W
Color temperature	4000 K
Light color (designation)	Cool White
Color rendering index Ra	≥ 80
Standard deviation of color matching	≤ 5 sdc _m
Low flicker	Yes
Photobiological safety group acc. to EN62778	RG1
Beam angle	110 °
UGR	≤ 29




LDC typ cone



LDC typ polar

Dimensions & Weight

Diameter	280.00 mm
Height	155.00 mm
Product weight	2264.00 g
Cable length	1500 mm



Materials & Colors

Product color	Black
Housing color	Black

Body material	Aluminum
Cover material	Polycarbonate (PC)
Glow Wire Test according to IEC 60695-2-12	850 °C
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-30...+50 °C
Temperature range at storage	-40...+70 °C
Type of connection	Cable, 3-pole
Type of protection	IP65
Protection class IK (shock resistance)	IK08
Dimmable	No
Mounting type	Suspended/Surface
Mounting location	Ceiling / Wall
Application environment	Indoor
LED module replaceable	Not replaceable
With light source	Yes

Lifespan

Lifespan L70/B50 at 25 °C	80000 h
Lifespan L80/B10 at 25 °C	50000 h
Lifespan L90/B10 at 25 °C	35000 h
Number of switching cycles	200000

Control gear

ECG - Output ripple current	< 10 %
-----------------------------	--------

Certificates & Standards

Standards	CE / CB / ENEC / TÜV SÜD / EAC
Luminaire with limited surface temperature, "D sign"	Yes
Ball shot safe	No

Additional product data

Product remark	
----------------	--

EQUIPMENT / ACCESSORIES

- Mounting hook included
- Mounting brackets, reflectors and refractors available as separate accessory

DOWNLOAD DATA

DOWNLOAD DATA

	User instruction UI HIGHBAY GEN 4
	Addon Technical Information LS Insert HB P GEN4
	Declarations of conformity EC Declaration HB P
	IES file (IES) HB P 87W 840 110DEG IP65
	LDT file (Eulumdat) HB P 87W 840 110DEG IP65
	R3D file (Relux 3D Model) HB P /HB SEN P 87W
	M3D file (3D Model) HB P/ HB SEN P 87W
	UGR file (UGR table) HB P 87W 840 110DEG IP65

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075692718	Shipping box 1	328 mm x 328 mm x 171 mm	2872.00 g	18.40 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.