SMT Current Sense Transformer

PH9505.XXXNL EP10 SMD Platform











Insulation: Reinforced, 6.5mm creepage

@ Isolation: 3000Vrms **@ Height:** 14.4mm Max

Prootprint: 13.6mm x 12.8mm Max

@ Current Rating: up to 30A

Operating Frequency: Greater than 20kHz

Electrical Specifications @ 25°C — Operating Temperature -40°C to +150°C									
Part ^{5,6} Number	Turns Ratio ±2.0%	Current ² Rating (A)	Secondary Inductance (mH Min)	DCR (mΩ Max)		Llinat			
				Primary (1*-2)	Secondary (5*-4)	Hipot (Vac)			
PH9505.050NLT	1:50	30	1.7	0.5	1500	3000			
PH9505.070NLT	1:70	30	3.0	0.5	2100	3000			
PH9505.100NLT	1:100	30	7.0	0.5	3100	3000			
PH9505.125NLT	1:125	30	11	0.5	4000	3000			
PH9505.180NLT	1:180	30	25	0.5	9000	3000			

NOTES:

- The temperature of component (ambient temperature plus temper-ature rise) must be within the specified operating temperature range.
- The maximum current rating is based upon temperature rise of the component and represents the DC current which will cause a typical temperature rise of 40°C.
- 3. To calculate value of terminating resistor (Rt) use the following formula: Rt (W) = VREF * N / (Ipeak primary)
- The peak flux density of the device must remain below 2200 Gauss. To calculate the peak flux density for uni-polar current use following formula:

Bpk = 8.85* Vref * (Duty_Cycle_Max) * 10^5 / (N * Freq_kHz)

- * for bi-polar current applications divide Bpk (as calculated above) by 2.
- This design complies with basic insulation according to EC60664/ IEC60590-1/IEC61558-1/-2-16 for a


working voltage up to 500Vrms and with reinforced insulation according to IEC60664/IEC60950-1 for working voltage up to 300Vrms


Application condition: OVC II, Pollution degree 2, Material Group 3, Altitude up to 2km. The actual creepage distance > 6.5mm and the clearance distance >4.5mm between primary and secondary windings. This creepage distance is reduced when the transformer is mounted on the proposed pad layout. Refer to the PCB material group and pollution degree to determine if this reduces the working voltage capability.

- Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. PH9505.100NL becomes PH9505.100NLT). Pulse complies to industry standard tape and reel specifi-
- The "NL" suffix indicates an RoHS-compliant part number.

Mechanical

Schematic





Tape & Reel 150/reel

Dimensions: Inches

Unless otherwise specified, all tolerances are ± .010

SMT Current Sense Transformer

PH9505.XXXNL EP10 SMD Platform



For More Information									
Pulse Worldwide Headquarters 15255 Innovation Drive Ste 100 San Diego, CA 92128 U.S.A.	Pulse Europe Pulse Electronics GmbH Am Rottland 12 58540 Meinerzhagen Germany	Pulse China Headquarters Pulse Electronics (ShenZhen) CO., LTD D708, Shenzhen Academy of Aerospace Technology, The 10th Keji South Road, Nanshan District, Shenzhen, P.R. China 518057	Pulse North China Room 2704/2705 Super Ocean Finance Ctr. 2067 Yan An Road West Shanghai 200336 China	Pulse South Asia 3 Fraser Street 0428 DUO Tower Singapore 189352	Pulse North Asia 1F., No.111 Xiyuan Rd Zhongli City Taoyuan City 32057 Taiwan (R.O.C)				
Tel: 858 674 8100 Fax: 858 674 8262	Tel: 49 2354 777 100 Fax: 49 2354 777 168	Tel: 86 755 33966678 Fax: 86 755 33966700	Tel: 86 21 62787060 Fax: 86 2162786973	Tel: 65 6287 8998 Fax: 65 6280 0080	Tel: 886 3 4356768 Fax: 886 3 4356820				

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2019. Pulse Electronics, Inc. All rights reserved.