

Fiber Optic Sensor Cable - 2M, Diffuse reflection, M3, straight, R15



FOACAMPDRC32

Fiber Optic Sensor Cable

Features

- Durable stainless steel head
- Flexible jacket
- Standard 2.2mm diameter ferrules
- Stable performance

Applications

- Industrial automation
- Discrete manufacturing
- High volume production
- Automotive manufacturing
- Stamping and plastic injection molding
- Packaging
- Food and Beverage
- Warehouse automation

Description

The L-com FOACAMPDRC32 is a diffuse reflection type fiber optic sensor cable. A stainless steel head and flexible PVC jacket makes the cable well suited for demanding industrial environments. The 2.2mm fiber ends make them compatible with industry standard amplifier ports, making interchanging quick and easy. Used in conjunction with L-com fiber optic sensor amplifiers, the resulting optical sensor is well suited for use in manufacturing and other industrial applications where fast, accurate sensing is critical. The L-com FOACAMPDRC32 is part of the IoT portfolio of products available from L-com, in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for more information on this, and other IoT products from L-com.

General Specifications

Design Type	Diffuse Reflection - Coaxial Core
Cable Type	POF
Jacket Type	PVC Black
Nominal Sensing Distance	60 mm
Cable Length	2 m
Cable Head Orientation	Straight
Cable Head Size	M3
Cable Head Material	Stainless Steel
Bend Radius	15 mm
Compatible Products	Fiber Optic Sensor Amplifiers

Environmental Specifications

Temperature

Operating Range	-25 to +70 deg C
Storage Range	-30 to +85 deg C

Compliance Certifications (see for current document)

CE Compliance	Yes
RoHS Compliance	Yes

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Fiber Optic Sensor Cable - 2M, Diffuse reflection, M3, straight, R15 FOACAMPDRC32](#)

Fiber Optic Sensor Cable - 2M, Diffuse reflection, M3, straight, R15

FOACAMPDRC32


Fiber Optic Sensor Cable



Fiber Optic Sensor Cable - 2M, Diffuse reflection, M3, straight, R15 from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing



NOTES:
1. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS	THIRD-ANGLE PROJECTION
TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	THE INFORMATION AND DIMENSIONS SHOWN HEREIN IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.
FRACTIONS ± 1/32	SCALE N/A
ANGLES ± 1°	SHEET 1 OF 1
CABLE LENGTH (L) TOLERANCES: L ≤ 12 [305] < L ≤ 60 [1524] = ±1 [25] / -0 60 [1524] < L ≤ 120 [3048] = ±4 [102] / -0 120 [3048] < L ≤ 300 [7620] = ±6 [152] / -0 300 [7620] < L = +5% / -0	ITEM NO. FOACAMPDRC32
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	REV A
SIZE A	DRAWN BY DMAY
CAGE CODE 43321	FOACAMPDRC32
 an INFINITE brand 50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845, USA. Phone: 1.800.341.5266 1.978.682.6936 Fax: 1.978.689.9484 Website: www.L-com.com E-mail: CustomerService@L-com.com	