


胶料	料号	模具	模号/AB端	ELECTRICAL TEST: 1.100% OPEN SHORT MIS WIRE TEST 2.CONTACT RESISTANCE:3 OHM MAX 3.INSULATION RESISTANCE:10M OHM MIN 4.HI-POT TEST:DC 300V/10ms	CONSUMER ITEM	LENGTH (mm)	ERP	Packing
内模料		内模				7000±50		
中模料		中模						
外模料		外模						




PIN Assignment

P1 HDMI AM

P2 HDMI AM

1	1
3	3
2	2
4	4
6	6
5	5
7	7
9	9
8	8
10	10
12	12
11	11
14	14
19	19
17	17
13	13
15	15
16	16
18	18
SHELL	SHELL



④	CABLE	HDMI 26-28AWG BC 19+1 [(1/0.404BC*1P+D1/0.32BC+AL/MY)*5P+1/0.32BC*4C]+AL +D1/0.32BC+B128/0.12AM+BLACK PVC OD : 8.2±0.15mm	m
③	MODEL	Black 45P PVC	g
②	MODEL	PE,Nature color	g
①	plug	HDMI AM 19P Gold plated PIN:3u SHELL:1u	2PCS
NO.	PART NAME	DESCRIPTION	UNIT

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△			
		HENRY	L.H.R	FINISHING		△	2018/03/22		A1
				MATERIAL		SYM	DATE		REVISION