




胶料	料号	模具	模号/AB端	ELECTRICAL TEST: 1.100% OPEN SHORT MIS WIRE TEST 2.CONTACT RESISTANCE:3 OHM MAX 3.INSULATION RESISTANCE:10M OHM MIN 4.HI-POT TEST:DC 300V/10ms	CONSUMER ITEM	LENGTH (mm)	ERP	Packing
内模料		内模				15000±100		
中模料		中模				20000±100		
外模料		外模						



PIN Assignment

P1 HDMI AM      P2 HDMI AM



⑦	CABLE	HDMI 26-28AWG 1PBC+Superconducting CCS 19+1 [(1/0.404BC*1P+D1/0.32CCS+AL/MY)*1P+(1/0.404CCS*1P+D1/0.32CCS+AL/MY)*4P+1/0.32CCS*3C+1/0.404BC*1C] +AL+D1/0.32CCS+B128/0.12AM BLACK PVC OD:8.2±0.15mm	m
⑥	IC	with one booster on the cable	1PCS
⑤	LABEL	white printing on black ground, "OUTPUT"	1PCS
④	LABEL	white printing on black ground, "INPUT"	1PCS
③	MODEL	Black 45P PVC	g
②	MODEL	PE, Nature color	g
①	PLUG	HDMI AM 19P Gold plated PIN:3u SHELL:1u	2PCS
NO.	PART NAME	DESCRIPTION	UNIT

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△			
		HENRY	L.H.R	FINISHING		△	2018/05/22		A1
				MATERIAL		SYM	DATE		REVISION