

LC1G1154LSEA

Contactor, high power, TeSys Giga, advanced version, 4 pole/NO, AC-1 $\leq 440\text{V}$ 250A, 200-500VAC/DC coil



Main

Range	TeSys
Range of Product	TeSys Giga
Product or Component Type	Contactor
Device short name	LC1G
Contactor application	Power switching
Utilisation category	AC-1 AC-5a AC-5b AC-6a AC-6b DC-1 DC-3 DC-5
Poles description	4P
[Ue] rated operational voltage	$\leq 1000\text{ V AC } 50/60\text{ Hz}$ $\leq 460\text{ V DC}$
[Ie] rated operational current	250 A 104 °F (40 °C) 1000 V AC-1
[Uc] control circuit voltage	200...500 V AC/DC 50/60 Hz
Color	Dark grey

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	250 A 104 °F (40 °C)
Rated breaking capacity	1040 A 440 V
[Icw] rated short-time withstand current	1.1 KA - 10 s 0.64 KA - 30 s 0.52 KA - 1 min 0.4 KA - 3 min 0.32 kA - 10 min
Associated fuse rating	125 A aM 440 V 125 A aM 690 V 315 A gG 690 V
Average impedance	0.00018 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	10 W AC-1 - Ith 250 A
Compatibility code	LC1G
Pole contact composition	4 NO
Auxiliary contact composition	1 NO + 1 NC
Network Frequency	50/60 Hz 16.67...400 Hz
Irms rated making capacity	1560 A 440 V
Control circuit voltage limits	Operational 0.8...1.1 Uc AC/DC 140 °F (60 °C) Drop-out 0.1...0.45 Uc AC/DC 140 °F (60 °C)
Coil technology	Built-in bidirectional peak limiting
Mechanical durability	5 Mcycles 8 Mcycles with sub-assembly substitution
Inrush power in VA (50/60 Hz, AC)	295 VA

Inrush power in W (DC)	215 W
Hold-in power consumption in VA (50/60 Hz, AC)	13.0 VA
Hold-in power consumption in W (DC)	8.0 W
Operating time	45...60 ms closing 15...45 ms opening
Maximum operating rate	300 cyc/h AC-1
Connections - terminals	Power circuit bar 2 25 x 6 mm Power circuit lugs-ring terminals 1 0.29 in ² (185 mm ²) Power circuit bolted connection Control circuit push-in 1 0.00...0.00 in ² (0.2...2.5 mm ²) solid stranded without cable end Control circuit push-in 1 0.00...0.00 in ² (0.25...2.5 mm ²) flexible with cable end Control circuit push-in 2 0.00...0.00 in ² (0.5...1.0 mm ²) with cable end Control circuit push-in 0.00...0.00 in ² (0.75...2.5 mm ²) solid stranded without cable end Control circuit push-in 0.00...0.00 in ² (0.75...2.5 mm ²) flexible with cable end
Connection pitch	1.38 in (35 mm)
Mounting Support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1
Product Certifications	CB Scheme CCC CULus EAC CE UKCA EU-RO-MR by DNV-GL
Tightening torque	159.31 lbf.in (18 N.m)
Height	10.04 in (255 mm)
Width	5.63 in (143 mm)
Depth	7.60 in (193 mm)
Net Weight	11.24 lb(US) (5.1 kg)

Environment

IP degree of protection	IP2x front face with shrouds IEC 60529 IP2x front face with shrouds VDE 0106
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Protective treatment	TH
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C) at Uc

Ordering and shipping details

Category	22329-TESYS GIGA CONTACTORS
Discount Schedule	I12
GTIN	3606481922724
Nbr. of units in pkg.	1
Package weight(Lbs)	14.05 lb(US) (6.374 kg)
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.84 in (25.0 cm)
Package 1 width	10.51 in (26.7 cm)
Package 1 Length	15.35 in (39.0 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	4
Package 2 Weight	78.26 lb(US) (35.496 kg)
Package 2 Height	41.34 in (105.0 cm)
Package 2 width	23.62 in (60.0 cm)
Package 2 Length	31.50 in (80.0 cm)
Package 3 Height	34.84 in (88.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product