

LC1G1854KUEN

Contactor, high power, TeSys Giga, standard version, 4 pole/NO, AC-1 $\leq 440\text{V}$ 305A, 100-250VAC/DC coil



Main

Range	TeSys
Range of Product	TeSys Giga
Product or Component Type	Contactor
Device short name	LC1G
Contactor application	Power switching
Utilisation category	AC-1 AC-5a AC-5b AC-6a AC-6b DC-1 DC-3 DC-5
Poles description	4P
[Ue] rated operational voltage	$\leq 1000\text{ V AC } 50/60\text{ Hz}$ $\leq 460\text{ V DC}$
[Ie] rated operational current	305 A 104 °F (40 °C) 1000 V AC-1
[Uc] control circuit voltage	100...250 V AC/DC 50/60 Hz

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	305 A 104 °F (40 °C)
Rated breaking capacity	1610 A 440 V
[Icw] rated short-time withstand current	1.5 KA - 10 s 0.92 KA - 30 s 0.74 KA - 1 min 0.5 KA - 3 min 0.4 KA - 10 min
Associated fuse rating	200 A aM 440 V 160 A aM 690 V 315 A gG 690 V
Average impedance	0.00017 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	20 W AC-1 - Ith 305 A
Compatibility code	LC1G
Pole contact composition	4 NO
Auxiliary contact composition	1 NO + 1 NC
Network Frequency	50/60 Hz 16.67...400 Hz
Irms rated making capacity	2310 A 440 V
Control circuit voltage limits	Operational 0.8...1.1 Uc AC/DC 140 °F (60 °C) Drop-out 0.1...0.45 Uc AC/DC 140 °F (60 °C)
Coil technology	Built-in bidirectional peak limiting
Mechanical durability	5 Mcycles 8 Mcycles with sub-assembly substitution
Inrush power in VA (50/60 Hz, AC)	540 VA
Inrush power in W (DC)	380 W

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Hold-in power consumption in VA (50/60 Hz, AC)	12.4 VA
Hold-in power consumption in W (DC)	7.8 W
Operating time	45...60 ms closing 15...45 ms opening
Maximum operating rate	300 cyc/h AC-1
Connections - terminals	Power circuit bar 2 25 x 6 mm Power circuit lugs-ring terminals 1 0.29 in ² (185 mm ²) Control circuit push-in 1 0.00...0.00 in ² (0.2...2.5 mm ²) solid stranded without cable end Control circuit push-in 1 0.00...0.00 in ² (0.25...2.5 mm ²) flexible with cable end Control circuit push-in 2 0.00...0.00 in ² (0.5...1.0 mm ²) with cable end Control circuit push-in 0.00...0.00 in ² (0.75...2.5 mm ²) solid stranded without cable end Control circuit push-in 0.00...0.00 in ² (0.75...2.5 mm ²) flexible with cable end
Connection pitch	1.38 in (35 mm)
Mounting Support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1
Product Certifications	CB Scheme CCC CULus EAC CE UKCA EU-RO-MR by DNV-GL
Tightening torque	159.31 lbf.in (18 N.m)
Height	7.60 in (193 mm)
Width	5.63 in (143 mm)
Depth	7.60 in (193 mm)
Net Weight	9.70 lb(US) (4.4 kg)
Color	Dark grey

Environment

IP degree of protection	IP2x front face with shrouds IEC 60529 IP2x front face with shrouds VDE 0106
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Protective treatment	TH
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C) at Uc

Ordering and shipping details

Category	22329-TESYS GIGA CONTACTORS
Discount Schedule	I12
GTIN	3606481922144
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.84 in (25.0 cm)
Package 1 Width	10.43 in (26.5 cm)
Package 1 Length	15.16 in (38.5 cm)
Package 1 Weight	12.54 lb(US) (5.686 kg)
Unit Type of Package 2	S06

Number of Units in Package 2	6
Package 2 Height	29.53 in (75 cm)
Package 2 Width	23.62 in (60 cm)
Package 2 Length	31.50 in (80 cm)
Package 2 Weight	97.26 lb(US) (44.116 kg)
Package 3 Height	29.53 in (75 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product