



CoolMOS™ 1) Power MOSFET

N-Channel Enhancement Mode
Low $R_{DS(on)}$, High V_{DSS} MOSFET

$$\begin{aligned} V_{DSS} &= 600 \text{ V} \\ I_{D25} &= 75 \text{ A} \\ R_{DS(on) \text{ max}} &= 36 \text{ m}\Omega \end{aligned}$$



miniBLOC, SOT-227 B



G = Gate D = Drain S = Source

Either source terminal at miniBLOC can be used as main or kelvin source

MOSFET				
Symbol	Conditions	Maximum Ratings		
V_{DSS}	$T_{VJ} = 25^{\circ}\text{C to } 150^{\circ}\text{C}$	600	V	
V_{GS}		± 20	V	
I_{D25}	$T_C = 25^{\circ}\text{C}$	75	A	
I_{D90}	$T_C = 90^{\circ}\text{C}$	50	A	
$I_{D \text{ puls}}$	pulse drain current, t_p limited by T_{Jmax}	250	A	
E_{AS}	$I_D = 10 \text{ A}; L = 36 \text{ mH}$	$T_C = 25^{\circ}\text{C}$	1.8	J
E_{AR}	$I_D = 20 \text{ A}; L = 5 \text{ mH}$	$T_C = 25^{\circ}\text{C}$	1	mJ
dv/dt	$V_{DS} < V_{DSS}; I_F \leq 100 \text{ A}$ $ di_F/dt \leq 100 \text{ A}/\mu\text{s}$	$T_{VJ} = 125^{\circ}\text{C}$	6	V/ns

Symbol	Conditions	Characteristic Values			
		$(T_{VJ} = 25^{\circ}\text{C}, \text{ unless otherwise specified})$			
		min.	typ.	max.	
$R_{DS(on)}$	$V_{GS} = 10 \text{ V}; I_D = I_{D90}$		30	36	m Ω
$V_{GS(th)}$	$V_{DS} = 20 \text{ V}; I_D = 5 \text{ mA}$	2.1		3.9	V
I_{DSS}	$V_{DS} = V_{DSS}; V_{GS} = 0 \text{ V}$		$T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 125^{\circ}\text{C}$	50	μA μA
I_{GSS}	$V_{GS} = \pm 20 \text{ V}; V_{DS} = 0 \text{ V}$			± 200	nA
Q_g Q_{gs} Q_{gd}	$V_{GS} = 0 \text{ to } 10 \text{ V}; V_{DS} = 350 \text{ V}; I_D = 100 \text{ A}$		500 50 240		nC nC nC
$t_{d(on)}$ t_r $t_{d(off)}$ t_f			20 30 110 10		ns ns ns ns
V_F	(reverse conduction) $I_F = 37.5 \text{ A}; V_{GS} = 0 \text{ V}$		0.9	1.1	V
R_{thJC}				0.22	K/W

Features

- miniBLOC package
 - Electrically isolated copper base
 - Low coupling capacitance to the heatsink for reduced EMI
 - High power dissipation due to AlN ceramic substrate
 - International standard package SOT-227
 - Easy screw assembly
- fast CoolMOS™ 1) power MOSFET 3rd generation
 - High blocking capability
 - Low on resistance
 - Avalanche rated for unclamped inductive switching (UIS)
 - Low thermal resistance due to reduced chip thickness
- Enhanced total power density

Applications

- Switched mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)
- Power factor correction (PFC)
- Welding
- Inductive heating

¹⁾ CoolMOS™ is a trademark of Infineon Technologies AG.

Source-Drain Diode


Symbol	Conditions	Characteristic Values		
		min.	typ.	max.
I_S	$V_{GS} = 0\text{ V}$			85
I_{SM}				250
V_{SD}	$I_F = 85\text{ A}; V_{GS} = 0\text{ V}$			1.2
t_{rr}	$I_F = 85\text{ A}; -di_F/dt = 200\text{ A}/\mu\text{s}; V_R = 350\text{ V}$	580		ns
Q_{RM}		46		μC
I_{RM}		140		A

Component

Symbol	Conditions	Maximum Ratings	
T_{VJ}	operating	-55...+150	°C
T_{stg}		-55...+125	°C
M_d	mounting torque	1.5	Nm
	terminal connection torque (M4)	1.5	Nm

Symbol	Conditions	Characteristic Values		
		min.	typ.	max.
R_{thCH}	with heatsink compound	0.1		K/W
Weight		30		g

miniBLOC, SOT-227 B Outline



SYM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	31.50	31.88	1.240	1.255
B	7.80	8.20	.307	.323
C	4.09	4.29	.161	.169
D	4.09	4.29	.161	.169
E	4.09	4.29	.161	.169
F	14.91	15.11	.587	.595
G	30.12	30.30	1.186	1.193
H	37.80	38.23	1.489	1.505
J	11.68	12.22	.460	.481
K	8.92	9.60	.351	.378
L	0.76	0.84	.030	.033
M	12.60	12.85	.496	.506
N	25.15	25.42	.990	1.001
O	1.98	2.13	.078	.084
P	4.95	5.97	.195	.235
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	.155	.174
S	4.72	4.85	.186	.191
T	24.59	25.07	.968	.987
U	-.05	.10	-.002	.004
V	3.30	4.57	.130	.180
W	19.81	21.08	.780	.830




Fig. 1 Typ. output characteristics $I_D = f(V_{DS})$




Fig. 2 Typ. transfer characteristics $I_D = f(V_{GS})$




Fig. 3 Typical normalized $R_{DS(on)} = f(I_D)$




Fig. 4 Typical normalized $R_{DS(on)} = f(T_J)$




Fig. 5 Continuous drain current $I_D = f(T_C)$

Fig. 6 Typ. normalized $V_{DSS} = f(T_J), V_{GS(th)} = f(T_J)$




Fig. 7 Typ. turn-on gate charge characteristics




Fig. 8 Forward Safe Operating Area, $I_D = f(V_{DS})$




Fig. 9 Typ. capacitances $C = f(V_{DS})$, $f = 1 \text{ MHz}$




Fig. 10 Typ. forward characteristics of reverse diode, $I_S = f(V_{SD})$




Fig. 11 Typical transconductance $g_{fs} = f(I_D)$




Fig. 12 Transient thermal resistance $Z_{thJK} = f(t_p)$



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.