WLC550 Industrial



Features

- 5 x 3 x 1.5 Inches Form factor
- Up to 550 Watts with Forced Air Cooled
- Efficiencies up to 92%
- -40 to 70 degree operating temperature*
- Remote ON/OFF
 New
- Now IEC/EN/UL62368-1 Compliant
 New
- Shall be approved to EN60950-1 2nd Edition
- 12V / 0.5A Fan Output
- Thermal Shut-Down feature
- MTBF : > 3M hours as per Telcordia SR-332, issue 3
- Approved with metal enclosures/accessories

	Electrical Specifications		
Input Voltage	90-264 VAC/390 VDC, Universal (Derate from 100% at 115VAC to 78% at 90VAC)		
Input Frequency	47-63 Hz		
Input Current	115 VAC: 6.0 A max. 230 VAC: 3.0 A max.		
No Load Power	< 0.5W @ 115VAC < 0.7W @ 230VAC		
Inrush Current	115 VAC – 25 A, 230 VAC – 45 A, 264 VAC – 75 A		
Leakage Current	<200uA @115VAC and <400uA @230VAC		
Efficiency	92%(48V), 91%(24V), 90%(12V,15V) typical@ 230VAC full load		
Hold-up Time	Full Load > 16 ms typical Convection Load > 55 ms typical Conduction Load > 30ms typical		
Power Factor	exceeds 0.95 with Full Load		
Output Power	up to 550W (Forced Air Cooled)		
	up to 250W (Conduction Cooled)		
	up to 150W (Convection Cooled)		
Output Voltage Adjustability	+/-3%		
Line Regulation	+/-0.5%		
Load Regulation	+/-1%		
Transient Response	50-100% step load change, at 0.1A/uS slew rate, 50% duty cycle, 50Hz=5% ,		
	recovery time < 5 ms		
Rise Time	55 ms typical		
Set Point Tolerance	+/-1%		
Over Current Protection	>110% ,Hiccup mode / Auto Recovery		
Over Voltage Protection	110 to 140% , Hiccup mode / Auto Recovery		
Short Circuit Protection	Hiccup mode / Auto Recovery		
Switching Frequency	PFC – 70 to 130 KHz ,Resonant – 68 to 80 KHz		
Operating Temperature	-40 to +70°C, $*$ -40 to 0°C startup is guaranteed with spec deviation (ref note 6)		
Storage Temperature	-40 to +85°C		
Relative Humidity	5% to 95%, noncondensing		
Altitude	Operating: 16,000 ft.; Nonoperating: 40,000 ft.		
Isolation Voltage	Input to Output – 4000 VDC for ITE application		
	Input to Earth : 2500 VDC		



Model Number	Voltage	Max. Load (Convection)	Max. Load ⁷ (Conduction)	Max. Load (400 LFM)	Min. Load	Ripple ¹
WLC550-1012	12V	9.17A	16.67A	41.67A	0.0A	2%
WLC550-1015	15V	7.33A	13.33A	33.33A	0.0A	2%
WLC550-1024	24V	6.25A	10.42A	22.92A	0.0A	1%
WLC550-1030	30V	5.00A	8.33A	18.33A	0.0A	1%
WLC550-1048	48V	3.13A	5.21A	11.46A	0.0A	1%
WLC550-1058	58V	2.59A	4.31A	9.48A	0.0A	1%

Add Suffix 'O' for Remote On/Off option (example: LFWLC550-1030-0)


For Power supply unit with L bracket (metal accessory option) add "-L" suffix at the end of model number

For Power supply unit with U channel (metal accessory option) add "-U" suffix at the end of model number

For Power supply unit with CK Cover kit (metal accessory option) add "-CK" suffix at the end of model number

For Power supply unit with CK Cover kit with FAN (metal accessory option) add "-CKF" suffix at the end of model number

REMOTE ON/OFF INHIBIT



4EM-20-348

Innovations in Power


39-DE60-48750-002 / A4

	Pin Connection	is
J1	Pin 1 Pin 2 Pin 3	AC LINE NOT FITTED AC NEUTRAL
J2	Pin 1 Pin 2	V1 +VE V1 -VE
J3	Pin 1	FAN +VE
J21 (Remote On/Off)	Pin 2 Pin 1	FAN -VE +VE(External)
	Pin 2	-VE (External)

Notes

- 1. Ripple is peak to peak with 20 MHz bandwidth and 10 µF (Electrolytic capacitor) in parallel with a 0.1 µF capacitor at rated line voltage and load ranges.
- 2. Combined output power of main output, fan supply shall not exceed max. Power rating.
- 3. Fan supply output voltage tolerance including set point accuracy, line and load regulation is +/-10% and Ripple and noise is less than 10%.
- 4. Specifications are for nominal input voltage, 25°C unless otherwise stated.
- 5. Thermal shutdown feature : The power supply goes in hiccup mode when the temperature of Substrate PCB exceeds 110 °C (+/-10 °C).
- 6. Output ripple can be more than 10% of the output voltage.
- 7. Refer Recommended Conduction Plate & Clearance on Page No. 6.

	Mechanical Specifications			
AC Input Connector (J1)	JST : B3P-VH-B(LF)(SN) or equivalent Mating: VHR-3M or equivalent Pins : SVH-41T-P1.1 or equivalent			
Earth (J4)	Molex: 19705-4301			
	Mating: 19003-0001			
DC Output Connector (J2)	6-32 inches Screw Pan HD			
(Screw Terminal)	Mating: Designed to accept Ring Tongue Terminal AMP : 8-31886-1,			
	wherein one 16 AWG(max) wire can be crimped.			
	Note : One Ring Tongue Terminal with 16 AWG is recommended for current up to 11A onl			
	Use multiple tongue terminals with wire f	for more current		
Aux (Fan) Output (J3)	AMP :640456-2			
Remote On/Off (J21)	Mating: 640440-2			
Dimensions	5 x 3 x 1.5 inches			
	(127 x 76.2x 38.1 mm)			
Weight	500 gm approx			
	EMC			
Parameter	Conditions/Description	Criteria		
Conducted Emissions	EN55032-B, CISPR22-B, FCC PART15-B	Pass		
Radiated Emissions	EN 55032 A	Pass		
		Level B with external core (King core K5B R		
		25x12x15-M in input cable)		
Input Current Harmonics	EN 61000-3-2	Class D		
Voltage Fluctuation and Flicker	EN 61000-3-3	Pass		
ESD Immunity	EN 61000-4-2	Level 3, Criterion A		
Radiated Field Immunity	EN 61000-4-3	Level 3, Criterion A		
Electrical Fast Transient Immunity	EN 61000-4-4	Level 3, Criterion A		
Surge Immunity	EN 61000-4-5	Level 3, Criterion A		
Conducted Immunity	EN 61000-4-6	Level 3, Criterion A		
Magnetic Field Immunity	EN 61000-4-8	Level 3, Criterion A		
Voltage dips, interruptions	EN 61000-4-11	Criterion A & B		
	Safety			
CE Mark	Complies with LVD Directive			
Approval Agency	Nemko, UL, C-UL			
Safety Standard(s) IEC 62368-1:2018, IEC 60950-1(ed.2);am1;am2				
	EN 62368-1:2014;A11, EN 60950-1:2006;A11;A1;A12;A2			
	UL 62368-1 & CAN/CSA C22.2 No. 62368-1:19, UL 60950-1 and CAN/CSA C22.2 No. 60950-1-07			
Safety File Number(s)	CB Test Certificate No : NO112396			
	Nemko Certificate No: P20224603			
	UL Certificate No: E515384-A6003-UL			



4EM-20-348

39-DE60-48750-002 / A4

Maximum Operating Temperature

8

Y

BOTTOM PCB

9

0


Q8

Q7


 \bigcirc

ШП


For reliable and safe operation, please make sure the maximum component temperatures given in table below is not exceeded.





Description	Max Temp Allowed
	(°C)
Common mode chokes	95
Input Bulk Capacitors	90
Differential choke	110
Boost Choke	110
Output Transformer	125 (for 12V & 15V)
	110 (for 24V,30V,48V,58V)
Output Capacitor	90
Bridge Rectifier	120
Aluminium Clad PCB	105
Output Rectifiers	110
	Common mode chokes Input Bulk Capacitors Differential choke Boost Choke Output Transformer Output Capacitor Bridge Rectifier Aluminium Clad PCB



















Mechanical Drawing

WLC550 WITH CK

